

SICK Sensor Intelligence.

SAFETY LASER SCANNERS

SAFETY LASER SCANNERS



Ordering information

Sub prod- uct family	Model	Scanning angle	Protective field range	Number of fields	Туре	Part no.
S300 Ad- vanced	Sensor without sys- tem plug	270°	3 m	12	S30B- 3011CA	1056428

The system plug has to be ordered separately. For details, see "Accessories, plug connnectors and cables".

Other models and accessories → www.sick.com/S300

Illustration may differ



Detailed technical data

Features

Sub product family	S300 Advanced
Model	Sensor without system plug
Application	Indoor
Protective field range	3 m
Warning field range	8 m (at 15 % reflectivity)
Distance measuring range	30 m
Type of field set	Triple field sets
Number of field sets	4
Number of fields	12
Number of monitoring cases	4
Scanning angle	270°
Resolution (can be configured)	30 mm, 40 mm, 50 mm, 70 mm, 150 mm
Angular resolution	0.5°
Response time	80 ms ¹⁾
Protective field supplement	100 mm
Number of multiple samplings	2 16, configurable
Delay of automatic reset	2 s 60 s, configurable

 $^{\left(1\right) }$ Depending on basic response time and multiple sampling.

Safety-related parameters

Туре	Type 3 (IEC 61496)
Safety integrity level	SIL 2 (IEC 61508)

SAFETY LASER SCANNERS

Category	Category 3 (EN ISO 13849)
Performance level	PL d (EN ISO 13849)
$\mbox{PFH}_{\mbox{D}}$ (mean probability of a dangerous failure per hour)	8.0 x 10 ⁻⁸
T _M (mission time)	20 years (EN ISO 13849)
Safe state in the event of a fault	At least one OSSD is in the OFF state.

Functions

Restart interlock	✓
External device monitoring (EDM)	✓
Multiple sampling	✓
Monitoring case switching	✓
Static protective field switching	✓
Contour as a reference	✓
Integrated configuration memory	✓
Measured data output	Via RS-422
Safe SICK device communication via EFI	✓

Interfaces

Connection type	System plug with or without connecting cable
Universal I/Os	5 ¹⁾
Inputs	
External device monitoring (EDM)	1 ²⁾
Reset/restart	1 ²⁾
Static control inputs	2
Static control inputs with EFI	5 ³⁾
Standby	1
Outputs	
OSSD pairs	1
Application diagnostic outputs	3 4)
Configuration method	PC with CDS (Configuration and Diagnostic Software)
Configuration and diagnostics interface	RS-232
Transmission rate	38.4 kBaud
Data interface	RS-422
Transmission rate	≤ 500 kBaud
Safe SICK device communication via EFI	
Transmission rate	≤ 500 kBaud
Length of cable	
Conductor cross section	0.22 mm ²

¹⁾ Freely programmable, e.g., external device monitoring input, reset input, contamination warning, reset required.

²⁾ Availability depends on the configuration of the universal I/Os.

³⁾ In combination with an EFI device (Flexi Soft or EFI gateway) five static control inputs are available. Otherwise two.

 $^{\rm 4)}$ Freely programmable, e.g. warning field, contamination, reset required.

SAFETY LASER SCANNERS

Electrical data

Protection class	III (EN 50178, EN 60950)
Supply voltage V _s	24 V DC (16.8 V DC 30 V DC)
Power consumption	$\leq 0.33 \text{ A}^{-1)}$ $\leq 1.7 \text{ A}^{-2)}$
Outputs	
Output signal switching devices (OSSDs)	2 x 250 mA
Application diagnostic outputs	3 x 100 mA ³⁾

 $^{1)}$ At 24 V DC without output load.

²⁾ At 24 V DC including maximum output load.

³⁾ Freely programmable, e.g. warning field, contamination, reset required.

Mechanical data		
Dimensions (W x H x D)	102 mm x 152 mm x 106 mm	
Weight	1.2 kg	
Housing material	Aluminum die cast	
Housing color	RAL 1021 (yellow)	
Optics cover material	Polycarbonate	
Optics cover surface finish	Outside with scratch-resistant coating	
Ambient data		
Enclosure rating	IP65 (EN 60529)	
Ambient operating temperature	-10 °C +50 °C	
Storage temperature	-25 °C +50 °C	
Vibration resistance	IEC 60068-2-6, IEC 60068-2-64, IEC 60721-3-5, IEC TR 60721-4-5, IEC 61496-3	
Class	5M1 (IEC 60721-3-5)	
Shock resistance	IEC 60068-2-27, IEC 60721-3-5, IEC TR 60721-4-5, IEC 61496-3	
Class	5M1 (IEC 60721-3-5)	
Continuous shock	50 m/s², 11 ms 100 m/s², 16 ms	

Other information

Type of light	Pulsed laser diode	
Wave length	905 nm	
Detectable remission factor	1.8 % > 1,000 %, reflectors	
Laser class	1 (21 CFR 1040.10 and 1040.11, IEC 60825-1)	
Classifications		
ECLASS 5.0	27272705	


ECLASS 5.0	21212105
ECLASS 5.1.4	27272705
ECLASS 6.0	27272705
ECLASS 6.2	27272705
ECLASS 7.0	27272705
ECLASS 8.0	27272705
ECLASS 8.1	27272705
ECLASS 9.0	27272705

SAFETY LASER SCANNERS

ECLASS 10.0	27272705
ECLASS 11.0	27272705
ECLASS 12.0	27272705
ETIM 5.0	EC002550
ETIM 6.0	EC002550
ETIM 7.0	EC002550
ETIM 8.0	EC002550
UNSPSC 16.0901	39121528


Dimensional drawing (Dimensions in mm (inch))

Laser scanner




SAFETY LASER SCANNERS

Scan plane origin



Connection diagram

Protective field switching with one pair of static inputs



S300 Advanced in connection with UE10-30S

Operating mode: With restart interlock and external device monitoring Protective field switching with control input IN A

Comments

¹⁾ Output circuits: These contacts must be incorporated into the control such that the dangerous state is brought to an end if the output circuit is open. For categories 4 and 3, they must be incorporated on two channels (x, y paths). Single-channel incorporation into the control (z path) is only possible with a single-channel control and taking the risk analysis into account.

SAFETY LASER SCANNERS

Recommended accessories

Other models and accessories → www.sick.com/S300

	Brief description	Туре	Part no.
Mounting bra	ckets and plates		
L	1 piece, mounting bracket for rear mounting on wall or machine	Mounting kit 1a	2034324
	$\ensuremath{1}$ piece, mounting bracket for rear mounting on wall or machine with protection of optics hood	Mounting kit 1b	2034325
	1 piece, mounting bracket, adjustable lateral axis, only in conjunction with mounting kit 1a (2034324) or 1b (2034325)	Mounting kit 2	2039302
	1 piece, mounting plate, adjustable longitudinal axis, only in conjunction with mount- ing kit 2 (2039302)	Mounting kit 3	2039303
Plug connecto	ors and cables		
Q	 Connection type head A: Flying leads Connection type head B: Flying leads Cable: 15-wire, AWG20, PVC Description: Unshielded Note: On 100 m reel Items supplied: By the meter 	Connecting cable	6030795
Q	 Connection type head A: Flying leads Connection type head B: Flying leads Cable: 2-wire, twisted pair, 120 Ohm, PVC Description: Shielded Note: Fitting for EFI connections Items supplied: By the meter 	EFI connecting cable	6029448
	 Connection type head A: Male connector, M8, 4-pin, straight Connection type head B: Male connector, USB-A, straight Cable: 2 m, 4-wire, PVC Description: Unshielded, Configuration cable with integrated RS-232 transducer on USB for connecting a sensor configuration connection (M8, 4-pin) to the USB interface of a PC 	DSL-8U04G02M025KM1	6034574
	 Connection type head A: Male connector, M8, 4-pin, straight Connection type head B: Male connector, USB-A, straight Cable: 10 m, 4-wire, PVC Description: Unshielded, Configuration cable with integrated RS-232 transducer on USB for connecting a sensor configuration connection (M8, 4-pin) to the USB interface of a PC 	DSL-8U04G10M025KM1	6034575
1000	 Connection type head A: System plug Description: Without cable, Not for use of incremental encoders, integrated configuration storage, For S300 Standard, Advanced, Expert and Professional Items supplied: With 1 x cable gland M16, 1 x blanking plug M16, 2 x blanking plug M12 	SX0B-A0000G	2032807
	 Connection type head A: System plug Cable: 5 m, 15-wire, PVC Description: Pre-assembled, Not for use of incremental encoders, integrated configuration storage, unshielded, For S300 Advanced, Expert and Professional Connection systems: Flying leads Items supplied: With 1 x cable gland M16, 1 x blanking plug M16, 2 x blanking plug M12 	SXOB-B1505G	2034264

SAFETY LASER SCANNERS

Brief description	Туре	Part no.
 Connection type head A: System plug Cable: 10 m, 15-wire, PVC Description: Pre-assembled, Not for use of incremental encoders, integrated configuration storage, unshielded, For S300 Advanced, Expert and Professional Connection systems: Flying leads Items supplied: With 1 x cable gland M16, 1 x blanking plug M16, 2 x blanking plug M12 	SXOB-B1510G	2034265

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

