

# WSE4SL-3N1137

MINIATURE PHOTOELECTRIC SENSORS

**SICK**Sensor Intelligence.



# Ordering information

Туре	Part no.
WSE4SL-3N1137	1058250

Other models and accessories → www.sick.com/W4

Illustration may differ



#### Detailed technical data

### **Features**

Functional principle	Through-beam photoelectric sensor
Sensing range max.	0 m 60 m
Sensing range	0 m 50 m
Emitted beam	
Light source	Laser 1)
Type of light	Visible red light
Light spot size (distance)	Ø 1 mm (500 mm)
Key laser figures	
Normative reference	EN 60825-1:2014, IEC 60825-1:2014 / CDRH 21 CFR 1040.10 & 1040.11
Laser class	1
Wave length	650 nm
Adjustment	Single teach-in button
Special applications	Detecting small objects
Part number of individual components	2064096 WS4SL-3D1136 2064098 WE4SL-3N1132
Mounting hole	M3

 $<sup>^{1)}</sup>$  Average service life: 50,000 h at TU = +25 °C.

# Safety-related parameters

MTTF <sub>D</sub>	350 years (EN ISO 13849-1) <sup>1)</sup>
	330 years (LIV 130 13049-1)

 $<sup>^{1)}</sup>$  Mode of calculation: Parts-Count-calculation.

DC <sub>avg</sub>	0 %
-------------------	-----

<sup>1)</sup> Mode of calculation: Parts-Count-calculation.

#### Electrical data

Supply voltage U <sub>B</sub>	10 V DC 30 V DC <sup>1)</sup>
Ripple	< 5 V <sub>pp</sub> <sup>2)</sup>
Current consumption	30 mA <sup>3)</sup>
Protection class	III
Digital output	
Туре	NPN <sup>4)</sup>
Switching mode	Light/dark switching <sup>4)</sup>
Output current I <sub>max</sub> .	≤ 100 mA
Response time	$\leq 0.5 \text{ ms}^{5)}$
Switching frequency	1,000 Hz <sup>6)</sup>
Output function	Complementary
Circuit protection	A <sup>7)</sup> B <sup>8)</sup> C <sup>9)</sup>

 $<sup>^{1)}</sup>$  Limit values when operated in short-circuit protected network: max. 8 A.

### Mechanical data

Housing	Rectangular
Design detail	Slim
Dimensions (W x H x D)	12.2 mm x 41.8 mm x 17.3 mm
Connection	Cable, 4-wire, 2 m <sup>1)</sup>
Connection detail	
Conductor size	0.14 mm <sup>2</sup>
Length of cable (L)	2 m <sup>1)</sup>
Material	
Housing	Plastic, Novodur
Front screen	Plastic, PMMA
Cable	PVC
Weight	100 g

 $<sup>^{1)}</sup>$  Do not bend below 0  $^{\circ}\text{C}.$ 

 $<sup>^{2)}\,\</sup>mathrm{May}$  not exceed or fall below  $\mathrm{U}_{\mathrm{V}}$  tolerances.

<sup>3)</sup> Without load.

<sup>4)</sup> Q = light switching.

<sup>5)</sup> Signal transit time with resistive load.

<sup>6)</sup> With light/dark ratio 1:1.

 $<sup>^{7)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

<sup>8)</sup> B = inputs and output reverse-polarity protected.

<sup>9)</sup> C = interference suppression.

#### Ambient data

Enclosure rating	IP66 IP67
Ambient operating temperature	-10 °C +50 °C
Ambient operating temperature extended	-30 °C +55 °C <sup>1) 2)</sup>
Ambient temperature, storage	-30 °C +70 °C


 $<sup>^{1)}</sup>$  As of T<sub>a</sub> = 50 °C, a max. supply voltage V<sub>max.</sub> = 24 V and a max. load current I<sub>max.</sub> = 50 mA is permitted.

#### Classifications

ECLASS 5.0	27270901
ECLASS 5.1.4	27270901
ECLASS 6.0	27270901
ECLASS 6.2	27270901
ECLASS 7.0	27270901
ECLASS 8.0	27270901
ECLASS 8.1	27270901
ECLASS 9.0	27270901
ECLASS 10.0	27270901
ECLASS 11.0	27270901
ECLASS 12.0	27270901
ETIM 5.0	EC002716
ETIM 6.0	EC002716
ETIM 7.0	EC002716
ETIM 8.0	EC002716
UNSPSC 16.0901	39121528


# Connection diagram

# Cd-231




 $<sup>^{2)}</sup>$  Operation below Tu -10 °C is possible if the sensor is already switched on at Tu > -10 °C, then cools down, and the supply voltage is subsequently not switched off. Switching on below Tu -10 °C is not permissible.

#### Characteristic curve



# Light spot size

#### Radius in mm (inch)




### Dimensions in mm (inch)


Sensing range	Vertical	Horizontal
0.5 m	< 1.0	< 1.0
(1.64 feet)	(0.04)	(0.04)
1 m	1.5	1.2
(3.28 feet)	(0.06)	(0.05)
5 m	15	11
(16.40 feet)	(0.59)	(0.43)
<b>10 m</b>	45	28
(32.81 feet)	(1.77)	(1.10)
60 m	336	200
(196.85 feet)	(13.23)	(7.87)



# Light spot size (detailed view)


### Detailed view close range






# Vertical Horizontal

# Sensing range diagram



# Dimensional drawing (Dimensions in mm (inch))

WL4SL-3, WL4SLG-3, WSE4SL-3, cable



- ① Center of optical axis
- ② Threaded mounting hole M3
- 3 Connection
- 4 LED indicator green: Supply voltage active
- ⑤ LED indicator yellow: Status of received light beam
- 6 Single teach-in button

#### Recommended accessories

Other models and accessories → www.sick.com/W4

	Brief description	Туре	Part no.
Plug connecto	rs and cables		
	<ul> <li>Connection type head A: Male connector, M8, 4-pin, straight</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: 0.14 mm² 0.5 mm²</li> </ul>	STE-0804-G	6037323

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

