

WSE4SL-3P2437V

MINIATURE PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
WSE4SL-3P2437V	1058269

Other models and accessories → www.sick.com/W4

Illustration may differ





Detailed technical data

Features

Functional principle	Through-beam photoelectric sensor
Sensing range max.	0 m 60 m
Sensing range	0 m 50 m
Emitted beam	
Light source	Laser 1)
Type of light	Visible red light
Light spot size (distance)	Ø 1 mm (500 mm)
Key laser figures	
Normative reference	EN 60825-1:2014, IEC 60825-1:2014 / CDRH 21 CFR 1040.10 & 1040.11
Laser class	1
Wave length	650 nm
Adjustment	Single teach-in button
Special applications	Hygienic and washdown zones, Detecting small objects
Part number of individual components	2064100 WS4SL-3D2436V 2064103 WE4SL-3P2432V
Housing design	Washdown ²⁾
Mounting hole	M3

 $^{^{1)}}$ Average service life: 50,000 h at T_U = +25 °C.

²⁾ Difference between standard/washdown and hygiene: The essential difference between a standard/washdown product and a hygiene product is that where the process and contact with the medium (activity in the vicinity of the food) are concerned, a hygiene product is designed in accordance with the latest standards and hygiene design guidelines, and materials are selected accordingly.

Safety-related parameters

MTTF _D	355 years (EN ISO 13849-1) ¹⁾
DC _{avg}	0 %

 $^{^{1)}}$ Mode of calculation: Parts-Count-calculation.

Electrical data

Supply voltage U _B	10 V DC 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Current consumption	30 mA ³⁾
Protection class	III
Digital output	
Туре	PNP ⁴⁾
Switching mode	Light/dark switching ⁴⁾
Output current I _{max.}	≤ 100 mA
Response time	\leq 0.5 ms $^{5)}$
Switching frequency	1,000 Hz ⁶⁾
Output function	Complementary
Circuit protection	A ⁷⁾ B ⁸⁾ C ⁹⁾

 $^{^{1)}}$ Limit values when operated in short-circuit protected network: max. 8 A. $^{2)}$ May not exceed or fall below U $_{\rm V}$ tolerances.

Mechanical data

Housing	Rectangular
Design detail	Slim
Dimensions (W x H x D)	15.3 mm x 55.4 mm x 22.2 mm
Connection	Male connector M12, 4-pin ¹⁾
Material	
Housing	Stainless steel, Stainless steel V4A (1.4404, 316L)
Front screen	Plastic, PMMA
Weight	45 g

 $^{^{1)}}$ Max. tightening torque: 0.7 Nm.

³⁾ Without load.

 $^{^{4)}}$ Q = light switching.

⁵⁾ Signal transit time with resistive load.

⁶⁾ With light/dark ratio 1:1.

 $^{^{7)}}$ A = V_S connections reverse-polarity protected.

⁸⁾ B = inputs and output reverse-polarity protected.

⁹⁾ C = interference suppression.

Ambient data

Enclosure rating	IP66 IP67 IP68 IP69K ¹⁾
Ambient operating temperature	-10 °C +50 °C
Ambient operating temperature extended	-30 °C +55 °C ^{2) 3)}
Ambient temperature, storage	-30 °C +70 °C
RoHS certificate	✓


 $^{^{1)}}$ Only in case of correctly mounted IP69K connecting cable.

Classifications

ECLASS 5.0	27270901
ECLASS 5.1.4	27270901
ECLASS 6.0	27270901
ECLASS 6.2	27270901
ECLASS 7.0	27270901
ECLASS 8.0	27270901
ECLASS 8.1	27270901
ECLASS 9.0	27270901
ECLASS 10.0	27270901
ECLASS 11.0	27270901
ECLASS 12.0	27270901
ETIM 5.0	EC002716
ETIM 6.0	EC002716
ETIM 7.0	EC002716
ETIM 8.0	EC002716
UNSPSC 16.0901	39121528

Connection diagram

Cd-232




- ① Sender
- 2 Receiver

 $^{^{2)}}$ As of T_a = 50 °C, a max. supply voltage V_{max.} = 24 V and a max. load current I_{max.} = 50 mA is permitted.


 $^{^{3)}}$ Operation below Tu -10 °C is possible if the sensor is already switched on at Tu > -10 °C, then cools down, and the supply voltage is subsequently not switched off. Switching on below Tu -10 °C is not permissible.

Characteristic curve



Light spot size

Radius in mm (inch)



Dimensions in mm (inch)


Sensing range	Vertical	Horizontal
0.5 m	< 1.0	< 1.0
(1.64 feet)	(0.04)	(0.04)
1 m	1.5	1.2
(3.28 feet)	(0.06)	(0.05)
5 m	15	11
(16.40 feet)	(0.59)	(0.43)
10 m	45	28
(32.81 feet)	(1.77)	(1.10)
60 m	336	200
(196.85 feet)	(13.23)	(7.87)



Light spot size (detailed view)


Detailed view close range






Vertical
Horizontal

Sensing range diagram



Dimensional drawing (Dimensions in mm (inch))

WSE4SL-3, WL4SLG-3





- ① Center of optical axis
- ② Threaded mounting hole M3
- 3 LED indicator yellow: Status of received light beam
- 4 LED indicator green: Supply voltage active
- ⑤ Single teach-in button

Recommended accessories

Other models and accessories → www.sick.com/W4

	Brief description	Туре	Part no.
Others			
	Connection type head A: Female connector, M12, 4-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB). Please do not use cleaning agents of any other Kind., Not resistant against lactic acid & hydrogen peroxide (H2O2) Application: Hygienic and washdown zones	DOL-1204-G05MNI	6052615

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

