

V3T13S-MR62A8

TriSpector1000

3D MACHINE VISION





Ordering information

Туре	Part no.
V3T13S-MR62A8	1060428

Other models and accessories → www.sick.com/TriSpector1000



Detailed technical data

Features

i catules	
Task	Position determination Presence inspection Quality check Measuring, 3D
Technology	3D triangulation
Product category	Configurable
Toolkit	Shape Area detection Blob Finder Volume Find plane Fixed plane
Working distance	291 mm 1,091 mm
Example field of view	540 mm x 200 mm
Illumination	Integrated
Illumination color	Red, laser, Visible, 660 nm, ± 7 nm
Laser class	2 (EN 60825-1:2014+A11:2021; IEC 60825-1:2014, Complies with the FDA performance requirements for laser products except for conformance with IEC 60825-1 Ed.3., as described in Laser Notice 56 dated May 8, 2019.)
Factory calibrated	✓
Width at minimum operating distance	180 mm
Width at maximum operating distance	660 mm
Maximum height range	800 mm
Imaging angle	67°
Offline support	Emulator

Mechanics/electronics

Connection type	M12, 12-pin male connector, A-coded (voltage supply, I/O) M12, 8-pin female connector, X-coded (Gigabit Ethernet) M12, 8-pin female connector, A-coded (encoder)
Connector material	Nickel plated brass
Supply voltage	24 V DC, ± 20 %
Ripple	< 5 V _{pp}
Power consumption	≤ 11 W
Current consumption	< 400 mA, without output load
Enclosure rating	IP67

Protection class	III
Housing material	Anodized aluminum
Window material	PMMA
Weight	1.7 kg
Dimensions (L x W x H)	307 mm x 62 mm x 84 mm

Performance

Scan/frame rate	5,000 3D profiles/s
Maximum number of profiles	2,500 Per image
Data points/profile	1,536
Height resolution	80 μm 670 μm
3D profile resolution	0.43 mm/px

Interfaces

Ethernet	√ , TCP/IP
Data transmission rate	1,000 Mbit/s
Serial	√ , RS-232, RS-422
Function	Encoder (RS-422 / DBS36E-BBCP02048)
Data transmission rate	Maximum encoder frequency: 300 MHz
Incremental	√ , ∏L
Configuration software	SOPAS ET
Digital input	3 (non-isolated)
Digital output	4 (non-isolated)
Encoder interface	RS-422 / TTL (DBS36E-BBCP02048)
Maximum encoder frequency	300 kHz

Ambient data

Electromagnetic compatibility (EMC)	EN 61000-6-2:2005 / EN 61000-6-3:2007
Shock load	15 g / 6 ms (EN 60068-2-27)
Vibration load	5 g, 10 Hz 150 Hz (EN 60068-2-6)
Ambient operating temperature	0 °C +50 °C ¹⁾
Storage temperature	-20 °C +70 °C ¹⁾

 $^{^{1)}}$ Permissible relative air humidity: 0 % ... 90 % (non-condensing).

Classifications


ECLASS 5.0	27310205
ECLASS 5.1.4	27310205
ECLASS 6.0	27310205
ECLASS 6.2	27310205
ECLASS 7.0	27310205
ECLASS 8.0	27310205
ECLASS 8.1	27310205
ECLASS 9.0	27310205
ECLASS 10.0	27310205

V3T13S-MR62A8 | TriSpector1000

3D MACHINE VISION

ECLASS 11.0	27310205
ECLASS 12.0	27310205
ETIM 5.0	EC001820
ETIM 6.0	EC001820
ETIM 7.0	EC001820
ETIM 8.0	EC001820
UNSPSC 16.0901	43211731


Dimensional drawing (Dimensions in mm (inch))




- ① Connector Encoder (thread inside)
- ② Connector Gigabit Ethernet (Gig E)
- ③ Connector Power I/O (thread inside)
- 4 LED; On
- ⑤ LED; State
- 6 LED; Link/Data
- ⑦ LED; Result
- 8 LED; Laser
- Fastening threads (M5 x 8.5 mm length)
- Optical receiver (center)
- ① Optical sender (center)
- Micro SD memory card

Field of view

Typical field of view



TriSpector1060 Typ. field of view in mm (inch)



Recommended accessories

Other models and accessories → www.sick.com/TriSpector1000

	Brief description	Туре	Part no.	
Mounting bra	Mounting brackets and plates			
	Mounting bracket set consisting of mounting bracket, cooling plate, includes angle display for setting the tilt angle	Mounting bracket	2076735	
Plug connecto	ors and cables			
	 Connection type head A: Male connector, M12, 5-pin, straight Connection type head B: Flying leads Cable: 2 m Description: Shielded Connection systems: Flying leads 	Connecting cable	6024860	
	 Connection type head A: Male connector, M12, 8-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 8-wire, PVC Description: Sensor/actuator cable, shielded Application: Zones with chemicals 	YM2A28- 050VA6XLEAX	2096233	
Ro Es	 Connection type head A: Female connector, M12, 8-pin, straight, A-coded Connection type head B: Male connector, M12, 8-pin, straight, A-coded Signal type: Sensor/actuator cable Cable: 2 m, 8-wire, PUR, halogen-free Description: Sensor/actuator cable, shielded Application: Zones with oils and lubricants, Drag chain operation 	YF2A28- 020UA6M2A28	2096105	
	 Connection type head A: Female connector, M12, 12-pin, straight Connection type head B: Male connector, M12, 5-pin, straight Signal type: Power Cable: 0.25 m Description: Power, Cable for connecting a TriSpector to power supply unit 2079609 	YF2A6B- C25XXXM2A15	2079766	
6	 Connection type head A: Female connector, M12, 12-pin, straight Connection type head B: Male connector, M12, 17-pin, straight Signal type: Power, digital I/Os, serial Cable: 0.25 m Description: Power, digital I/Os, serial, shielded, cable to connect TriSpector to CDF600-2, needs to be used in combination with further connection cable (e.g. part number 2055419) 	YF2AAB- C25S01M2AAD	2086398	

V3T13S-MR62A8 | TriSpector1000

3D MACHINE VISION

	Brief description	Туре	Part no.
1	 Connection type head A: Male connector, M12, 8-pin, straight, X-coded Connection type head B: Male connector, RJ45, 8-pin, straight Signal type: Ethernet, Gigabit Ethernet Cable: 2 m, 8-wire, PUR, halogen-free Description: Ethernet, Gigabit Ethernet, shielded Application: Zones with oils and lubricants 	YM2X18- 020EG1MRJA8	2106258
Others			
	24 V DC power supply unit, 5-pin, M12, for TriSpector in combination with connecting cable 2079766	Power supply unit	2079609

Recommended services

Additional services → www.sick.com/TriSpector1000

	Туре	Part no.
Commissioning		
 Product area: 3D machine vision Range of services: Inspection of connection, fine adjustment, optimization of parameters of SICK product as well as tests, set-up of previously defined functions of image settings, task configuration, result settings, interface settings, as well as verification tests Travel expenses: The prices do not include travel costs such as hotel, flight, travel time and expenses. Duration: Additional work will be invoiced separately 	TriSpector1000 commissioning	1612239
Maintenance		
 Product area: 3D machine vision Range of services: Inspection, analysis and restoring of defined functions, inspection and adaptation of previously defined functions of image settings, task configuration, result settings, and interface settings Duration: Additional work will be invoiced separately Travel expenses: The prices do not include travel costs such as hotel, flight, travel time and expenses. 	TriSpector1000 maintenance	1612243
Extended warranty		
 Product area: Identification solutions, machine vision, Detection and ranging solutions, safety camera sensors, Safety laser scanners, Safety radar sensors Range of services: The services correspond to the scope of the statutory manufacturer warranty (SICK general terms of delivery). Duration: Five-year warranty from delivery date. 	Extended warranty for a total of five years from delivery date	1680671

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

