



DL100-21HA2109

Dx100

TIME-OF-FLIGHT SENSORS

SICK
Sensor Intelligence.



Illustration may differ



Ordering information

| Type | part no. |
|----------------|----------|
| DL100-21HA2109 | 1060387 |

Other models and accessories → www.sick.com/Dx100

Detailed technical data

Features

| | |
|----------------------------------|--|
| Measuring range | 0.15 m ... 100 m, on "diamond grade" reflective tape |
| Scope | Indoor |
| Target | Reflector |
| Resolution | 0.1 mm, 0.125 mm, 1 mm, 10 mm, 100 mm |
| Repeatability | 0.5 mm ¹⁾ |
| Measurement accuracy | ± 2 mm ²⁾ |
| Response time | 2 ms |
| Measurement cycle time | 1 ms ³⁾ |
| Output time | 1 ms |
| Emitted beam | |
| Light source | Laser, red ⁴⁾ |
| Type of light | Visible red light |
| Typ. light spot size (distance) | 5 mm + (2 mm x distance in m) |
| Key laser figures | |
| Normative reference | IEC 60825-1:2014, EN 60825-1:2014 |
| Laser class | 2 |
| Max. movement speed | 15 m/s |
| Acceleration (max.) | ≤ 15 m/s ² |
| Heating | ✓ |
| Safety-related parameters | |
| MTTF _D | 101 years |

¹⁾ Statistical error 1 σ, environmental conditions constant, min. warm-up time 10 min.

²⁾ From 150 mm ... 180 mm measuring range the accuracy can reach ± 4 mm.

³⁾ Measurement cycle synchronous to PLC request.

⁴⁾ Average service life: 100,000 h at T_U = +25 °C.

DC_{avg} 0%

- 1) Statistical error 1 σ , environmental conditions constant, min. warm-up time 10 min.
 2) From 150 mm ... 180 mm measuring range the accuracy can reach ± 4 mm.
 3) Measurement cycle synchronous to PLC request.
 4) Average service life: 100,000 h at T_U = +25 °C.

Interfaces

| | |
|---------------------------------------|--|
| CANopen | ✓ , CANopen |
| Digital output | |
| Number | 2 ¹⁾ |
| Type | Push-pull: PNP/NPN |
| Function | Distance: Distance switching output |
| | Speed; Speed output |
| | Service: Warning message as the sensor ages, if the damping value is exceeded (for example when contaminated, if the permitted interior device temperature is exceeded or undercut, if the measured value has a plausibility error, if the laser is not ready for operation, if the heating is switched on |
| | Laser off |
| | Preset |
| Maximum output current I _A | ≤ 100 mA ²⁾ |
| Multifunctional input (MF) | 1 x MF1 ³⁾ |

1) HIGH = > V_S - 3 V / LOW = < 2 V.

2) Max. 100 nF/20 mH.

3) HIGH > 12 V / LOW < 3 V.

Electronics

| | |
|-------------------------------------|--|
| Supply voltage U_B | DC 18 V ... 30 V, limit values |
| Current consumption | At 24 V DC < 1,000 mA |
| Ripple | 5 V _{pp} ¹⁾ |
| Modulation frequency | Fix |
| Initialization time | Typ. 1.5 s ²⁾ |
| Display | 6 digit 5 x 7 dot matrix display, LEDs |
| Enclosure rating | IP65 |
| Protection class | III |
| Connection type | Male connector |

1) May not fall short of or exceed V_S tolerances.

2) After loss of reflector < 40 ms.

Mechanics

| | |
|-------------------------------|--|
| Dimensions (W x H x D) | 69.4 mm x 82.5 mm x 100.2 mm |
| Housing material | Metal (Aluminum die cast) |
| Window material | Plastic (PMMA) |
| Weight | Approx. 800 g (with mounting bracket: approx. 1,600 g) |

Ambient data

| | |
|--|---|
| Ambient temperature, operation | -40 °C ... +55 °C, operation with heating ^{1) 2)} -40 °C ... +75 °C, operation with cooling case ^{1) 2)} |
| Ambient temperature, storage | -40 °C ... +75 °C |
| Effect of air pressure | 0.3 ppm/hPa |
| Effect of air temperature | 1 ppm/K |
| Temperature drift | Typ. 0.1 mm/K |
| Typ. Ambient light immunity | ≤ 100,000 lx |
| Mechanical load | Shock: (EN 600 68-2-27) Sine: (EN 600 68-2-6) Noise: (EN 600 68-2-64) |
| Electromagnetic compatibility (EMC) | EN 61000-6-2, EN 61000-6-4 ³⁾ |

¹⁾ Temperatures < -10 °C require warm-up time of typ. 7 minutes.


²⁾ For operation below -20 °C, a supply voltage of at least 24 V is required.

³⁾ This is a Class A device. This device can cause radio interference in living quarters.

Classifications

| | |
|-----------------------|----------|
| ECLASS 5.0 | 27270801 |
| ECLASS 5.1.4 | 27270801 |
| ECLASS 6.0 | 27270801 |
| ECLASS 6.2 | 27270801 |
| ECLASS 7.0 | 27270801 |
| ECLASS 8.0 | 27270801 |
| ECLASS 8.1 | 27270801 |
| ECLASS 9.0 | 27270801 |
| ECLASS 10.0 | 27270801 |
| ECLASS 11.0 | 27270801 |
| ECLASS 12.0 | 27270916 |
| ETIM 5.0 | EC001825 |
| ETIM 6.0 | EC001825 |
| ETIM 7.0 | EC001825 |
| ETIM 8.0 | EC001825 |
| UNSPSC 16.0901 | 41111613 |


Dimensional drawing




Dimensions in mm (inch)

- ① Optical axis, sender
- ② Optical axis, receiver
- ③ Zero level
- ④ Threaded mounting hole M5
- ⑤ status LED [status]
- ⑥ Display
- ⑦ Control elements


Voltage supply connection type




CANin connection type




CANout connection type




Voltage supply connection diagram




CAN out connection diagram




CAN in connection diagram




Connection diagram Dx100 power supply, M12 male connector, 4-pin



Ethernet connection diagram




Adjustment possible DL100-xxXXxx09



- ① status LED [status]
- ② Display
- ③ Control elements

Recommended accessories

Other models and accessories → www.sick.com/Dx100

| | Brief description | Type | part no. |
|---|---|--------------|------------|
| reflectors and optics | | | |
| | Strich | | On request |
| | Strich | | On request |
| Mounting systems | | | |
|  | <ul style="list-style-type: none">Description: Alignment unit for Dx100, incl. mounting materialMaterial: SteelDetails: Steel, zinc coated | BEF-AH-DX100 | 2058653 |

| | Brief description | Type | part no. |
|---|---|---|------------|
| connectors and cables | | | |
| | <ul style="list-style-type: none"> Connection type head A: Male connector, M12, 5-pin, straight, A-coded Connection type head B: Flying leads Signal type: Fieldbus, CANopen, DeviceNet™ Cable: 10 m, PUR, halogen-free Description: Fieldbus, unshielded, CANopen, DeviceNet™ | YM2A14-100C1BXLEAX | 6021293 |
|  | <ul style="list-style-type: none"> Connection type head A: Female connector, M12, 5-pin, A-coded Connection type head B: Flying leads Signal type: Power, CAN Cable: 5 m, 5-wire Description: Power, unshielded, CAN | DOL-1205-G05M_Can | 6021166 |
|  | <ul style="list-style-type: none"> Connection type head A: Female connector, M12, 5-pin, straight, A-coded Connection type head B: Male connector, M12, 5-pin, straight, A-coded Signal type: DeviceNet™, CANopen Cable: 5 m, PUR, halogen-free Description: DeviceNet™, shielded, CANopen | CAN cable (male connector - female connector) | 6021168 |
|  | <ul style="list-style-type: none"> Connection type head A: Male connector, M12, 4-pin, straight, D-coded Connection type head B: Male connector, RJ45, 8-pin, straight Signal type: PROFINET Cable: 5 m, 4-wire, AWG22, PUR, halogen-free Description: PROFINET, shielded | SSL-2J04-G05MZ | 6035389 |
|  | <ul style="list-style-type: none"> Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, shielded Application: Zones with chemicals, Uncontaminated zones | YF2A24-050VB4XLEAX | 2096247 |
| | Strich | | On request |
|  | <ul style="list-style-type: none"> Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 10 m, 4-wire, PVC Description: Sensor/actuator cable, shielded Application: Zones with chemicals, Uncontaminated zones | YF2A24-100VB4XLEAX | 2144087 |
|  | <ul style="list-style-type: none"> Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 0.6 m, 4-wire, PVC Description: Sensor/actuator cable, shielded Application: Zones with chemicals, Uncontaminated zones | YF2A24-C60VB4XLEAX | 2145742 |
|  | <ul style="list-style-type: none"> Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PVC Description: Sensor/actuator cable, shielded Application: Zones with chemicals, Uncontaminated zones | YF2A24-020VB4XLEAX | 2145744 |
|  | <ul style="list-style-type: none"> Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 1 m, 4-wire, PVC Description: Sensor/actuator cable, shielded Application: Zones with chemicals, Uncontaminated zones | YF2A24-010VB4XLEAX | 2145743 |
|  | <ul style="list-style-type: none"> Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 3 m, 4-wire, PVC Description: Sensor/actuator cable, shielded Application: Zones with chemicals, Uncontaminated zones | YF2A24-030VB4XLEAX | 2145746 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com