

IRT-P211C63

ZoneControl

MULTITASK PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
IRT-P211C63	1063127

Other models and accessories → www.sick.com/ZoneControl

Illustration may differ



Detailed technical data

Features

Functional principle	Photoelectric proximity sensor
Functional principle detail	Background suppression
Actuator	Pneumatic, valve supplied separately
Max. number of sensors	Approx. 30 ¹⁾ Approx. 50 ²⁾
Logical principle of operation	Single accumulation
Type of Release	Single release, block (slug) release
Dimensions (W x H x D)	20.6 mm x 99.2 mm x 48.9 mm
Sensing range max.	60 mm 900 mm
Sensing range	60 mm 900 mm
Focus	7°
Type of light	Infrared light
Light source	LED ³⁾
Light spot size (distance)	Ø 20 mm (500 mm)
Angle of dispersion	7°
Adjustment	Potentiometer, 9 turns
Special applications	ZoneControl

 $^{^{1)}\,\}mathrm{When}$ powerd from the end of the IR daisy chain.

²⁾ When powerd from center of the IR daisy chain.

 $^{^{3)}}$ Average service life: 100,000 h at TU = +25 °C.

Mechanics/electronics

Supply voltage \mathbf{U}_{B}	10 V DC 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Current consumption	20 mA ³⁾
Switching output	PNP
Signal voltage PNP HIGH/LOW	Approx. V _S – 0.5 V / 0 V
Output current I _{max} .	≤ 100 mA
Response time	2 ms
Switching frequency	250 Hz
Connection type	Male connector M12, 4-pin
Connection type for daisy chain	Cable with female connector, M12, 4-pin 1.2 m
Circuit protection	A ⁴⁾ C ⁵⁾ D ⁶⁾
Protection class	III
Weight	175 g
Housing material	Plastic, ABS
Enclosure rating	IP67
Shock and vibration resistance	According to IEC 68
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E189383 & NRKH7.E189383
Mode of operation solenoid valve	HIGH to Drive
Connection type solenoid valve	Cable with 9.4 mm DIN valve connection

¹⁾ Limit values.

Safety-related parameters

MTTF _D	771 years
DC _{avg}	0 %

Pneumatic

Connection type solenoid valve	Cable with 9.4 mm DIN valve connection

Classifications

Oldoomodiono	
ECLASS 5.0	27270904
ECLASS 5.1.4	27270904
ECLASS 6.0	27270904
ECLASS 6.2	27270904
ECLASS 7.0	27270904
ECLASS 8.0	27270904

 $^{^{2)}\,\}text{May}$ not exceed or fall below U_{V} tolerances.

³⁾ Without load and valve deenergized.

 $^{^{\}rm 4)}$ A = V_S connections reverse-polarity protected.

⁵⁾ C = interference suppression.

⁶⁾ D = outputs overcurrent and short-circuit protected.

IRT-P211C63 | ZoneControl


MULTITASK PHOTOELECTRIC SENSORS

ECLASS 8.1	27270904
ECLASS 9.0	27270904
ECLASS 10.0	27270904
ECLASS 11.0	27270904
ECLASS 12.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528


Connection diagram



Cd-264




Characteristic curve




Light spot size

Diameter in mm (inch)



Distance in mm (inch)


Sensing range diagram



- Sensing range max.
- ① Sensing range on black, 5 % remission
- ② Sensing range on white, 90% remission factor

Dimensional drawing (Dimensions in mm (inch))

IR, for Motor Driven Rollers (MDR)



- ① LED
- ② Potentiometer
- 3 Fixing hole
- ④ Center of optical axis, sender
- ⑤ Series connection, cable with female connector
- © Connection for motor
- Center of optical axis, receiver
- ® Male connector M12, 4-pin

Recommended accessories

Other models and accessories → www.sick.com/ZoneControl

Duinf description	Type	Part no.
Brief description	Туре	Part no.
Mounting brackets and plates		
Mounting bracket, steel, zinc coated, mounting hardware included	BEF-WK-WTR	2051786
	BEF-WN-RT/IRT	2074621
Plug connectors and cables		
 Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A14- 050VB3XLEAX	2096235
 Connection type head A: Male connector, M12, 4-pin, straight Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² 	STE-1204-G	6009932

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

