

LUTM-UP81162P

LUMINESCENCE SENSORS



Ordering information

Туре	Part no.
LUTM-UP81162P	1067295

Other models and accessories → www.sick.com/LUTM

Illustration may differ







Detailed technical data

Features

Dimensions (W x H x D)	12 mm x 31.5 mm x 21 mm
Sensing distance	≤ 12.5 mm ¹⁾
Housing design	Small
Working range	8 mm 20 mm
Light source	LED, UV ²⁾
Wave length	370 nm
Light emission	Long side
Light spot size	2 mm x 2.5 mm ³⁾
Light spot direction	Vertical
Receiving range	450 nm 750 nm
Adjustment	Teach-in button
Teach-in mode	2-point teach-in static/dynamic
Output function	Light/dark switching ⁴⁾

¹⁾ From leading edge of lens.

Mechanics/electronics

Supply voltage	12 V DC 24 V DC ¹⁾
Ripple	\leq 5 $V_{pp}^{2)}$

 $^{^{1)}}$ Limit values: DC 12 V (-10 %) ... DC 24 V (+20 %). Operation in short-circuit protected network max. 8 A.

 $^{^{2)}}$ Average service life: 100,000 h at T_U = +25 °C.

³⁾ At sensing distance.

 $^{^{4)}}$ L/D switching via teach-in.

 $^{^{2)}\,\}mathrm{May}$ not exceed or fall below U_{V} tolerances.

³⁾ Without load.

 $^{^{4)}}$ With light/dark ratio 1:1.

⁵⁾ Signal transit time with resistive load.

 $^{^{6)}}$ At supply voltage > 24 V, I $_{max}$ = 30 mA. I $_{max}$ is consumption count of all Q $_{n}$.

Current consumption	\leq 50 mA $^{3)}$
Switching frequency	6 kHz ⁴⁾
Response time	80 μs ⁵⁾
Jitter	40 μs
Switching output	PNP
Switching output (voltage)	PNP: HIGH = $U_V \le 2 \text{ V} / \text{LOW approx. 0 V}$
Switching mode	Light/dark switching
Output current I _{max.}	< 100 mA ⁶⁾
Input, teach-in (ET)	PNP Teach: $U = 10 \text{ V} < U_V$ Run: $U < 2 \text{ V}$
Connection type	Cable with M12 male connector, 4-pin, 0.2 m
Protection class	III
Circuit protection	U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression
Enclosure rating	IP67
Weight	70 g
Housing material	Plastic, ABS

 $^{^{1)}}$ Limit values: DC 12 V (-10 %) ... DC 24 V (+20 %) . Operation in short-circuit protected network max. 8 A.

Ambient data

Ambient operating temperature	-10 °C +55 °C
Ambient temperature, storage	-20 °C +75 °C
Shock load	According to IEC 60068
UL File No.	NRKH.E348498 & NRKH7.E348498

Classifications

eCl@ss 5.0	27270908
eCl@ss 5.1.4	27270908
eCl@ss 6.0	27270908
eCl@ss 6.2	27270908
eCl@ss 7.0	27270908
eCl@ss 8.0	27270908
eCl@ss 8.1	27270908
eCl@ss 9.0	27270908
eCl@ss 10.0	27270908
eCl@ss 11.0	27270908
eCl@ss 12.0	27270908
ETIM 5.0	EC001822

 $^{^{2)}}$ May not exceed or fall below U_{V} tolerances.

³⁾ Without load.


⁴⁾ With light/dark ratio 1:1.

⁵⁾ Signal transit time with resistive load.

 $^{^{6)}}$ At supply voltage > 24 V, I_{max} = 30 mA. I_{max} is consumption count of all Q_{n} .

ETIM 6.0	EC001822
ETIM 7.0	EC001822
ETIM 8.0	EC001822
UNSPSC 16.0901	39121528

Dimensional drawing (Dimensions in mm (inch))




For length of cable (L), see technical data

- ① Center of optical axis, sender
- ② Center of optical axis, receiver
- 3 Mounting holes M3
- Display and adjustment elements

Adjustments

Display and adjustment elements



- ① Teach-in button ② LED yellow ③ LED green

Connection diagram

Cd-092

Concept of operation

Setting the switching threshold (dynamic)


1. Position background

the




Press the teach-in button and keep it pressed. LED flashing slowly.


2. Move at least the fluorecent mark and background using the light spot.



Keep the teach-in button > 3 < 30 s pressed.




Release the teach-in button.



Yellow LED will illuminate, when emitted light is on the fluorecent mark.

Sensitivity setting



Switching characteristics

Static teach-in: light/dark setting is defined using teach-in sequence.

Dynamic teach-in: switching output active on fluorecent mark, if background is longer in the field of view during the teach-in. The switching threshold is set automatically between the background and the mark.


Teach-in can also be performed using an external control signal (only dynamic teach-in).

Keylock activation and deactivation: hold down teach-in button > 30 s.

Teach-in failure: yellow LED indicator and the transmitted light of the sensor flashing quickly. For dynamic teach-in with ET signal (5 Hz) via switching output Q.


Setting the switching threshold (static)

1. Position fluorecent mark




Press and hold teach-in button > 1 < 3 s. Yellow LED flashes slowly.

2. Position background



Press and hold teach-in button < 3 s. Yellow LED goes out.

Sensing distance



Recommended accessories

Other models and accessories → www.sick.com/LUTM

	Brief description	Туре	Part no.
Mounting brackets and plates			
	Stainless steel (1.4301)	BEF-WN-G6	2062909
Plug connectors and cables			
	Head A: female connector, M12, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m	YF2A14- 050VB3XLEAX	2096235
	Head A: male connector, M12, 4-pin, straight Cable: unshielded	STE-1204-G	6009932

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

