



# PGT-11-S WLAN

PGT-11-S

PROGRAMMING DEVICES

**SICK**  
Sensor Intelligence.



## Ordering information

| Type          | part no. |
|---------------|----------|
| PGT-11-S WLAN | 1067474  |

Other models and accessories → [www.sick.com/PGT-11-S](http://www.sick.com/PGT-11-S)

## Detailed technical data


### Technical specifications

|                               |   |
|-------------------------------|---|
| <b>Accessory group</b>        | Programming and configuration tools   |
| <b>Description</b>            | SVip® WLAN programming tool for all motor feedback systems  |
| <b>Suitable for</b>           | SRS/SRM50, SKS/SKM36, SFS/SFM60, SES/SEM70, SES/SEM90, TTK50/70, VFS60, CKS36, EKS/EKM36, EFS/EFM50, EES/EEM37, EDS/EDM35       |
| <b>Items supplied</b>         | 1 x PGT-11-S WLAN, 1 x Power supply 100-240 V AC/12V DC, Primary adapter (Europe, UK, USA/Japan, Australia), Ethernet cable 3 m |
| <b>Dimensions (W x H x L)</b> | 108.9 mm x 49.5 mm x 190 mm   |

### Classifications

|                       |          |
|-----------------------|----------|
| <b>ECLASS 5.0</b>     | 27279211 |
| <b>ECLASS 5.1.4</b>   | 27279211 |
| <b>ECLASS 6.0</b>     | 27279211 |
| <b>ECLASS 6.2</b>     | 27279211 |
| <b>ECLASS 7.0</b>     | 27279211 |
| <b>ECLASS 8.0</b>     | 27279211 |
| <b>ECLASS 8.1</b>     | 27279211 |
| <b>ECLASS 9.0</b>     | 19200590 |
| <b>ECLASS 10.0</b>    | 19200590 |
| <b>ECLASS 11.0</b>    | 19200590 |
| <b>ETIM 5.0</b>       | EC001418 |
| <b>ETIM 6.0</b>       | EC001418 |
| <b>ETIM 7.0</b>       | EC001418 |
| <b>ETIM 8.0</b>       | EC001418 |
| <b>UNSPSC 16.0901</b> | 32151707 |

Dimensional drawing



Dimensions in mm (inch)

### Recommended accessories

Other models and accessories → [www.sick.com/PGT-11-S](http://www.sick.com/PGT-11-S)

|   | Brief description   | Type               | part no. |
|---|---|--------------------|----------|
| connectors and cables   |   |                    |          |
|    | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, DUBOX, 8-pin, straight</li> <li><b>Connection type head B:</b> Male connector, M23, 17-pin, straight</li> <li><b>Signal type:</b> HIPERFACE®</li> <li><b>Cable:</b> 1 m, 8-wire</li> <li><b>Description:</b> HIPERFACE®, unshielded</li> </ul>          | DSL-2317-G01MJB1   | 2071326  |
|    | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M23, 12-pin, straight</li> <li><b>Connection type head B:</b> Male connector, M23, 17-pin, straight</li> <li><b>Signal type:</b> HIPERFACE®</li> <li><b>Cable:</b> 1 m, 8-wire</li> <li><b>Description:</b> HIPERFACE®, unshielded</li> </ul>           | DSL-2317-G01MJB2   | 2071328  |
|    | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, JST, 8-pin, straight</li> <li><b>Connection type head B:</b> Male connector, M23, 17-pin, straight</li> <li><b>Signal type:</b> HIPERFACE®</li> <li><b>Cable:</b> 1 m, 8-wire</li> <li><b>Description:</b> HIPERFACE®, unshielded</li> </ul>            | DSL-2317-G01MJB6   | 2071327  |
|    | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M12, 8-pin, straight</li> <li><b>Connection type head B:</b> Male connector, M23, 17-pin, straight</li> <li><b>Signal type:</b> HIPERFACE®</li> <li><b>Cable:</b> 1 m, 8-wire</li> <li><b>Description:</b> HIPERFACE®, unshielded</li> </ul>            | DSL-2317-G01MJC1   | 2071329  |
|    | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, terminal box, 8-pin, straight</li> <li><b>Connection type head B:</b> Male connector, M23, 17-pin, straight</li> <li><b>Signal type:</b> HIPERFACE®</li> <li><b>Cable:</b> 1 m, 8-wire</li> <li><b>Description:</b> HIPERFACE®, unshielded</li> </ul>   | DSL-2317-G01MJC6   | 2071330  |
|  | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, terminal box, 8-pin, straight</li> <li><b>Connection type head B:</b> Male connector, M23, 17-pin, straight</li> <li><b>Signal type:</b> Incremental</li> <li><b>Cable:</b> 1 m, 8-wire</li> <li><b>Description:</b> Incremental, unshielded</li> </ul> | DSL-2317-G01MJC7   | 2071331  |
|  | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, JST, 8-pin, straight</li> <li><b>Connection type head B:</b> Male connector, M23, 17-pin, straight</li> <li><b>Signal type:</b> Incremental</li> <li><b>Cable:</b> 1 m, 8-wire</li> <li><b>Description:</b> Incremental, unshielded</li> </ul>          | DSL-2317-G01MJB7   | 2071332  |
|  | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M12, 4-pin, straight</li> <li><b>Connection type head B:</b> Female connector, JST, 4-pin, straight</li> <li><b>Signal type:</b> HIPERFACE DSL®</li> <li><b>Cable:</b> 1 m</li> <li><b>Description:</b> HIPERFACE DSL®, shielded</li> </ul>             | DSL-1202-G01MA     | 2061361  |
|  | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M12, 8-pin, straight</li> <li><b>Connection type head B:</b> Female connector, M23, 12-pin, straight</li> <li><b>Signal type:</b> HIPERFACE®</li> <li><b>Cable:</b> 1 m, 8-wire</li> <li><b>Description:</b> HIPERFACE®, unshielded</li> </ul>          | YF2AA8-010S01M23BE | 2109107  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

**For us, that is “Sensor Intelligence.”**

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)