

# WLG4SC-3P2232A70

**MINIATURE PHOTOELECTRIC SENSORS** 





Illustration may differ

# Ordering information

Туре	Part no.
WLG4SC-3P2232A70	1067763

The sensor is equipped with a special Smart Task function. Additional information can be found in the "Technical Data." Use of the sensor for pure object detection is limited.

Other models and accessories → www.sick.com/W4





#### Detailed technical data

#### **Features**

Functional principle	Photoelectric retro-reflective sensor
Functional principle detail	Autocollimation
Sensing range max.	0 m 5 m <sup>1)</sup>
Sensing range	0 m 3 m <sup>1)</sup>
Polarisation filters	Yes
Emitted beam	
Light source	PinPoint LED <sup>2)</sup>
Type of light	Visible red light
Light spot size (distance)	Ø 45 mm (1.5 m)
Key LED figures	
Wave length	650 nm
Adjustment	IO-Link, Single teach-in button
Special applications	Detecting transparent objects
Pin 2 configuration	External input, Teach-in input, Sender off input, Detection output, logic output, Device contamination alarm output
AutoAdapt	<b>√</b>

<sup>1)</sup> Reflector PL80A.

 $<sup>^{2)}</sup>$  Average service life: 100,000 h at  $T_{U}$  = +25 °C.

## Safety-related parameters

MTTF <sub>D</sub>	1,222 years
DC <sub>avg</sub>	0 %

#### Communication interface

IO-Link	<b>√</b> , COM2 (38,4 kBaud)
Data transmission rate	COM2 (38,4 kBaud)
Cycle time	2.3 ms
Process data length	16 Bit
Process data structure	Bit 0 = switching signal $Q_{L1}$ Bit 1 = switching signal $Q_{L2}$ Bit 2 15 = measuring value
VendorID	26
DeviceID HEX	0x8000DE
DeviceID DEC	8388830

## Electrical data

	40
Supply voltage U <sub>B</sub>	10 V DC 30 V DC <sup>1)</sup>
Ripple	$<$ 5 $V_{pp}^{2)}$
Current consumption	20 mA <sup>3)</sup>
Protection class	III
Digital output	
Туре	PNP <sup>4)</sup>
Switching mode	Light/dark switching
Output current I <sub>max.</sub>	≤ 100 mA
Repeatability (response time)	150 μs <sup>5)</sup>
Switching frequency	1,000 Hz
Attenuation along light beam	> 8 %
Circuit protection	A <sup>6)</sup> B <sup>7)</sup> C <sup>8)</sup> D <sup>9)</sup>
Response time Q/ on Pin 2	300 μs 450 μs <sup>10) 5)</sup>
Switching frequency Q / to pin 2	1,000 Hz <sup>11)</sup>

 $<sup>^{1)}\,\</sup>mathrm{Limit}$  values when operated in short-circuit protected network: max. 8 A.

 $<sup>^{\</sup>rm 2)}$  May not exceed or fall below  $\rm U_{\rm V}$  tolerances.

<sup>3)</sup> Without load.

 $<sup>^{\</sup>rm 4)}$  Pin 4: This switching output must not be connected to another output.

 $<sup>^{5)}</sup>$  Valid for Q  $\backslash$  on Pin2, if configured with software.

 $<sup>^{6)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

 $<sup>^{7)}</sup>$  B = inputs and output reverse-polarity protected.

<sup>8)</sup> C = interference suppression.

 $<sup>^{9)}</sup>$  D = outputs overcurrent and short-circuit protected.

 $<sup>^{10)}</sup>$  Signal transit time with resistive load.

 $<sup>^{11)}</sup>$  With light / dark ratio 1:1, valid for Q  $\backslash$  on Pin2, if configured with software.

#### Mechanical data

Housing	Rectangular
Design detail	Slim
Dimensions (W x H x D)	12.2 mm x 41.8 mm x 17.3 mm
Connection	Male connector M8, 4-pin
Material	
Housing	Plastic, ABS
Front screen	Plastic, PMMA
Weight	30 g

#### Ambient data

Enclosure rating	IP67 IP66
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E181493 & NRKH7.E181493

## Smart Task

Logic function  Direct WINDOW  Timer function  Deactivated On delay Off delay ON and OFF delay Impulse (one shot)  Inverter  Response time  1) 2)  Repeatability  1) 2)  Time measurement accuracy SIO Direct: SIO Logic: - 0,7 + 0,7 ms ± 0,5 % of time measurement value IOL: - 0.9 + 0.9 ms ± 0.5% of the time measurement  Time measurement accuracy (e.g. accuracy for time measurement value = 1 s)  SIO Direct: SIO Logic: -5,7 + 5,7 ms		
WINDOW  Timer function  Deactivated On delay Off delay ON and OFF delay Impulse (one shot)  Inverter  Response time  1) 2)  Repeatability  1) 2)  Time measurement accuracy  SIO Direct: — SIO Logic: - 0,7 + 0,7 ms ± 0,5 % of time measurement value IOL: - 0.9 + 0.9 ms ± 0.5% of the time measurement  Time measurement accuracy (e.g. accuracy for time measurement value = 1 s )  SIO Direct: — SIO Logic: - 5,7 + 5,7 ms	Smart Task name	Time measurement + debouncing
On delay Off delay ON and OFF delay Impulse (one shot)  Yes  Response time  1) 2)  Time measurement accuracy SIO Direct: — SIO Logic: - 0,7 + 0,7 ms ± 0,5 % of time measurement value IOL: - 0.9 + 0.9 ms ± 0.5% of the time measurement Time measurement accuracy (e.g. accuracy for time measurement value = 1 s)  On delay Off delay ON and OFF delay Impulse (one shot)  SIO Direct: — SIO Direct: — SIO Direct: — SIO Logic: - 5,7 + 5,7 ms	Logic function	
Response time  1) 2)  Time measurement accuracy  SIO Direct: SIO Logic: - 0,7 + 0,7 ms ± 0,5 % of time measurement value IOL: - 0.9 + 0.9 ms ± 0.5% of the time measurement  Time measurement accuracy (e.g. accuracy for time measurement value = 1 s )  SIO Direct: SIO Direct: SIO Direct: SIO Logic: - 5,7 + 5,7 ms	Timer function	On delay Off delay ON and OFF delay
Repeatability  1) 2)  Time measurement accuracy  SIO Direct: — SIO Logic: - 0,7 + 0,7 ms ± 0,5 % of time measurement value IOL: - 0.9 + 0.9 ms ± 0.5% of the time measurement  Time measurement accuracy (e.g. accuracy for time measurement value = 1 s )  SIO Direct: — SIO Logic: - 5,7 + 5,7 ms	Inverter	Yes
Time measurement accuracy  SIO Direct: SIO Logic: - 0,7 + 0,7 ms ± 0,5 % of time measurement value IOL: - 0.9 + 0.9 ms ± 0.5% of the time measurement  Time measurement accuracy (e.g. accuracy for time measurement value = 1 s )  SIO Direct: SIO Dir	Response time	1) 2)
SIO Logic: $-0.7 + 0.7 \text{ ms} \pm 0.5\%$ of time measurement value IOL: $-0.9 + 0.9 \text{ ms} \pm 0.5\%$ of the time measurement  Time measurement accuracy (e.g. accuracy for time measurement value = 1 s )  SIO Direct: SIO Logic: $-5.7 + 5.7 \text{ ms}$	Repeatability	1) 2)
for time measurement value = 1 s ) SIO Logic: - 5,7 + 5,7 ms	Time measurement accuracy	SIO Logic: - 0,7 + 0,7 ms $\pm$ 0,5 % of time measurement value
IUL: - 5,9 + 5,9 IIIS	, , , , , , , , , , , , , , , , , , ,	
Resolution time measuring value 1 ms	Resolution time measuring value	1 ms
Min. Time between two process events (switches)  SIO Direct: SIO Logic: 450 μs IOL: 500 μs	•	SIO Logic: 450 μs
Debounce time max.  SIO Direct: — SIO Logic: 30.000 ms IOL: 30.000 ms	Debounce time max.	SIO Logic: 30.000 ms
Switching signal	Switching signal	
Switching signal Q <sub>L1</sub> Output type (dependant on the adjusted threshold)	Switching signal Q <sub>L1</sub>	Output type (dependant on the adjusted threshold)
Switching signal Q <sub>L2</sub> Output type (dependant on the adjusted threshold)	Switching signal Q <sub>L2</sub>	Output type (dependant on the adjusted threshold)
Measuring value Time measurement value	Measuring value	Time measurement value

<sup>1)</sup> SIO Logic: Sensor operation in standard I/O mode without IO-Link communication. Sensor-internal logic or timing parameters plus Automation Functions used.

 $<sup>^{2)}</sup>$  IOL: Sensor operation with full IO-Link communication and usage of logic, timing and Automation Function parameters.

# Diagnosis

Device status	Yes
Quality of teach	Yes
Quality of run	Yes, Contamination display

## Classifications

ECLASS 5.0	27270902
ECLASS 5.1.4	27270902
ECLASS 6.0	27270902
ECLASS 6.2	27270902
ECLASS 7.0	27270902
ECLASS 8.0	27270902
ECLASS 8.1	27270902
ECLASS 9.0	27270902
ECLASS 10.0	27270902
ECLASS 11.0	27270902
ECLASS 12.0	27270902
ETIM 5.0	EC002717
ETIM 6.0	EC002717
ETIM 7.0	EC002717
ETIM 8.0	EC002717
UNSPSC 16.0901	39121528

# Connection diagram

## Cd-367




# MINIATURE PHOTOELECTRIC SENSORS

#### Characteristic curve


WL4S-3, WLG4S-3, 5 m

#### Operating reserve



- ① Reflector PL80A
- ② Reflector PL40A
- 3 Reflector PL20A
- ④ PL10F reflector
- ⑤ Reflector P250 CHEM
- © Reflective tape REF-IRF-56

# Light spot size



# Sensing range diagram


WL4S-3, WLG4S-3, 5 m

1	0		3.0		5.0
2	0	2.0		4.0	
3	0	1.3 2	.2		
4	0 1	1.6			
(5)	0 0.5 0.8				
(	) :	1 2	2 3	3 4	1 5
				Distance	e in m (feet)

- Sensing range
- Sensing range max.
- ① Reflector PL80A
- ② Reflector PL40A
- 3 Reflector PL20A
- ④ PL10F reflector
- ⑤ Reflective tape REF-IRF-56

## Dimensional drawing (Dimensions in mm (inch))

WL4S-3, WLG4S-3, single teach-in button





- ① Center of optical axis
- ② Threaded mounting hole M3
- 3 Connection
- 4 LED indicator green: Supply voltage active
- ⑤ Orange LED indicator: status of received light beam
- Teach-in button

# MINIATURE PHOTOELECTRIC SENSORS

#### Recommended accessories

Other models and accessories → www.sick.com/W4

	Brief description	Туре	Part no.				
Mounting brackets and plates							
	Mounting bracket for wall mounting, Stainless steel 1.4571, mounting hardware included	BEF-W4-A	2051628				
	Universal mounting bracket for reflectors, steel, zinc coated	BEF-WN-REFX	2064574				
Plug connecto	Plug connectors and cables						
	<ul> <li>Connection type head A: Male connector, M8, 4-pin, straight</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: 0.14 mm² 0.5 mm²</li> </ul>	STE-0804-G	6037323				
Reflectors							
	Fine triple reflector, screw connection, suitable for laser sensors, 20 mm x 32 mm, PM-MA/ABS, Screw-on, 2 hole mounting	PL10F	5311210				
Others							
	<ul> <li>Connection type head A: Female connector, M8, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF8U14- 050VA3XLEAX	2095889				

## Recommended services

Additional services → www.sick.com/W4

	Туре	Part no.
Function Block Factory		
<ul> <li>Description: The Function Block Factory supports common programmable logic controllers (PLCs) from various manufacturers, such as Siemens, Beckhoff, Rockwell Automation and B&amp;R. More information on the FBF can be found <a href="https://fbf.cloud.sick.com" target="_blank"> here</a>.</li> <li>Note: You can configure your function block at <a href="https://fbf.cloud.sick.com" target="_blank"> Function Block Factory.</a> As a login please use your SICK ID.</li> </ul>	Function Block Factory	On request

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

