

# STR1-SAFUOAC5

STR1

**NON-CONTACT SAFETY SWITCHES** 





#### Ordering information

Туре	Part no.
STR1-SAFU0AC5	1069575

Consists of sensor (1073228) and actuator (1073221)

Other models and accessories → www.sick.com/STR1



#### Detailed technical data

#### **Features**

System part	Sensor with actuator
Sensor principle	RFID
Number of safe outputs	2
Auxiliary contact (AUX)	1 (Switching behavior complementary to OSSDs)
Safe switch on distance S <sub>ao</sub>	14 mm (-10 +70 °C) <sup>1)</sup> 10 mm (-3010 °C) <sup>1)</sup>
Safe switch off distance $\mathbf{S}_{\mathrm{ar}}$	28 mm <sup>1)</sup>
Active sensor surfaces	3
Active sensor surface	Top, sides (left, right) <sup>2)</sup>
Actuation directions	5
Coding	Uniquely coded

<sup>1)</sup> Values apply for the frontal alignment of the sensor to the actuator. A detailed display of the alignment options and values can be found in the operating instructions.

#### Safety-related parameters

, ,	
Safety integrity level	SIL 3 (IEC 61508)
Category	Category 4 (EN ISO 13849)
Performance level	PL e (EN ISO 13849)
$\ensuremath{PFH_D}$ (mean probability of a dangerous failure per hour)	5,21 x 10 <sup>-9</sup>
T <sub>M</sub> (mission time)	20 years (EN ISO 13849)
Туре	Type 4 (EN ISO 14119)
Actuator coding level	High coding level (EN ISO 14119)
Safe state in the event of a fault	At least one safety-related semiconductor output (OSSD) is in the OFF state.

#### **Functions**

Safe series connection	With Flexi Loop (with diagnostics)
------------------------	------------------------------------

 $<sup>^{2)}</sup>$  For details see operating instructions.

#### Interfaces

Connection type	Cable with plug M12, 5-pin
Length of cable	0.2 m
Long connecting cable	≤ 200 m
Cable diameter	5.5 mm
Conductor cross section	0.12 mm <sup>2</sup>
Bend radius (with fixed installation)	> 8 x cable diameter
Bend radius (with moving cable)	> 12 x cable diameter
Cable material	PVC
Conductor material	Copper
Coupling nut material	Zinc die-cast, nickel-plated
Display elements	LEDs
Diagnostics indicator	<b>√</b>
Status display	✓

#### Electrical data

Protection class	III (IEC 61140)
Classification according to cULus	Class 2
Supply voltage V <sub>s</sub>	24 V DC (19.2 V DC 28.8 V DC)
Power consumption	50 mA
Type of output	Self-monitoring semiconductor outputs (OSSDs)
Output current	≤ 100 mA
Response time	40 ms <sup>1)</sup>
Release time	100 ms <sup>1) 2)</sup>
Risk time	80 ms <sup>1) 3)</sup>
Switch-on time	2.5 s <sup>4)</sup>

<sup>1)</sup> In a safe series connection, each downstream safety switch increases the system response time. More response times can be found in the operating instructions.

#### Mechanical data

Dimensions (W x H x D)	40 mm x 18 mm x 26 mm
Weight	68 g
Housing material	VISTAL®

#### Ambient data

Enclosure rating	IP67, IP69K (EN 60529, ISO 20653)
Ambient operating temperature	−30 °C +70 °C <sup>1)</sup>
Storage temperature	-30 °C +70 °C
Vibration resistance	10 Hz 55 Hz, 1 mm (IEC 60068-2-6)

<sup>1)</sup> Only applies for safety switches whose serial numbers begin with number series 1825\*\*\*\* or higher. For safety switches whose serial numbers deviate from this, an ambient operating temperature of-10 °C ... +70 °C applies.

 $<sup>^{2)}</sup>$  Response time on approach to the enable zone.

<sup>3)</sup> Detection time for internal oder external faults (e.g., short-circuit or cross-circuit of output signal switching devices). Follow the detailed information in the operating instructions.

<sup>&</sup>lt;sup>4)</sup> The time specified applies to one sensor after the supply voltage has been applied to the safety switch. In a safe series connection, 0.1¬s must be added for each sensor. An additional 0.5¬s per taught-in actuator must be added for uniquely coded and permanently coded sensors.

The serial number is displayed on the safety switch over the data matrix code.

# STR1-SAFU0AC5 | STR1

#### NON-CONTACT SAFETY SWITCHES

Shock resistance	30 g, 11 ms (IEC 60068-2-27)
EMC	EN IEC 61326-3-1, EN IEC 60947-5-2, EN IEC 60947-5-3, EN 300330 V2.1.1

<sup>1)</sup> Only applies for safety switches whose serial numbers begin with number series 1825\*\*\*\* or higher. For safety switches whose serial numbers deviate from this, an ambient operating temperature of-10 °C ... +70 °C applies.


The serial number is displayed on the safety switch over the data matrix code.

#### Classifications


ECLASS 5.0	27272403
ECLASS 5.1.4	27272403
ECLASS 6.0	27272403
ECLASS 6.2	27272403
ECLASS 7.0	27272403
ECLASS 8.0	27272403
ECLASS 8.1	27272403
ECLASS 9.0	27272403
ECLASS 10.0	27272403
ECLASS 11.0	27272403
ECLASS 12.0	27274601
ETIM 5.0	EC001829
ETIM 6.0	EC001829
ETIM 7.0	EC001829
ETIM 8.0	EC001829
UNSPSC 16.0901	39122205

#### Dimensional drawing (Dimensions in mm (inch))

Sensor with cable and male connector




"Flat" actuator




#### Response range

"Flat"/"Mini" actuator, active side sensor surface



Assured switch on distance Sao 9 mm. Observe border areas for parallel approach: a minimum distance of 4 mm (typical) must be upheld when the actuator moves laterally to the sensor surface. This prevents early triggering due to the side preparation areas. "Flat"/"Mini" actuator, active front sensor surface




Assured switch on distance Sao 14 mm. Observe border areas for parallel approach: a minimum distance of 10 mm (typical) must be upheld when the actuator moves laterally to the sensor surface. This prevents early triggering due to the side preparation areas.

#### Pin assignment



1	Voltage supply 24 V DC
2	OSSD 1
3	Voltage supply 0 V DC
4	OSSD 2
5	Aux output (not safe)


#### Connection single sensor



- ① Safe evaluation unit
- ② Connecting cable with M12 female connector, 5-pin and flying leads (e.g., YF2A15-xxxVB5XLEAX)
- ③ STR1 RFID safety switch (e.g., STR1-SAxxOAC5)

#### Series connection


Series connection with Flexi Loop (with diagnostics)




- ① Flexi Soft safety controller
- ② Connecting cable with M12 female connector, 5-pin and flying leads (e.g., YF2A15-xxxVB5XLEAX)
- ③ FLN-OSSD1000105 Flexi Loop node
- 4 FLN-EMSS1100108 Flexi Loop node
- (a.g., YF2A15-xxxUB5M2A15)
- © Connection cable with 8-pin, M12 male connector and 8-pin, M12 female connector (e.g., YF2A18-xxxUA5M2A18)
- ③ STR1 RFID safety switch (e.g., STR1-SAxxOAC5)
- $\hbox{ @ Safety locking device (e.g., i10-x0454 or i110-x0454)} \\$
- FLT-TERM00001 Flexi Loop terminating element

#### Connection diagram

STR1 RFID safety switch to RLY3-OSSD2 safety relay



Parallel connection of two STR1 RFID safety switches to a Flexi Classic safety controller



#### Recommended accessories

Other models and accessories → www.sick.com/STR1

	Brief description	Туре	Part no.		
Nuts and scre	Nuts and screws				
	10 pieces	Safety screws M4 x 14	5333570		
Others					
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 5-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A15-020VB5XLEAX	2096239		
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 5-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A15-050VB5XLEAX	2096240		
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 10 m, 5-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A15-100VB5XLEAX	2096241		
Safety switchi	Safety switching amplifier				
	<ul> <li>Applications: Evaluation unit</li> <li>Compatible sensor types: Safety sensors with OSSDs</li> <li>Connection type: Front connector with spring terminals</li> <li>Restart interlock: yes</li> <li>External device monitoring (EDM): Integrated</li> <li>Outputs: 2 enabling current paths (safe), 2 application diagnostic outputs (not safe), 1 test pulse output (not safe)</li> <li>Housing width: 18 mm</li> </ul>	RLY3-0SSD200	1085344		

### SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

