

# IQ40-40NNSKKOS

**INDUCTIVE PROXIMITY SENSORS** 





#### Ordering information

Туре	Part no.
IQ40-40NNSKK0S	1071855

Other models and accessories → www.sick.com/IQG



#### Detailed technical data

#### **Features**

Housing	Rectangular
Housing	Standard design
Dimensions (W x H x D)	40 mm x 40 mm x 118 mm
Sensing range S <sub>n</sub>	40 mm
Safe sensing range S <sub>a</sub>	32.4 mm
Installation type	Non-flush
Switching frequency	100 Hz
Connection type	Cable gland
Switching output	NPN
Output function	NO
Electrical wiring	DC 3-wire
Enclosure rating	IP67, IP68, IP69K
Special applications	Difficult application conditions

#### Mechanics/electronics

Supply voltage	10 V DC 30 V DC
Ripple	≤ 10 V <sub>pp</sub> <sup>1)</sup>
Voltage drop	≤ 2 V
Time delay before availability	≤ 50 ms
Hysteresis	3 % 15 % <sup>2)</sup>
Reproducibility	≤ 6 %
Temperature drift (of S <sub>r</sub> )	± 10 %
Continuous current I <sub>a</sub>	≤ 200 mA

<sup>&</sup>lt;sup>1)</sup> Of Ub.

 $<sup>^{2)}</sup>$  Of  $S_{r}$ .

<sup>3)</sup> Reference voltage: 50 V DC.

No load current	12.5 mA
Cable gland clamping area	M20 1.5
Wire size	≤ 2.5 mm²
Short-circuit protection	✓
Reverse polarity protection	✓
Power-up pulse protection	✓
Shock and vibration resistance	30 g, 11 ms / 10 55 Hz, 1 mm
Ambient operating temperature	-25 °C +85 °C
Ambient temperature, storage	-40 °C +85 °C
Housing material	Plastic, PA 66
Sensing face material	Plastic, PA 66
Tightening torque, max.	1.8 Nm
Protection class	II <sup>3)</sup>
UL File No.	E348498

<sup>1)</sup> Of Ub.

#### Safety-related parameters

MTTF <sub>D</sub>	1,125 years
DC <sub>avg</sub>	0 %
T <sub>M</sub> (mission time)	20 years

#### **Reduction factors**

Note	The values are reference values which may vary
Stainless steel (V2A, 304)	Approx. 0.8
Aluminum (AI)	Approx. 0.34
Copper (Cu)	Approx. 0.27
Brass (Br)	Approx. 0.38

#### Installation note

Remark	Associated graphic see "Installation"
Α	42 mm
В	150 mm
c	40 mm
D	120 mm
E	40 mm
F	150 mm

#### Classifications

ECLASS 5.0	27270101
ECLASS 5.1.4	27270101
ECLASS 6.0	27270101
ECLASS 6.2	27270101


<sup>&</sup>lt;sup>2)</sup> Of S<sub>r</sub>.

<sup>3)</sup> Reference voltage: 50 V DC.

#### INDUCTIVE PROXIMITY SENSORS


ECLASS 7.0	27270101
ECLASS 8.0	27270101
ECLASS 8.1	27270101
ECLASS 9.0	27270101
ECLASS 10.0	27270101
ECLASS 11.0	27270101
ECLASS 12.0	27274001
ETIM 5.0	EC002714
ETIM 6.0	EC002714
ETIM 7.0	EC002714
ETIM 8.0	EC002714
UNSPSC 16.0901	39122230

#### Installation note




#### Connection diagram

#### Cd-342




#### Response diagram



#### Dimensional drawing (Dimensions in mm (inch))

IQG Standard, cable gland



- ① LED output state, yellow
- ② Sensing face
- 3 Operational status LED, green

#### Recommended accessories

Other models and accessories → www.sick.com/IQG

Brief description		Туре	Part no.
Plug connectors and cables			
<ul> <li>Connection type head A: Fema</li> <li>Connection type head B: Flying</li> <li>Signal type: Sensor/actuator of Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator of Application: Zones with chemic</li> </ul>	ole, unshielded	YF2A14- 050VB3XLEAX	2096235

## IQ40-40NNSKKOS | IQG INDUCTIVE PROXIMITY SENSORS

	Brief description	Туре	Part no.
***	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YG2A14- 050VB3XLEAX	2095897
	Connection type head A: Female connector, M12, 4-pin, straight     Description: Unshielded, Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: -     Connection systems: Screw-type terminals     Permitted cross-section: ≤ 0.75 mm²	DOS-1204-G	6007302
	<ul> <li>Connection type head A: Male connector, M12, 4-pin, straight</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm²</li> </ul>	STE-1204-G	6009932

#### SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

### **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

