

# IQ40-40NPSKCOK

**INDUCTIVE PROXIMITY SENSORS** 



## IQ40-40NPSKCOK | IQG

INDUCTIVE PROXIMITY SENSORS



#### Ordering information

Туре	Part no.
IQ40-40NPSKCOK	1071850

Included in delivery: BEF-KH-IQ40 (1)

Other models and accessories → www.sick.com/IQG



## Detailed technical data

#### Features

Housing	Rectangular
Housing	Short-body
Dimensions (W x H x D)	40 mm x 40 mm x 66 mm
Sensing range S <sub>n</sub>	40 mm
Safe sensing range S <sub>a</sub>	32.4 mm
Installation type	Non-flush
Switching frequency	100 Hz
Connection type	Male connector M12, 4-pin
Switching output	PNP
Output function	NO
Electrical wiring	DC 3-wire
Enclosure rating	IP67, IP68, IP69K
Special applications	Difficult application conditions
Items supplied	Push-lock mounting system (1x)

#### Mechanics/electronics

Supply voltage	10 V DC 30 V DC
Ripple	$\leq$ 10 V <sub>pp</sub> <sup>1)</sup>
Voltage drop	≤ 2 V
Time delay before availability	≤ 50 ms
Hysteresis	3 % 15 % <sup>2)</sup>
Reproducibility	≤ 6 %
Temperature drift (of S <sub>r</sub> )	± 10 %

<sup>1)</sup> Of Ub.

 $^{2)}$  Of  $\mathrm{S}_{\mathrm{r}}.$ 

<sup>3)</sup> Reference voltage: 50 V DC.

# IQ40-40NPSKCOK | IQG

INDUCTIVE PROXIMITY SENSORS

Continuous current l <sub>a</sub>	≤ 200 mA
No load current	12.5 mA
Short-circuit protection	✓
Reverse polarity protection	✓
Power-up pulse protection	✓
Shock and vibration resistance	30 g, 11 ms / 10 55 Hz, 1 mm
Ambient operating temperature	-25 °C +85 °C
Ambient temperature, storage	-40 °C +85 °C
Housing material	Plastic, PA 66
Sensing face material	Plastic, PA 66
Tightening torque, max.	1.8 Nm
Protection class	II <sup>3)</sup>
UL File No.	E348498

<sup>&</sup>lt;sup>1)</sup> Of Ub.

## Safety-related parameters

MTTF <sub>D</sub>	1,125 years
DC <sub>avg</sub>	0 %
T <sub>M</sub> (mission time)	20 years
Reduction factors	
Note	The values are reference values which may vary
Stainless steel (V2A, 304)	Approx. 0.8
Aluminum (Al)	Approx. 0.34
Copper (Cu)	Approx. 0.27
Brass (Br)	Approx. 0.38

#### Installation note

Remark	Associated graphic see "Installation"
A	42 mm
В	150 mm
c	40 mm
D	120 mm
E	40 mm
F	150 mm

#### Classifications

ECLASS 5.0	27270101
ECLASS 5.1.4	27270101
ECLASS 6.0	27270101
ECLASS 6.2	27270101
ECLASS 7.0	27270101

 $<sup>^{2)}</sup>$  Of S<sub>r</sub>.


<sup>&</sup>lt;sup>3)</sup> Reference voltage: 50 V DC.

## IQ40-40NPSKCOK | IQG

INDUCTIVE PROXIMITY SENSORS


ECLASS 8.0	27270101
ECLASS 8.1	27270101
ECLASS 9.0	27270101
ECLASS 10.0	27270101
ECLASS 11.0	27270101
ECLASS 12.0	27274001
ETIM 5.0	EC002714
ETIM 6.0	EC002714
ETIM 7.0	EC002714
ETIM 8.0	EC002714
UNSPSC 16.0901	39122230

#### Installation note




## Connection diagram

Cd-011




#### Response diagram



#### Dimensional drawing (Dimensions in mm (inch))

IQG Short-body housing



① LED output state, yellow

② Sensing face

③ Operational status LED, green

INDUCTIVE PROXIMITY SENSORS

#### **Recommended accessories**

Other models and accessories -> www.sick.com/IQG

	Brief description	Туре	Part no.
Plug connectors and cables			
<b>N</b>	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A14- 050VB3XLEAX	2096235
*	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YG2A14- 050VB3XLEAX	2095897
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight</li> <li>Description: Unshielded, Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: -</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm<sup>2</sup></li> </ul>	DOS-1204-G	6007302
	<ul> <li>Connection type head A: Male connector, M12, 4-pin, straight</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm<sup>2</sup></li> </ul>	STE-1204-G	6009932

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

