



SICK Sensor Intelligence.

3D MACHINE VISION

3D MACHINE VISION



Ordering information

| Туре | Part no. |
|---------------|----------|
| V3T12S-MR32A7 | 1072923 |

Other models and accessories

www.sick.com/TriSpector1000



CE E EAE

| Features | |
|-------------------------------------|--|
| Task | Position determination Presence inspection Quality check Measuring, 3D |
| Technology | 3D triangulation |
| Product category | Configurable |
| Toolkit | Shape Area detection Blob Finder Volume Find plane Fixed plane |
| Working distance | 141 mm 541 mm |
| Example field of view | 270 mm x 100 mm |
| Illumination | Integrated |
| Illumination color | Red, laser, Visible, 660 nm, ± 7 nm |
| Laser class | 2 (EN 60825-1:2014+A11:2021; IEC 60825-1:2014, Complies with the FDA performance re- quirements for laser products except for conformance with IEC 60825-1 Ed.3., as described in Laser Notice 56 dated May 8, 2019.) |
| Factory calibrated | 1 |
| Width at minimum operating distance | 90 mm |
| Width at maximum operating distance | 330 mm |
| Maximum height range | 400 mm |
| Imaging angle | 65° |
| Offline support | Emulator |
| Mechanics/electronics | |
| Connection type | M12, 12-pin male connector, A-coded (voltage supply, I/O) M12, 8-pin female connector, X-coded (Gigabit Ethernet) M12, 8-pin female connector, A-coded (encoder) |
| Connector material | Nickel plated brass |
| Supply voltage | 24 V DC, ± 20 % |
| Ripple | < 5 V _{pp} |
| Power consumption | ≤ 11 W |
| Current consumption | < 400 mA, without output load |
| Enclosure rating | IP67 |

3D MACHINE VISION

| Protection class | 111 |
|---|---------------------------------------|
| Housing material | Anodized aluminum |
| Window material | Glass |
| Weight | 1.3 kg |
| Dimensions (L x W x H) | 217 mm x 62 mm x 84 mm |
| Performance | |
| Scan/frame rate | 5,000 3D profiles/s |
| Maximum number of profiles | 2,500 Per image |
| Data points/profile | 1,536 |
| Height resolution | 40 μm 280 μm |
| 3D profile resolution | 0.215 mm/px |
| Interfaces | |
| Ethernet | ✓, TCP/IP |
| Data transmission rate | 1,000 Mbit/s |
| Serial | ✓, RS-232, RS-422 |
| Function | Encoder (RS-422 / DBS36E-BBCP02048) |
| Data transmission rate | Maximum encoder frequency: 300 MHz |
| Incremental | ✓, TTL |
| Configuration software | SOPAS ET |
| Digital input | 3 (non-isolated) |
| Digital output | 4 (non-isolated) |
| Encoder interface | RS-422 / TTL (DBS36E-BBCP02048) |
| Maximum encoder frequency | 300 kHz |
| Ambient data | |
| Electromagnetic compatibility (EMC) | EN 61000-6-2:2005 / EN 61000-6-3:2007 |
| Shock load | 15 g / 6 ms (EN 60068-2-27) |
| Vibration load | 5 g, 10 Hz 150 Hz (EN 60068-2-6) |
| Ambient operating temperature | 0 °C +50 °C ¹⁾ |
| Storage temperature | -20 °C +70 °C ¹⁾ |
| ¹⁾ Permissible relative air humidity: 0 % 90 % (non-condensing). | |
| Classifications | |
| ECLASS 5.0 | 27310205 |
| ECLASS 5.1.4 | 27310205 |
| ECLASS 6.0 | 27310205 |

27310205

27310205

27310205

27310205

27310205

27310205

ECLASS 6.2

ECLASS 7.0

ECLASS 8.0

ECLASS 8.1


ECLASS 9.0

ECLASS 10.0

3D MACHINE VISION

| ECLASS 11.0 | 27310205 |
|----------------|----------|
| ECLASS 12.0 | 27310205 |
| ETIM 5.0 | EC001820 |
| ETIM 6.0 | EC001820 |
| ETIM 7.0 | EC001820 |
| ETIM 8.0 | EC001820 |
| UNSPSC 16.0901 | 43211731 |


Dimensional drawing (Dimensions in mm (inch))



- ① Connector Encoder (thread inside)
- ② Connector Gigabit Ethernet (Gig E)
- ③ Connector Power I/O (thread inside)
- ④ LED; On
- ⑤ LED; State
- 6 LED; Link/Data
- ② LED; Result
- ⑧ LED; Laser
- ③ Fastening threads (M5 x 8.5 mm length)
- Optical receiver (center)
- (1) Optical sender (center)
- 12 Micro SD memory card

Field of view

Typical field of view




Max. height range

Width at max. working distance

4 MACHINE VISION | SICK

TriSpector1030 Typ. field of view in mm (inch)



Recommended accessories

Other models and accessories → www.sick.com/TriSpector1000

| | Brief description | Туре | Part no. |
|------------------------------|--|------------------------|----------|
| Mounting brackets and plates | | | |
| | Mounting bracket set consisting of mounting bracket, cooling plate, includes angle dis- play for setting the tilt angle | Mounting bracket | 2076735 |
| Plug connecto | ors and cables | | |
| K | Connection type head A: Male connector, M12, 5-pin, straight Connection type head B: Flying leads Cable: 2 m Description: Shielded Connection systems: Flying leads | Connecting cable | 6024860 |
| | Connection type head A: Male connector, M12, 8-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 8-wire, PVC Description: Sensor/actuator cable, shielded Application: Zones with chemicals | YM2A28- 050VA6XLEAX | 2096233 |
| R. R. | Connection type head A: Female connector, M12, 8-pin, straight, A-coded Connection type head B: Male connector, M12, 8-pin, straight, A-coded Signal type: Sensor/actuator cable Cable: 2 m, 8-wire, PUR, halogen-free Description: Sensor/actuator cable, shielded Application: Zones with oils and lubricants, Drag chain operation | YF2A28- 020UA6M2A28 | 2096105 |
| | Connection type head A: Female connector, M12, 12-pin, straight Connection type head B: Male connector, M12, 5-pin, straight Signal type: Power Cable: 0.25 m Description: Power, Cable for connecting a TriSpector to power supply unit 2079609 | YF2A6B- C25XXXM2A15 | 2079766 |
| | Connection type head A: Female connector, M12, 12-pin, straight Connection type head B: Male connector, M12, 17-pin, straight Signal type: Power, digital I/Os, serial Cable: 0.25 m Description: Power, digital I/Os, serial, shielded, cable to connect TriSpector to CDF600-2, needs to be used in combination with further connection cable (e.g. part number 2055419) | YF2AAB- C25S01M2AAD | 2086398 |

3D MACHINE VISION

| | Brief description | Туре | Part no. |
|--------|--|------------------------|----------|
| 11 | Connection type head A: Male connector, M12, 8-pin, straight, X-coded Connection type head B: Male connector, RJ45, 8-pin, straight Signal type: Ethernet, Gigabit Ethernet Cable: 2 m, 8-wire, PUR, halogen-free Description: Ethernet, Gigabit Ethernet, shielded Application: Zones with oils and lubricants | YM2X18- 020EG1MRJA8 | 2106258 |
| Others | | | |
| | 24 V DC power supply unit, 5-pin, M12, for TriSpector in combination with connecting cable 2079766 | Power supply unit | 2079609 |

Recommended services

Additional services -> www.sick.com/TriSpector1000

| | Туре | Part no. |
|---|--|----------|
| Commissioning | | |
| Product area: 3D machine vision Range of services: Inspection of connection, fine adjustment, optimization of parameters of SICK product as well as tests, set-up of previously defined functions of image settings, task configuration, result settings, interface settings, as well as verification tests Travel expenses: The prices do not include travel costs such as hotel, flight, travel time and expenses. Duration: Additional work will be invoiced separately | TriSpector1000 commissioning | 1612239 |
| Maintenance | | |
| Product area: 3D machine vision Range of services: Inspection, analysis and restoring of defined functions, inspection and adaptation of previously defined functions of image settings, task configuration, result settings, and interface settings Duration: Additional work will be invoiced separately Travel expenses: The prices do not include travel costs such as hotel, flight, travel time and expenses. | TriSpector1000 maintenance | 1612243 |
| Extended warranty | | |
| Product area: Identification solutions, machine vision, Detection and ranging solutions, safety camera sensors, Safety laser scanners, Safety radar sensors Range of services: The services correspond to the scope of the statutory manufacturer warranty (SICK general terms of delivery). Duration: Five-year warranty from delivery date. | Extended warranty for a total of five years from delivery date | 1680671 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

