

# WTT12L-B1548

PowerProx

**MULTITASK PHOTOELECTRIC SENSORS** 





#### Ordering information

Туре	Part no.
WTT12L-B1548	1072624

Other models and accessories → www.sick.com/PowerProx

Illustration may differ



#### Detailed technical data

#### **Features**

Functional principle	Photoelectric proximity sensor
Functional principle detail	Background suppression, Optical time-of-flight
Dimensions (W x H x D)	20 mm x 49.6 mm x 44.2 mm
Housing design (light emission)	Rectangular
Sensing range max.	50 mm 1,800 mm <sup>1)</sup>
Sensing range	100 mm 1,800 mm <sup>2) 3)</sup>
Type of light	Visible red light
Light source	Laser <sup>4)</sup>
Light spot size (distance)	Ø 12 mm (1,800 mm)
Wave length	658 nm
Laser class	1 (IEC 60825-1 / CDRH 21 CFR 1040.10 & 1040.11)
Adjustment	Potentiometer, 4 turns (2 x)

 $<sup>^{1)}</sup>$  Object with 6 ... 90% remission (based on standard white, DIN 5033).

<sup>&</sup>lt;sup>2)</sup> Adjustable.

 $<sup>^{\</sup>rm 3)}$  Object with 90% remission (based on standard white, DIN 5033).

<sup>&</sup>lt;sup>4)</sup> Average service life: 100,000 h at  $T_U$  = +25 °C.

#### Mechanics/electronics

Supply voltage $\mathbf{U}_{\mathrm{B}}$	10 V DC 30 V DC <sup>1)</sup>
Ripple	< 5 V <sub>pp</sub> <sup>2)</sup>
Current consumption	70 mA <sup>3)</sup>
Switching output	Push-pull: PNP/NPN 4)
Number of switching outputs	2 (Q <sub>1</sub> , Q <sub>2</sub> ) <sup>4)</sup>
Switching mode	Light switching <sup>4)</sup>
Output current I <sub>max.</sub>	≤ 100 mA
Response time	≤ 16.7 ms <sup>5)</sup>
Switching frequency	30 Hz <sup>6)</sup>
Analog output	-
Input	L/D = light/dark switching
Connection type	Cable, 5-wire, 2 m <sup>7)</sup>
Cable material	PVC
Conductor cross section	0.14 mm <sup>2</sup>
Circuit protection	A <sup>8)</sup> B <sup>9)</sup> C <sup>10)</sup>
Protection class	III
Weight	111 g
Housing material	Plastic, VISTAL®
Optics material	Plastic, PMMA
Enclosure rating	IP67
Ambient operating temperature	-35 °C +50 °C <sup>11)</sup>
Ambient temperature, storage	-40 °C +70 °C
Warm-up time	< 15 min <sup>12)</sup>
Initialization time	< 300 ms
UL File No.	NRKH.E181493

 $<sup>^{1)}</sup>$  Limit values. Operated in short-circuit protected network: max. 8 A.

#### Safety-related parameters

MTTF <sub>D</sub>	133 years
<b>DC</b> <sub>avg</sub>	0 %

 $<sup>^{2)}\,\</sup>text{May}$  not exceed or fall below  $\text{U}_{\text{V}}$  tolerances.

 $<sup>^{3)}</sup>$  Without load. At  $V_S = 24 \text{ V}$ .

 $<sup>^{4)}</sup>$  Q1, Q2 = 2 switching thresholds, light switching.

 $<sup>^{5)}</sup>$  Signal transit time with resistive load.

<sup>6)</sup> With light/dark ratio 1:1.

<sup>7)</sup> Do not bend below 0 °C.

 $<sup>^{8)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

 $<sup>^{9)}</sup>$  B = inputs and output reverse-polarity protected.


 $<sup>^{10)}</sup>$  C = interference suppression.

 $<sup>^{11)}</sup>$  As of T<sub>a</sub> = 45 °C, a max.load current I<sub>max</sub> = 50 mA is permitted.

 $<sup>^{12)}</sup>$  Below  $T_u$  = -10 °C a warm-up time is necessary.

T <sub>M</sub> (mission time)	20 years
Classifications	
eCl@ss 5.0	27270904
eCl@ss 5.1.4	27270904
eCl@ss 6.0	27270904
eCl@ss 6.2	27270904
eCl@ss 7.0	27270904
eCl@ss 8.0	27270904
eCl@ss 8.1	27270904
eCl@ss 9.0	27270904
eCl@ss 10.0	27270904
eCl@ss 11.0	27270904
eCl@ss 12.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528

#### Dimensional drawing (Dimensions in mm (inch))




- ① Optical axis, sender
- ② Optical axis, receiver
- 3 LED indicator yellow: Status of received light beam
- ④ LED indicator green: power on
- (5) LED indicator yellow: Status of received light beam
- 6 Mounting hole, Ø 4.2 mm
- ⑦ Connection
- 8 Potentiometer
- Single teach-in button

#### Connection diagram

#### Cd-287

#### Characteristic curve


Min. distance from object to background in mm (inch)



- ① Sensing range on black, 6% remission factor
- ② Sensing range on white, 90% remission factor


#### Light spot size


Radius in mm (inch)



- $\textcircled{1} \ \, \mathsf{Light} \, \mathsf{spot} \, \mathsf{horizontal}$
- ② Light spot vertical

### Repeatability





- $\textcircled{\scriptsize 1}$  6 % remission, on black
- 2 90 % remission, on white

#### Recommended accessories

Other models and accessories → www.sick.com/PowerProx

	Brief description	Туре	Part no.	
Mounting brackets and plates				
	Mounting brackets	BEF-WTT12L	2078538	
Plug connectors and cables				
	Head A: male connector, M12, 5-pin, straight Cable: unshielded For field bus technology	STE-1205-G	6022083	

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

