



# WL9LG-3P1152


W9

PHOTOELECTRIC SENSORS

**SICK**  
Sensor Intelligence.



Illustration may differ



### Ordering information

| Type         | part no. |
|--------------|----------|
| WL9LG-3P1152 | 1076049  |

Other models and accessories → [www.sick.com/W9](http://www.sick.com/W9)

### Detailed technical data

#### Features

|  |   |
|--|---|
| <b>Functional principle</b>            | Photoelectric retro-reflective sensor                               |
| <b>Functional principle detail</b>     | Without reflector minimum distance (autocollimation/coaxial optics) |
| <b>Dimensions (W x H x D)</b>          | 12.2 mm x 50 mm x 23.6 mm   |
| <b>Housing design (light emission)</b> | Rectangular   |
| <b>Mounting hole</b>                   | M3  |
| <b>Sensing range max.</b>              | 0 m ... 3.5 m <sup>1)</sup><br>2)                                   |
| <b>Sensing range</b>                   | 0 m ... 2.2 m <sup>1)</sup><br>2)                                   |
| <b>Type of light</b>                   | Visible red light   |
| <b>Light source</b>                    | Laser <sup>3)</sup>   |
| <b>Light spot size (distance)</b>      | Ø 0.4 mm (60 mm)  |
| <b>Wave length</b>                     | 650 nm  |
| <b>Laser class</b>                     | 1 (IEC 60825-1 / CDRH 21 CFR 1040.10 & 1040.11) <sup>4)</sup>       |
| <b>Adjustment</b>                      | Single teach-in button  |
| <b>AutoAdapt</b>                       | ✓   |

<sup>1)</sup> Reflective tape REF-AC1000.

<sup>2)</sup> To ensure reliable operation, we recommend using REF-AC1000 reflective tape or reflective-tap reflectors such as P41F, PLV14-A, PLH25-M12, or PLH25-D12. Reflectors with large-scale triple structures must only be used if deemed suitable for the application.

<sup>3)</sup> Average service life: 50,000 h at T<sub>U</sub> = +25 °C.

<sup>4)</sup> Do not intentionally look into the laser beam. Never point the laser beam at people's eyes.

|                             |  |
|-----------------------------|--|
| <b>Special applications</b> | Detecting small objects, Detecting transparent objects |
|-----------------------------|--|

- 1) Reflective tape REF-AC1000.
- 2) To ensure reliable operation, we recommend using REF-AC1000 reflective tape or reflective-tap reflectors such as P41F, PLV14-A, PLH25-M12, or PLH25-D12. Reflectors with large-scale triple structures must only be used if deemed suitable for the application.
- 3) Average service life: 50,000 h at  $T_U = +25\text{ °C}$ .
- 4) Do not intentionally look into the laser beam. Never point the laser beam at people's eyes.

### Mechanics/electronics

|   |  |
|---|--|
| <b>Supply voltage <math>U_B</math></b>        | 10 V DC ... 30 V DC <sup>1)</sup>                      |
| <b>Ripple</b>                                 | < 5 V <sub>pp</sub> <sup>2)</sup>                      |
| <b>Current consumption</b>                    | 30 mA <sup>3)</sup>                                    |
| <b>Switching output</b>                       | PNP <sup>4)</sup>                                      |
| <b>Output function</b>                        | Complementary  |
| <b>Switching mode</b>                         | Light/dark switching <sup>4)</sup>                     |
| <b>Output current <math>I_{max}</math></b>    | ≤ 100 mA   |
| <b>Response time</b>                          | ≤ 0.5 ms <sup>5)</sup>                                 |
| <b>Switching frequency</b>                    | 1,000 Hz <sup>6)</sup>                                 |
| <b>Connection type</b>                        | Cable, 4-wire, 2 m <sup>7)</sup>                       |
| <b>Cable material</b>                         | Plastic, PVC   |
| <b>Conductor cross section</b>                | 0.14 mm <sup>2</sup>                                   |
| <b>Circuit protection</b>                     | A <sup>8)</sup><br>B <sup>9)</sup><br>C <sup>10)</sup> |
| <b>Protection class</b>                       | III  |
| <b>Weight</b>                                 | 80 g   |
| <b>Polarizing filter</b>                      | ✓  |
| <b>Housing material</b>                       | Plastic, VISTAL®                                       |
| <b>Optics material</b>                        | Plastic, PMMA  |
| <b>Enclosure rating</b>                       | IP66<br>IP67<br>IP69K                                  |
| <b>Ambient operating temperature</b>          | -10 °C ... +50 °C                                      |
| <b>Ambient operating temperature extended</b> | -30 °C ... +55 °C <sup>11) 12)</sup>                   |

- 1) Limit values when operated in short-circuit protected network: max. 8 A.
- 2) May not fall below or exceed  $U_y$  tolerances.
- 3) Without load.
- 4) Q = light switching.
- 5) Signal transit time with resistive load.
- 6) With light/dark ratio 1:1.
- 7) Do not bend below 0 °C.
- 8) A =  $V_S$  connections reverse-polarity protected.
- 9) B = inputs and output reverse-polarity protected.
- 10) C = interference suppression.
- 11) As of  $T_a = 50\text{ °C}$ , a max. supply voltage  $V_{max} = 24\text{ V}$  and a max. load current  $I_{max} = 50\text{ mA}$  is permitted.
- 12) Operation below  $T_u -10\text{ °C}$  is possible if the sensor is already switched on at  $T_u > -10\text{ °C}$ , then cools down, and the supply voltage is subsequently not switched off. Switching on below  $T_u -10\text{ °C}$  is not permissible.

|                                     |                   |
|-------------------------------------|-------------------|
| <b>Ambient temperature, storage</b> | -30 °C ... +70 °C |
| <b>UL File No.</b>                  | NRKH.E181493      |

- 1) Limit values when operated in short-circuit protected network: max. 8 A.
- 2) May not fall below or exceed  $U_V$  tolerances.
- 3) Without load.
- 4) Q = light switching.
- 5) Signal transit time with resistive load.
- 6) With light/dark ratio 1:1.
- 7) Do not bend below 0 °C.
- 8) A =  $V_S$  connections reverse-polarity protected.
- 9) B = inputs and output reverse-polarity protected.
- 10) C = interference suppression.
- 11) As of  $T_a = 50$  °C, a max. supply voltage  $V_{max.} = 24$  V and a max. load current  $I_{max.} = 50$  mA is permitted.
- 12) Operation below  $T_u -10$  °C is possible if the sensor is already switched on at  $T_u > -10$  °C, then cools down, and the supply voltage is subsequently not switched off. Switching on below  $T_u -10$  °C is not permissible.

### Safety-related parameters

|                         |  |
|-------------------------|--|
| <b>MTTF<sub>D</sub></b> | 655 years (EN ISO 13849-1) <sup>1)</sup> |
| <b>DC<sub>avg</sub></b> | 0 %                                      |

<sup>1)</sup> Mode of calculation: Parts-Count-calculation.

### Certificates

|   |   |
|---|---|
| <b>EU declaration of conformity</b>           | ✓ |
| <b>UK declaration of conformity</b>           | ✓ |
| <b>ACMA declaration of conformity</b>         | ✓ |
| <b>Moroccan declaration of conformity</b>     | ✓ |
| <b>China RoHS</b>                             | ✓ |
| <b>ECOLAB certificate</b>                     | ✓ |
| <b>cULus certificate</b>                      | ✓ |
| <b>Laser safety (IEC 60825-1) certificate</b> | ✓ |


### Classifications

|                     |          |
|---------------------|----------|
| <b>ECLASS 5.0</b>   | 27270902 |
| <b>ECLASS 5.1.4</b> | 27270902 |
| <b>ECLASS 6.0</b>   | 27270902 |
| <b>ECLASS 6.2</b>   | 27270902 |
| <b>ECLASS 7.0</b>   | 27270902 |
| <b>ECLASS 8.0</b>   | 27270902 |
| <b>ECLASS 8.1</b>   | 27270902 |
| <b>ECLASS 9.0</b>   | 27270902 |
| <b>ECLASS 10.0</b>  | 27270902 |
| <b>ECLASS 11.0</b>  | 27270902 |
| <b>ECLASS 12.0</b>  | 27270902 |
| <b>ETIM 5.0</b>     | EC002717 |
| <b>ETIM 6.0</b>     | EC002717 |
| <b>ETIM 7.0</b>     | EC002717 |
| <b>ETIM 8.0</b>     | EC002717 |

UNSPSC 16.0901


39121528

Adjustments Single teach-in button




- ③ LED indicator yellow: Status of received light beam
- ④ LED indicator green: power on
- ⑧ Teach-in button

Connection diagram Cd-095




Characteristic curve



- ① Reflector PLV14-A / PLH25-M12 / PLH25-D12
- ② Reflector P41F / reflective tape REF-AC1000


### Light spot size



#### Dimensions in mm (inch)


| Sensing range                | Vertical      | Horizontal    |
|------------------------------|---------------|---------------|
| <b>60 mm<br/>(2.36)</b>      | 0.4<br>(0.02) | 0.4<br>(0.02) |
| <b>200 mm<br/>(7.87)</b>     | 3.2<br>(0.13) | 2.4<br>(0.09) |
| <b>2,000 mm<br/>(78.74)</b>  | 40<br>(1.57)  | 30<br>(0.18)  |
| <b>3,500 mm<br/>(137.80)</b> | 60<br>(2.36)  | 50<br>(1.97)  |

### Light spot size (detailed view)




① Minimum distance between sensor and reflector

### Sensing range diagram



- Sensing range    ■ Sensing range max.
- ① Reflector PLV14-A / PLH25-M12 / PLH25-D12
- ② Reflector P41F / reflective tape REF-AC1000

### Dimensional drawing WL9L-3



- ① Sender and receiver optical axis center
- ② Mounting hole M3 (Ø 3.1 mm)
- ③ LED indicator yellow: Status of received light beam
- ④ LED indicator green: power on
- ⑤ Connecting cable or connecting cable with connector
- ⑥ male connector M8, 4-pin
- ⑦ male connector M12, 4-pin

Recommended accessories

Other models and accessories → [www.sick.com/W9](http://www.sick.com/W9)

|   | Brief description  | Type          | part no. |
|---|--|---------------|----------|
| <b>Mounting systems</b>   |  |               |          |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Plate N08 for universal clamp bracket</li> <li><b>Material:</b> Steel, zinc diecast</li> <li><b>Details:</b> Zinc plated steel (sheet), Zinc die cast (clamping bracket)</li> <li><b>Items supplied:</b> Universal clamp (5322626), mounting hardware</li> <li><b>Usable for:</b> W100, W150, W4S, W4F, W8, W9-3, W8G, W8 Laser, W8 Inox, G6, W100 Laser, W100-2, W10, G6 Inox, RAY10, W4SLG-3, W9, GR18, MultiPulse, Reflex Array, MultiLine, LUT3, KT5, KT8, KT10, CS8</li> </ul> | BEF-KHS-N08   | 2051607  |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Plate N11N for universal clamp bracket</li> <li><b>Material:</b> Stainless steel</li> <li><b>Details:</b> Stainless steel 1.4571 (sheet), Stainless steel 1.4408 (clamp)</li> <li><b>Items supplied:</b> Universal clamp (5322627), mounting hardware</li> <li><b>Usable for:</b> DeltaPac, Glare, WTD20E</li> </ul>  | BEF-KHS-N11N  | 2071081  |
| <b>reflectors and optics</b>  |  |               |          |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Suitable for laser sensors, self-adhesive, cut, see alignment note</li> <li><b>Dimensions:</b> 56.3 mm 56.3 mm</li> <li><b>Ambient operating temperature:</b> -20 °C ... +60 °C</li> </ul>  | REF-AC1000-56 | 4063030  |
| <b>connectors and cables</b>  |  |               |          |
|  | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Male connector, M12, 4-pin, straight, A-coded</li> <li><b>Description:</b> Unshielded</li> <li><b>Connection systems:</b> Screw-type terminals</li> <li><b>Permitted cross-section:</b> ≤ 0.75 mm<sup>2</sup></li> </ul>   | STE-1204-G    | 6009932  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)