



WLG4C-3P2232A00

W4

PHOTOELECTRIC SENSORS

**SICK**  
Sensor Intelligence.



Illustration may differ

## Ordering information

| Type            | part no. |
|-----------------|----------|
| WLG4C-3P2232A00 | 1080933  |

Other models and accessories → [www.sick.com/W4](http://www.sick.com/W4)

## Detailed technical data

### Features

|                             |                                                                                                                     |
|-----------------------------|---------------------------------------------------------------------------------------------------------------------|
| <b>Functional principle</b> | Photoelectric retro-reflective sensor                                                                               |
| <b>Sensing range max.</b>   | 0.01 m ... 4.5 m <sup>1)</sup>                                                                                      |
| <b>Sensing range</b>        | 0.02 m ... 3.5 m <sup>1)</sup>                                                                                      |
| <b>Polarisation filters</b> | Yes                                                                                                                 |
| <b>Emitted beam</b>         |                                                                                                                     |
| Light source                | PinPoint LED <sup>2)</sup>                                                                                          |
| Type of light               | Visible red light                                                                                                   |
| Light spot size (distance)  | Ø 75 mm (1.5 m)                                                                                                     |
| <b>Key LED figures</b>      |                                                                                                                     |
| Wave length                 | 650 nm                                                                                                              |
| <b>Adjustment</b>           | Single teach-in button, IO-Link                                                                                     |
| <b>Special applications</b> | Detecting transparent objects                                                                                       |
| <b>Pin 2 configuration</b>  | External input, Teach-in input, Sender off input, Detection output, logic output, Device contamination alarm output |
| <b>AutoAdapt</b>            | ✓                                                                                                                   |

<sup>1)</sup> Reflector PL80A.

<sup>2)</sup> Average service life: 100,000 h at T<sub>U</sub> = +25 °C.

### Communication interface

|                        |                                                                                                              |
|------------------------|--------------------------------------------------------------------------------------------------------------|
| <b>IO-Link</b>         | ✓ , COM2 (38,4 kBaud)                                                                                        |
| Data transmission rate | COM2 (38,4 kBaud)                                                                                            |
| Cycle time             | 2.3 ms                                                                                                       |
| Process data length    | 16 Bit                                                                                                       |
| Process data structure | Bit 0 = switching signal Q <sub>L1</sub><br>Bit 1 = switching signal Q <sub>L2</sub><br>Bit 2 ... 15 = empty |
| VendorID               | 26                                                                                                           |
| DeviceID HEX           | 0x800103                                                                                                     |

|              |         |
|--------------|---------|
| DeviceID DEC | 8388867 |
|--------------|---------|

## Electronics

|                                         |                                                        |
|-----------------------------------------|--------------------------------------------------------|
| <b>Supply voltage <math>U_B</math></b>  | 10 V DC ... 30 V DC <sup>1)</sup>                      |
| <b>Ripple</b>                           | < 5 V <sub>pp</sub> <sup>2)</sup>                      |
| <b>Current consumption</b>              | 20 mA <sup>3)</sup>                                    |
| <b>Protection class</b>                 | III                                                    |
| <b>Digital output</b>                   |                                                        |
| Type                                    | PNP <sup>4)</sup>                                      |
| Switching mode                          | Light/dark switching                                   |
| Output current $I_{max}$                | ≤ 100 mA                                               |
| Response time                           | < 0.5 ms <sup>5)</sup>                                 |
| Repeatability (response time)           | 150 μs <sup>6)</sup>                                   |
| Switching frequency                     | 1,000 Hz <sup>7)</sup>                                 |
| <b>Attenuation along light beam</b>     | > 8 %                                                  |
| <b>Circuit protection</b>               | A <sup>8)</sup><br>C <sup>9)</sup><br>D <sup>10)</sup> |
| <b>Response time Q/ on Pin 2</b>        | 300 μs ... 450 μs <sup>5) 6)</sup>                     |
| <b>Switching frequency Q / to pin 2</b> | 1,000 Hz <sup>11)</sup>                                |

<sup>1)</sup> Limit values.

<sup>2)</sup> May not fall below or exceed  $U_V$  tolerances.

<sup>3)</sup> Without load.

<sup>4)</sup> Pin 4: This switching output must not be connected to another output.

<sup>5)</sup> Signal transit time with resistive load.

<sup>6)</sup> Valid for Q \ on Pin2, if configured with software.

<sup>7)</sup> With light/dark ratio 1:1.

<sup>8)</sup> A =  $V_S$  connections reverse-polarity protected.

<sup>9)</sup> C = interference suppression.

<sup>10)</sup> D = outputs overcurrent and short-circuit protected.

<sup>11)</sup> With light / dark ratio 1:1, valid for Q \ on Pin2, if configured with software.

## Mechanics

|                               |                          |
|-------------------------------|--------------------------|
| <b>Housing</b>                | Rectangular              |
| <b>Design detail</b>          | Flat                     |
| <b>Dimensions (W x H x D)</b> | 16 mm x 39.5 mm x 12 mm  |
| <b>Connection</b>             | Male connector M8, 4-pin |
| <b>Material</b>               |                          |
| Housing                       | Plastic, ABS             |
| Front screen                  | Plastic, PMMA            |
| <b>Weight</b>                 | 30 g                     |

## Ambient data

|                                      |                   |
|--------------------------------------|-------------------|
| <b>Enclosure rating</b>              | IP67<br>IP66      |
| <b>Ambient operating temperature</b> | -40 °C ... +60 °C |

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Ambient temperature, storage</b> | -40 °C ... +75 °C            |
| <b>UL File No.</b>                  | NRKH.E181493 & NRKH7.E181493 |

## Smart Task

|                                  |                                                                                                                                   |
|----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| <b>Smart Task name</b>           | Base logics                                                                                                                       |
| <b>Logic function</b>            | Direct<br>AND<br>OR<br>WINDOW<br>Hysteresis                                                                                       |
| <b>Timer function</b>            | Deactivated<br>Switch-on delay<br>Off delay<br>ON and OFF delay<br>Impulse (one shot)                                             |
| <b>Inverter</b>                  | Yes                                                                                                                               |
| <b>Switching frequency</b>       | SIO Direct: 1000 Hz<br>SIO Logic: 1000 Hz<br>IOL: 900 Hz                                                                          |
| <b>Response time</b>             | SIO Direct: 300 µs ... 450 µs <sup>1)</sup><br>SIO Logic: 500 µs ... 600 µs <sup>2)</sup><br>IOL: 500 µs ... 900 µs <sup>3)</sup> |
| <b>Repeatability</b>             | SIO Direct: 150 µs <sup>1)</sup><br>SIO Logic: 150 µs <sup>2)</sup><br>IOL: 400 µs <sup>3)</sup>                                  |
| <b>Switching signal</b>          |                                                                                                                                   |
| Switching signal Q <sub>L1</sub> | Switching output                                                                                                                  |
| Switching signal Q <sub>L2</sub> | Switching output                                                                                                                  |

<sup>1)</sup> SIO Direct: sensor operation in standard I/O mode without IO-Link communication and without using internal sensor logic or time parameters (set to "direct"/"deactivated").

<sup>2)</sup> SIO Logic: Sensor operation in standard I/O mode without IO-Link communication. Sensor-internal logic or timing parameters plus Automation Functions used.

<sup>3)</sup> IOL: Sensor operation with full IO-Link communication and usage of logic, timing and Automation Function parameters.

## Diagnosis


|                         |                            |
|-------------------------|----------------------------|
| <b>Device status</b>    | Yes                        |
| <b>Quality of teach</b> | Yes                        |
| <b>Quality of run</b>   | Yes, Contamination display |

## Classifications

|                     |          |
|---------------------|----------|
| <b>ECLASS 5.0</b>   | 27270902 |
| <b>ECLASS 5.1.4</b> | 27270902 |
| <b>ECLASS 6.0</b>   | 27270902 |
| <b>ECLASS 6.2</b>   | 27270902 |
| <b>ECLASS 7.0</b>   | 27270902 |
| <b>ECLASS 8.0</b>   | 27270902 |
| <b>ECLASS 8.1</b>   | 27270902 |
| <b>ECLASS 9.0</b>   | 27270902 |
| <b>ECLASS 10.0</b>  | 27270902 |
| <b>ECLASS 11.0</b>  | 27270902 |


|                       |          |
|-----------------------|----------|
| <b>ECLASS 12.0</b>    | 27270902 |
| <b>ETIM 5.0</b>       | EC002717 |
| <b>ETIM 6.0</b>       | EC002717 |
| <b>ETIM 7.0</b>       | EC002717 |
| <b>ETIM 8.0</b>       | EC002717 |
| <b>UNSPSC 16.0901</b> | 39121528 |

### Connection diagram Cd-367




### Characteristic curve WLG4-3 with polarisation filter

Operating reserve in %



- ① Reflective tape REF-IRF-56
- ② PL10F reflector
- ③ Reflector PL20A
- ④ Reflector PL40A
- ⑤ Reflector PL80A

Sensing range diagram WLG4-3 with polarisation filter



- Sensing range      ■ Sensing range max.
- ① Reflective tape REF-IRF-56  
② PL10F reflector  
③ Reflector PL20A  
④ Reflector PL40A  
⑤ Reflector PL80A

## Modified teach mode

### Geänderter Teach Modus modified teach mode WLG4-3

---

Bitte neuen Teach-In-Mode ab Herstellungswoche  
**01/2013** berücksichtigen.

Teach-In-Taste drücken:

- **2 Sek.** für transparente Objekte (8% Schaltschwelle mit autom. Nachführung)
- **8 Sek.** für Standardanwendungen (Schaltschwelle 50%)

Teach-In-Mode **vor** Herstellungswoche **01/2013**

Teach-In-Taste drücken:

- **2 Sek.** (50% Schaltschwelle ohne Nachführung)
  - **8 Sek.** für transparente Objekte (Schaltschwelle 10%)
- 

Please consider new teach-in mode as of  
production week **01/2013**.

Press teach-in button:

- **2 sec.** for clear objects (8% threshold with continuous threshold adaption)
- **8 sec.** for standard mode (50% threshold)

Teach-In-Mode **before** production week **01/2013**.

Press teach-in button:

- **2 sec.** (50% threshold without continuous threshold adaption)
  - **8 sec.** for clear objects (threshold 10%)
- 

Bsp. Herstellungswoche 1309 = KW09/2013  
eg production week 1309 = CW09/2013



**SICK**  
Sensor Intelligence.

[illegible]

- ① Center of optical axis, sender
- ② Center of optical axis, receiver
- ③ Orange LED indicator: status of received light beam
- ④ LED indicator green: Supply voltage active
- ⑤ Threaded mounting hole M3
- ⑥ Connection
- ⑦ Teach-in button

Other models and accessories → [www.sick.com/W4](http://www.sick.com/W4)

8 PHOTOELECTRIC SENSORS | SICK

|                                                                                   | Brief description                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | Type               | part no. |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|----------|
| reflectors and optics                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |                    |          |
|  | <ul style="list-style-type: none"> <li>• <b>Description:</b> Fine triple reflector, screw connection, suitable for laser sensors</li> <li>• <b>Dimensions:</b> 52 mm 62 mm</li> <li>• <b>Ambient operating temperature:</b> -30 °C ... +65 °C</li> </ul>                                                                                                                                                                                                                                | P250F              | 5308843  |
| connectors and cables                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |                    |          |
|  | <ul style="list-style-type: none"> <li>• <b>Connection type head A:</b> Female connector, M8, 4-pin, straight, A-coded</li> <li>• <b>Connection type head B:</b> Flying leads</li> <li>• <b>Signal type:</b> Sensor/actuator cable</li> <li>• <b>Cable:</b> 5 m, 4-wire, PVC</li> <li>• <b>Description:</b> Sensor/actuator cable, unshielded</li> <li>• <b>Application:</b> Zones with chemicals, Uncontaminated zones</li> </ul>                                                      | YF8U14-050VA3XLEAX | 2095889  |
|  | <ul style="list-style-type: none"> <li>• <b>Connection type head A:</b> Male connector, M8, 4-pin, straight, A-coded</li> <li>• <b>Description:</b> Unshielded</li> <li>• <b>Connection systems:</b> Screw-type terminals</li> <li>• <b>Permitted cross-section:</b> 0.14 mm² ... 0.5 mm²</li> </ul>                                                                                                                                                                                    | STE-0804-G         | 6037323  |
|  | <ul style="list-style-type: none"> <li>• <b>Connection type head A:</b> Female connector, M8, 4-pin, straight, A-coded</li> <li>• <b>Connection type head B:</b> Flying leads</li> <li>• <b>Signal type:</b> Sensor/actuator cable</li> <li>• <b>Cable:</b> 5 m, 4-wire, PUR, halogen-free</li> <li>• <b>Description:</b> Sensor/actuator cable, unshielded</li> <li>• <b>Application:</b> Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul> | YF8U14-050UA3XLEAX | 2094792  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)