



# WSE9LC-3P2436A00


W9

PHOTOELECTRIC SENSORS

**SICK**  
Sensor Intelligence.



Illustration may differ



Ordering information

| Type             | part no. |
|------------------|----------|
| WSE9LC-3P2436A00 | 1080958  |

Other models and accessories → [www.sick.com/W9](http://www.sick.com/W9)

Detailed technical data

Features

|                                 |                                                                                                   |
|---------------------------------|---------------------------------------------------------------------------------------------------|
| Functional principle            | Through-beam photoelectric sensor                                                                 |
| Dimensions (W x H x D)          | 12.2 mm x 52.2 mm x 23.6 mm                                                                       |
| Housing design (light emission) | Rectangular                                                                                       |
| Mounting hole                   | M3                                                                                                |
| Sensing range max.              | 0 m ... 60 m                                                                                      |
| Sensing range                   | 0 m ... 50 m                                                                                      |
| Type of light                   | Visible red light                                                                                 |
| Light source                    | Laser <sup>1)</sup>                                                                               |
| Light spot size (distance)      | Ø 1 mm (500 mm)                                                                                   |
| Wave length                     | 650 nm                                                                                            |
| Laser class                     | 1 (IEC 60825-1 / CDRH 21 CFR 1040.10 & 1040.11) <sup>2)</sup>                                     |
| Adjustment                      | IO-Link                                                                                           |
| Pin 2 configuration             | External input, Teach-in input, Detection output, logic output, Device contamination alarm output |
| Special applications            | Detecting small objects                                                                           |

<sup>1)</sup> Average service life: 50,000 h at T<sub>U</sub> = +25 °C.

<sup>2)</sup> Do not intentionally look into the laser beam. Never point the laser beam at people's eyes.

## Mechanics/electronics

|                                               |                                                          |
|-----------------------------------------------|----------------------------------------------------------|
| <b>Supply voltage <math>U_B</math></b>        | 10 V DC ... 30 V DC <sup>1)</sup>                        |
| <b>Ripple</b>                                 | < 5 V <sub>pp</sub> <sup>2)</sup>                        |
| <b>Current consumption</b>                    | 30 mA <sup>3)</sup>                                      |
| <b>Switching output</b>                       | PNP <sup>4)</sup><br>5)                                  |
| <b>Output function</b>                        | Complementary                                            |
| <b>Switching mode</b>                         | Light/dark switching <sup>4)</sup>                       |
| <b>Output current <math>I_{max.}</math></b>   | ≤ 100 mA                                                 |
| <b>Response time</b>                          | ≤ 0.5 ms <sup>6)</sup>                                   |
| <b>Response time Q/ on Pin 2</b>              | 300 μs ... 450 μs <sup>6) 7)</sup>                       |
| <b>Switching frequency</b>                    | 1,000 Hz <sup>8)</sup>                                   |
| <b>Switching frequency Q / to pin 2</b>       | ≤ 1,000 Hz <sup>9)</sup>                                 |
| <b>Connection type</b>                        | Male connector M12, 4-pin                                |
| <b>Circuit protection</b>                     | A <sup>10)</sup><br>B <sup>11)</sup><br>C <sup>12)</sup> |
| <b>Protection class</b>                       | III                                                      |
| <b>Weight</b>                                 | 13 g                                                     |
| <b>Housing material</b>                       | Plastic, VISTAL®                                         |
| <b>Optics material</b>                        | Plastic, PMMA                                            |
| <b>Enclosure rating</b>                       | IP66<br>IP67<br>IP69K                                    |
| <b>Ambient operating temperature</b>          | -10 °C ... +50 °C                                        |
| <b>Ambient operating temperature extended</b> | -30 °C ... +55 °C <sup>13) 14)</sup>                     |
| <b>Ambient temperature, storage</b>           | -30 °C ... +70 °C                                        |
| <b>UL File No.</b>                            | NRKH.E181493                                             |
| <b>Part number of individual components</b>   | 2064063 WS9L-3D2436, 2088364 WE9LC-3P2430A00             |
| <b>Repeatability Q/ on Pin 2:</b>             | 150 μs <sup>7)</sup>                                     |

<sup>1)</sup> Limit values when operated in short-circuit protected network: max. 8 A.

<sup>2)</sup> May not fall below or exceed  $U_V$  tolerances.

<sup>3)</sup> Without load.

<sup>4)</sup> Q = light switching.

<sup>5)</sup> Pin 4: This switching output must not be connected to another output.

<sup>6)</sup> Signal transit time with resistive load.

<sup>7)</sup> Valid for Q \ on Pin2, if configured with software.

<sup>8)</sup> With light/dark ratio 1:1.

<sup>9)</sup> With light / dark ratio 1:1, valid for Q \ on Pin2, if configured with software.

<sup>10)</sup> A =  $V_S$  connections reverse-polarity protected.

<sup>11)</sup> B = inputs and output reverse-polarity protected.

<sup>12)</sup> C = interference suppression.

<sup>13)</sup> As of  $T_a = 50 °C$ , a max. supply voltage  $V_{max.} = 24 V$  and a max. load current  $I_{max.} = 50 mA$  is permitted.

<sup>14)</sup> Operation below  $T_u -10 °C$  is possible if the sensor is already switched on at  $T_u > -10 °C$ , then cools down, and the supply voltage is subsequently not switched off. Switching on below  $T_u -10 °C$  is not permissible.

## Safety-related parameters

|                                     |                                          |
|-------------------------------------|------------------------------------------|
| <b>MTTF<sub>D</sub></b>             | 405 years (EN ISO 13849-1) <sup>1)</sup> |
| <b>DC<sub>avg</sub></b>             | 0 %                                      |
| <b>T<sub>M</sub> (mission time)</b> | 10 years                                 |

<sup>1)</sup> Mode of calculation: Parts-Count-calculation.

## Communication interface

|                                       |                                                                                                              |
|---------------------------------------|--------------------------------------------------------------------------------------------------------------|
| <b>Communication interface</b>        | IO-Link V1.1                                                                                                 |
| <b>Communication Interface detail</b> | COM2 (38,4 kBaud)                                                                                            |
| <b>Cycle time</b>                     | 2.3 ms                                                                                                       |
| <b>Process data length</b>            | 16 Bit                                                                                                       |
| <b>Process data structure</b>         | Bit 0 = switching signal Q <sub>L1</sub><br>Bit 1 = switching signal Q <sub>L2</sub><br>Bit 2 ... 15 = empty |
| <b>VendorID</b>                       | 26                                                                                                           |
| <b>DeviceID HEX</b>                   | 0x80011C                                                                                                     |
| <b>DeviceID DEC</b>                   | 8388892                                                                                                      |

## Smart Task

|                                  |                                                                                                                                   |
|----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| <b>Smart Task name</b>           | Base logics                                                                                                                       |
| <b>Logic function</b>            | Direct<br>AND<br>OR<br>WINDOW<br>Hysteresis                                                                                       |
| <b>Timer function</b>            | Deactivated<br>Switch-on delay<br>Off delay<br>ON and OFF delay<br>Impulse (one shot)                                             |
| <b>Inverter</b>                  | Yes                                                                                                                               |
| <b>Switching frequency</b>       | SIO Direct: 1000 Hz <sup>1)</sup><br>SIO Logic: 1000 Hz <sup>2)</sup><br>IOL: 900 Hz <sup>3)</sup>                                |
| <b>Response time</b>             | SIO Direct: 300 µs ... 450 µs <sup>1)</sup><br>SIO Logic: 500 µs ... 600 µs <sup>2)</sup><br>IOL: 500 µs ... 900 µs <sup>3)</sup> |
| <b>Repeatability</b>             | SIO Direct: 150 µs <sup>1)</sup><br>SIO Logic: 150 µs <sup>2)</sup><br>IOL: 400 µs <sup>3)</sup>                                  |
| <b>Switching signal</b>          |                                                                                                                                   |
| Switching signal Q <sub>L1</sub> | Output type (dependant on the adjusted threshold)                                                                                 |
| Switching signal Q <sub>L2</sub> | Output type (dependant on the adjusted threshold)                                                                                 |

<sup>1)</sup> SIO Direct: sensor operation in standard I/O mode without IO-Link communication and without using internal sensor logic or time parameters (set to "direct"/"deactivated").

<sup>2)</sup> SIO Logic: Sensor operation in standard I/O mode without IO-Link communication. Sensor-internal logic or timing parameters plus Automation Functions used.

<sup>3)</sup> IOL: Sensor operation with full IO-Link communication and usage of logic, timing and Automation Function parameters.

## Diagnosis

|                         |     |
|-------------------------|-----|
| <b>Device status</b>    | Yes |
| <b>Function reserve</b> | Yes |


## Certificates

|                                               |   |
|-----------------------------------------------|---|
| <b>EU declaration of conformity</b>           | ✓ |
| <b>UK declaration of conformity</b>           | ✓ |
| <b>ACMA declaration of conformity</b>         | ✓ |
| <b>Moroccan declaration of conformity</b>     | ✓ |
| <b>China RoHS</b>                             | ✓ |
| <b>ECOLAB certificate</b>                     | ✓ |
| <b>cULus certificate</b>                      | ✓ |
| <b>Laser safety (IEC 60825-1) certificate</b> | ✓ |

## Classifications


|                       |          |
|-----------------------|----------|
| <b>ECLASS 5.0</b>     | 27270901 |
| <b>ECLASS 5.1.4</b>   | 27270901 |
| <b>ECLASS 6.0</b>     | 27270901 |
| <b>ECLASS 6.2</b>     | 27270901 |
| <b>ECLASS 7.0</b>     | 27270901 |
| <b>ECLASS 8.0</b>     | 27270901 |
| <b>ECLASS 8.1</b>     | 27270901 |
| <b>ECLASS 9.0</b>     | 27270901 |
| <b>ECLASS 10.0</b>    | 27270901 |
| <b>ECLASS 11.0</b>    | 27270901 |
| <b>ECLASS 12.0</b>    | 27270901 |
| <b>ETIM 5.0</b>       | EC002716 |
| <b>ETIM 6.0</b>       | EC002716 |
| <b>ETIM 7.0</b>       | EC002716 |
| <b>ETIM 8.0</b>       | EC002716 |
| <b>UNSPSC 16.0901</b> | 39121528 |

## Adjustments Single teach-in button




- ③ LED indicator yellow: Status of received light beam
- ④ LED indicator green: power on
- ⑧ Teach-in button


Connection diagram Cd-376



Characteristic curve



Light spot size




Dimensions in mm (inch)

| Sensing range         | Vertical        | Horizontal      |
|-----------------------|-----------------|-----------------|
| 0.5 m<br>(1.64 feet)  | < 1.0<br>(0.04) | < 1.0<br>(0.04) |
| 1 m<br>(3.28 feet)    | 1.5<br>(0.06)   | 1.2<br>(0.05)   |
| 5 m<br>(16.40 feet)   | 15<br>(0.59)    | 11<br>(0.43)    |
| 10 m<br>(32.81 feet)  | 45<br>(1.77)    | 28<br>(1.10)    |
| 60 m<br>(196.85 feet) | 336<br>(13.23)  | 200<br>(7.87)   |

Vertical

Horizontal


Light spot size (detailed view) Detailed view close range




Vertical

Horizontal

Sensing range diagram



Dimensional drawing WSE9L-3



Dimensions in mm (inch)

- ① Sender and receiver optical axis center
- ② Mounting hole M3 (Ø 3.1 mm)
- ③ LED indicator yellow: Status of received light beam
- ④ LED indicator green: power on
- ⑤ Connecting cable or connecting cable with connector
- ⑥ male connector M8, 4-pin
- ⑦ male connector M12, 4-pin

Recommended accessories

Other models and accessories → [www.sick.com/W9](http://www.sick.com/W9)

|                       | Brief description                                                                                                                                                                                                                                                                                                                                                                                                            | Type               | part no. |
|-----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|----------|
| connectors and cables |                                                                                                                                                                                                                                                                                                                                                                                                                              |                    |          |
|                       | <ul style="list-style-type: none"><li>• <b>Connection type head A:</b> Female connector, M12, 4-pin, straight, A-coded</li><li>• <b>Connection type head B:</b> Flying leads</li><li>• <b>Signal type:</b> Sensor/actuator cable</li><li>• <b>Cable:</b> 5 m, 4-wire, PVC</li><li>• <b>Description:</b> Sensor/actuator cable, unshielded</li><li>• <b>Application:</b> Zones with chemicals, Uncontaminated zones</li></ul> | YF2A14-050VB3XLEAX | 2096235  |
|                       | <ul style="list-style-type: none"><li>• <b>Connection type head A:</b> Male connector, M12, 4-pin, straight, A-coded</li><li>• <b>Description:</b> Unshielded</li><li>• <b>Connection systems:</b> Screw-type terminals</li><li>• <b>Permitted cross-section:</b> ≤ 0.75 mm<sup>2</sup></li></ul>                                                                                                                            | STE-1204-G         | 6009932  |

|                                                                                   | Brief description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Type        | part no. |
|-----------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|----------|
| Mounting systems                                                                  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |             |          |
|  | <ul style="list-style-type: none"><li>• <b>Description:</b> Plate N08 for universal clamp bracket</li><li>• <b>Material:</b> Steel, zinc diecast</li><li>• <b>Details:</b> Zinc plated steel (sheet), Zinc die cast (clamping bracket)</li><li>• <b>Items supplied:</b> Universal clamp (5322626), mounting hardware</li><li>• <b>Usable for:</b> W100, W150, W4S, W4F, W8, W9-3, W8G, W8 Laser, W8 Inox, G6, W100 Laser, W100-2, W10, G6 Inox, RAY10, W4SLG-3, W9, GR18, MultiPulse, Reflex Array, MultiLine, LUT3, KT5, KT8, KT10, CS8</li></ul> | BEF-KHS-N08 | 2051607  |
|  | <ul style="list-style-type: none"><li>• <b>Description:</b> Mounting bracket</li><li>• <b>Material:</b> Steel</li><li>• <b>Details:</b> Steel, zinc coated</li><li>• <b>Items supplied:</b> Mounting hardware included</li><li>• <b>Suitable for:</b> W9-3</li></ul>                                                                                                                                                                                                                                                                               | BEF-WN-W9-2 | 2022855  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

**For us, that is “Sensor Intelligence.”**

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)