



WTB9LC-3P2462A00

W9

SMALL PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
WTB9LC-3P2462A00	1080942

Other models and accessories → www.sick.com/W9

Illustration may differ



Detailed technical data

Features

Functional principle	Photoelectric proximity sensor
Functional principle detail	Background suppression
Dimensions (W x H x D)	12.2 mm x 52.2 mm x 23.6 mm
Housing design (light emission)	Rectangular
Mounting hole	M3
Sensing range max.	25 mm 300 mm ¹⁾
Sensing range	25 mm 300 mm ¹⁾
Type of light	Visible red light
Light source	Laser ²⁾
Light spot size (distance)	Ø 1 mm (170 mm)
Wave length	650 nm
Laser class	1 (IEC 60825-1 / CDRH 21 CFR 1040.10 & 1040.11)
Adjustment	IO-Link Single teach-in button
Pin 2 configuration	External input, Teach-in input, Sender off input, Detection output, logic output
Special applications	Detecting small objects

 $^{^{1)}}$ Object with 90% remission (based on standard white, DIN 5033).

 $^{^{2)}}$ Average service life: 50,000 h at T_U = +25 °C.

Mechanics/electronics

Supply voltage \mathbf{U}_{B}	10 V DC 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Current consumption	30 mA ³⁾
Switching output	PNP ^{4) 5)}
Output function	Complementary
Switching mode	Light/dark switching ⁴⁾
Output current I _{max.}	≤ 100 mA
Response time	\leq 0.5 ms $^{6)}$
Response time Q/ on Pin 2	300 μs 450 μs ^{6) 7)}
Switching frequency	1,000 Hz ⁸⁾
Switching frequency Q / to pin 2	≤ 1,000 Hz ⁹⁾
Connection type	Male connector M12, 4-pin
Circuit protection	A ¹⁰⁾ B ¹¹⁾ C ¹²⁾
Protection class	III
Weight	13 g
Housing material	Plastic, VISTAL®
Optics material	Plastic, PMMA
Enclosure rating	IP66 IP67 IP69K
Ambient operating temperature	-10 °C +50 °C
Ambient operating temperature extended	-30 °C +55 °C ^{13) 14)}
Ambient temperature, storage	-30 °C +70 °C
UL File No.	NRKH.E181493
Repeatability Q/ on Pin 2:	150 μs ⁷⁾

 $^{^{1)}}$ Limit values when operated in short-circuit protected network: max. 8 A.

 $^{^{2)}\,\}mathrm{May}$ not exceed or fall below U_{V} tolerances.

³⁾ Without load.

⁴⁾ Q = light switching.

 $^{^{5)}}$ Pin 4: this switching output must not be connected to any other output.

⁶⁾ Signal transit time with resistive load.

 $^{^{7)}}$ Valid for Q \ on Pin2, if configured with software.

 $^{^{8)}}$ With light/dark ratio 1:1.

 $^{^{9)}}$ With light / dark ratio 1:1, valid for Q \backslash on Pin2, if configured with software.

 $^{^{10)}}$ A = V_S connections reverse-polarity protected.

 $^{^{11)}}$ B = inputs and output reverse-polarity protected.

 $^{^{12)}}$ C = interference suppression.

 $^{^{13)}}$ As of $T_a = 50$ °C, a max. supply voltage $V_{max.} = 24$ V and a max. load current $I_{max.} = 50$ mA is permitted.

 $^{^{14)}}$ Operation below Tu -10 °C is possible if the sensor is already switched on at Tu > -10 °C, then cools down, and the supply voltage is subsequently not switched off. Switching on below Tu -10 °C is not permissible.

Safety-related parameters

MTTF _D	326 years (EN ISO 13849-1) ¹⁾
DC _{avg}	0 %
T _M (mission time)	10 years

 $^{^{1)}}$ Mode of calculation: Parts-Count-calculation.

Communication interface

Communication interface	IO-Link V1.1
Communication Interface detail	COM2 (38,4 kBaud)
Cycle time	2.3 ms
Process data length	16 Bit
Process data structure	Bit 0 = switching signal Q_{L1} Bit 1 = switching signal Q_{L2} Bit 2 15 = empty
VendorID	26
DeviceID HEX	0x80010C
DeviceID DEC	8388876

Smart Task

Smart Task name Base logics Logic function Direct AND OR WINDOW Hysteresis Hysteresis Timer function Deactivated On delay Off delay Impulse (one shot) Inverter Yes Switching frequency SIO Direct: 1000 Hz ¹⁾ SIO Logic: 600 Hz ²⁾ IOL: 450 Hz ³⁾ Response time SIO Direct: 300 μs 450 μs ¹⁾ SIO Logic: 750 μs 900 μs ²⁾ IOL: 800 μs 1200 μs ³⁾ Repeatability SIO Direct: 150 μs ¹⁾ SIO Logic: 150 μs ²⁾ IOL: 400 μs ³⁾ Switching signal OLI Switching signal QLI Switching Switching Switching Switching Switching Switch			
AND OR WINDOW Hysteresis Timer function Deactivated On delay Off delay Impulse (one shot) Inverter Yes Switching frequency SIO Direct: 1000 Hz ¹⁾ SIO Logic: 600 Hz ²⁾ IOL: 450 Hz ³⁾ Response time SIO Direct: 300 μs 450 μs ¹⁾ SIO Logic: 750 μs 900 μs ²⁾ IOL: 800 μs 1200 μs ³⁾ Repeatability SIO Direct: 150 μs ¹⁾ SIO Logic: 150 μs ²⁾ IOL: 400 μs ³⁾ Switching signal Switching signal Switching signal Q _{L1} Output type (dependant on the adjusted threshold)	Smart Task name		Base logics
On delay Off delay ON and OFF delay Impulse (one shot) Inverter Yes Switching frequency SIO Direct: 1000 Hz ¹⁾ SIO Logic: 600 Hz ²⁾ IOL: 450 Hz ³⁾ Response time SIO Direct: 300 μs 450 μs ¹⁾ SIO Logic: 750 μs 900 μs ²⁾ IOL: 800 μs 1200 μs ³⁾ Repeatability SIO Direct: 150 μs ¹⁾ SIO Logic: 150 μs ²⁾ IOL: 400 μs ³⁾ Switching signal Switching signal Output type (dependant on the adjusted threshold)	Logic function		AND OR WINDOW
Switching frequency $SIO \ Direct: 1000 \ Hz^{-1} \\ SIO \ Logic: 600 \ Hz^{-2} \\ IOL: 450 \ Hz^{-3})$ Response time $SIO \ Direct: 300 \ \mu s \dots 450 \ \mu s^{-1} \\ SIO \ Logic: 750 \ \mu s \dots 900 \ \mu s^{-2} \\ IOL: 800 \ \mu s \dots 1200 \ \mu s^{-3})$ Repeatability $SIO \ Direct: 150 \ \mu s^{-1} \\ SIO \ Logic: 150 \ \mu s^{-2} \\ IOL: 400 \ \mu s^{-3})$ Switching signal $Switching \ signal \ Q_{L1}$ Output type (dependant on the adjusted threshold)	Timer function		On delay Off delay ON and OFF delay
SIO Logic: 600 Hz^{2}) $10L: 450 \text{ Hz}^{3}$ Response time $SIO \text{ Direct: } 300 \text{ µs } 450 \text{ µs}^{1}$ $SIO \text{ Logic: } 750 \text{ µs } 900 \text{ µs}^{2}$ $10L: 800 \text{ µs } 1200 \text{ µs}^{3}$ Repeatability $SIO \text{ Direct: } 150 \text{ µs}^{1}$ $SIO \text{ Logic: } 150 \text{ µs}^{2}$ $10L: 400 \text{ µs}^{3}$ Switching signal $Switching \text{ signal } Q_{L1}$ Output type (dependant on the adjusted threshold)	Inverter		Yes
SIO Logic: $750 \ \mu s \dots 900 \ \mu s^{2}$) IOL: $800 \ \mu s \dots 1200 \ \mu s^{3}$) Repeatability SIO Direct: $150 \ \mu s^{1}$) SIO Logic: $150 \ \mu s^{2}$) IOL: $400 \ \mu s^{3}$) Switching signal Switching signal Q _{L1} Output type (dependant on the adjusted threshold)	Switching frequency		SIO Logic: 600 Hz ²⁾
Since Direct. 156 μ s Since Direct. 156 μ	Response time		SIO Logic: 750 μs 900 μs ²⁾
Switching signal Q _{L1} Output type (dependant on the adjusted threshold)	Repeatability		SIO Logic: 150 μ s ²⁾
	Switching signal		
Switching signal Q _{L2} Output type (dependant on the adjusted threshold)		Switching signal Q_{L1}	Output type (dependant on the adjusted threshold)
		Switching signal Q _{L2}	Output type (dependant on the adjusted threshold)

¹⁾ SIO Direct: sensor operation in standard I/O mode without IO-Link communication and without using internal sensor logic or time parameters (set to "direct"/"deactivated").

²⁾ SIO Logic: Sensor operation in standard I/O mode without IO-Link communication. Sensor-internal logic or timing parameters plus Automation Functions used.


³⁾ IOL: Sensor operation with full IO-Link communication and usage of logic, timing and Automation Function parameters.

Diagnosis

Device status	Yes
Classifications	
ECLASS 5.0	27270904
ECLASS 5.1.4	27270904
ECLASS 6.0	27270904
ECLASS 6.2	27270904
ECLASS 7.0	27270904
ECLASS 8.0	27270904
ECLASS 8.1	27270904
ECLASS 9.0	27270904
ECLASS 10.0	27270904
ECLASS 11.0	27270904
ECLASS 12.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528

Adjustments

Single teach-in button




- ③ LED indicator yellow: Status of received light beam
- 4 LED indicator green: power on
- ® Teach-in button

Connection diagram

Cd-367

Characteristic curve

% of sensing range




Sensing range in mm (inch)

- ① Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor③ Sensing range on white, 90% remission factor

Light spot size

Radius in mm (inch)




Dimensions in mm (inch)

Sensing range	Vertical	Horizontal
50 mm	1.2	1.0
(1.97)	(0.05)	(0.04)
100 mm	1.1	1.0
(3.94)	(0.04)	(0.04)
200 mm	0.9	0.9
(7.87)	(0.04)	(0.04)
300 mm	0.8	0.8
(11.81)	(0.03)	(0.03)

Vertical
Horizontal


Sensing range diagram



- Sensing range typ. max.
- ① Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- 3 Sensing range on white, 90% remission factor

Dimensional drawing (Dimensions in mm (inch))

WTB9L-3



- ① Center of optical axis, receiver
- ② Center of optical axis, sender
- 3 Mounting hole M3 (Ø 3.1 mm)
- 4 LED indicator yellow: Status of received light beam
- ⑤ LED indicator green: power on
- © Connecting cable or connecting cable with connector
- 7 Male connector M8, 4-pin
- Male connector M12, 4-pin

Recommended accessories

Other models and accessories → www.sick.com/W9

	Brief description	Туре	Part no.
Mounting bra	ckets and plates		
0-2	Mounting bracket, steel, zinc coated, mounting hardware included	BEF-WN-W9-2	2022855
Plug connecto	ors and cables		
	Head A: female connector, M12, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m	YF2A14- 050VB3XLEAX	2096235
	Head A: male connector, M12, 4-pin, straight Cable: unshielded	STE-1204-G	6009932

Recommended services

Additional services → www.sick.com/W9

	Туре	Part no.
Function Block Factory		
 Description: The Function Block Factory supports common programmable logic controllers (PLCs) from various manufacturers, such as Siemens, Beckhoff, Rockwell Automation and B&R. More information on the FBF can be found here. Note: You can configure your function block at Function Block Factory. As a login please use your SICK ID. 	Function Block Factory	On request

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

