



# SIM2000-2P04G10

SIM2x00

EDGE COMPUTING DEVICES

**SICK**  
Sensor Intelligence.



### Ordering information

Type	part no.
SIM2000-2P04G10	1081902

Other models and accessories → [www.sick.com/SIM2x00](http://www.sick.com/SIM2x00)



### Detailed technical data

#### Features

<b>Product category</b>	Programmable
<b>Generation</b>	Second generation
<b>Supported products</b>	2D and 3D cameras from SICK or based on the GigE machine vision standard 2D and 3D LiDAR sensors Image-based code readers Bar code scanners RFID read/write device Displacement measurement sensors Incremental and absolute encoders Photoelectric sensors
<b>Processor</b>	8-core ARM Cortex-A72 CPU with NEON accelerator
<b>Random Access Memory</b>	4 GB DDR4
<b>Flash memory</b>	7 GB eMMC, of which 5 GB are available for applications
<b>Programming software</b>	SICK AppStudio Can be programmed within the SICK AppSpace environment
<b>Toolkit</b>	SICK algorithm API
<b>Further functions</b>	FPGA for I/O handling Dedicated fieldbus controller

#### Mechanics/electronics

<b>Connections</b>	I/O, Power, SERIAL, INC, Fieldbus, CAN, SENSOR S1-S4, SENSOR S5-S6, Ethernet with PoE, USB	1 x M12, 8-pin female connector, A-coded, 1 x M12, 4-pin male connector, T-coded, 1 x M12, 8-pin female connector, A-coded, 1 x M12, 8-pin female connector, A-coded, 2 x M12, 4-pin female connector, D-coded, 1 x M12, 5-pin female connector, A-coded, 4 x M12, 5-pin female connector, A-coded, 2 x M12, 5-pin female connector, A-coded, 4 x M12, 8-pin female connector, X-coded, 1 x Micro-B, Under the servicing panel, Under the servicing panel
<b>Supply voltage</b>		24 V DC, ± 10 %
<b>Power consumption</b>		Typ. 45 W, without connected sensor
<b>Power output</b>		140 W, total, all connections
<b>Output current</b>		
	SENSOR S1-S4	≤ 1 A (on power supply pin)
	SENSOR S5-S6	≤ 2.5 A (on power supply pin)

SENSOR S5-S6	≤ 3.2 A (≤ 10 kHz, rise time/fall time/delay < 10µs when power gate-API used)
CAN	≤ 1 A (on power supply pin)
SERIAL	≤ 0.5 A (on power supply pin)
INC	≤ 500 mA (on power supply pin)
I/O	≤ 500 mA (on power supply pin)
<b>Enclosure rating</b>	IP65
<b>Protection class</b>	III
<b>Electrical safety</b>	EN 61010
<b>Housing material</b>	Aluminum die cast
<b>Housing color</b>	Light blue (RAL 5012)
<b>Weight</b>	1,995 g
<b>Dimensions (L x W x H)</b>	176 mm x 83 mm x 196 mm

## Interfaces

<b>Ethernet</b>	✓ (4) , TCP/IP, FTP, OPC UA, MQTT
Type of fieldbus integration	GigE machine vision/GenICAM
Remark	Fieldbus ports, in preparation
Function	Data output, Configuration, firmware update, image transmission
Data transmission rate	20 kbit/s ... 230 kBaud, 10/100/1,000/2,500 Mbit/s
<b>PROFINET</b>	✓ (2) , RS-232, RS-422, RS-485
Remark	Fieldbus-Ports
Function	Dual port Ethernet-based fieldbus, Also configurable as RS-422, firmware update
Data transmission rate	≤ 1 Mbit/s, 10/100 MBit/s
<b>EtherNet/IP™</b>	✓ (2) , RS-422
Remark	Fieldbus ports, in preparation
Function	Dual port Ethernet-based fieldbus, diagnosis
Data transmission rate	10/100 MBit/s
<b>EtherCAT®</b>	✓ (2) , USB 2.0
Remark	SENSOR S1-S4
Function	Dual port Ethernet-based fieldbus
Data transmission rate	10/100 MBit/s
<b>IO-Link</b>	✓ (4) , RS-232
Remark	SENSOR S1-S4
Function	IO-Link Master 1.1
Data transmission rate	RS-232: 115,2 kBaud, RS-422/RS-485: 2 MBaud
<b>Serial</b>	✓ , RS-422
Function	Can also be configured as an encoder interface, max. frequency 2 MHz
Data transmission rate	Max. frequency 2 MHz; RS-422: 2 MBaud
<b>Incremental</b>	✓ (4)
Function	Interface for encoder
<b>CAN</b>	✓
Function	SICK CAN sensor network CSN (CAN controller/CAN device, multiplexer/server) with activatable termination resistor

<b>USB</b>		✓
	Function	For configuration
<b>Operator interfaces</b>		Web server (GUI), SICK AppStudio (programming), SICK AppManager (app installation, firmware update)
<b>Data storage and retrieval</b>		Image and data logging via optional microSD memory card, internal RAM and external FTP
<b>Memory card(s)</b>		Industry-grade microSD memory card (flash card), max. 32 GB, optional
<b>Digital inputs/outputs</b>		
	I/O	2 opto-decoupled inputs (Max. frequency: 30 kHz)
	I/O	2 inputs/outputs (can be configured) (Max. frequency: 30 kHz)
	SENSOR S1-S4	1 input each (Max. frequency: 30 kHz)
	SENSOR S1-S4	1 input/output each (can be configured) (Max. frequency: 30 kHz)
	SENSOR S5-S6	1 input each (Max. frequency: 10 kHz)
	SENSOR S5-S6	2 inputs/outputs each (can be configured) (Max. frequency: 30 kHz)
<b>Control elements</b>		1 selector switch (under the servicing panel) 1 functional button (under the servicing panel)

### Ambient data

<b>Electromagnetic compatibility (EMC)</b>	IEC 61000-6-2:2016 EN IEC 61000-6-2:2019 IEC 61000-6-3:2020
<b>Shock load</b>	IEC 60068-2-27:2008
<b>Ambient operating temperature</b>	0 °C ... +50 °C <sup>1) 2)</sup>
<b>Ambient temperature, storage</b>	-20 °C ... +70 °C <sup>1)</sup>

<sup>1)</sup> Permissible relative humidity: 0% ... 90% (non-condensing).

<sup>2)</sup> While taking account of the mounting requirements described, see operating instructions. In the event of overtemperature, the device protects itself by resetting and then restarting.

### Certificates

<b>EU declaration of conformity</b>	✓
<b>UK declaration of conformity</b>	✓
<b>ACMA declaration of conformity</b>	✓
<b>China RoHS</b>	✓

### Classifications

<b>ECLASS 5.0</b>	27242208
<b>ECLASS 5.1.4</b>	27242608
<b>ECLASS 6.0</b>	27242608
<b>ECLASS 6.2</b>	27242608
<b>ECLASS 7.0</b>	27242608
<b>ECLASS 8.0</b>	27242608
<b>ECLASS 8.1</b>	27242608
<b>ECLASS 9.0</b>	27242608
<b>ECLASS 10.0</b>	27242608
<b>ECLASS 12.0</b>	27244090
<b>ETIM 5.0</b>	EC001604
<b>ETIM 6.0</b>	EC001604

<b>ETIM 7.0</b>	EC001604
<b>ETIM 8.0</b>	EC001604
<b>UNSPSC 16.0901</b>	32151705

Overview SICK AppSpace



## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)