


# MDA650 2,5 Image

Master Data Analyzer

TRACK AND TRACE SYSTEMS

**SICK**  
Sensor Intelligence.



### Ordering information

Type	part no.
MDA650 2,5 Image	1087607

Other models and accessories → [www.sick.com/Master\\_Data\\_Analyzer](http://www.sick.com/Master_Data_Analyzer)

### Detailed technical data

#### Features

<b>Products by tasks</b>	Measuring - Dimension, contour and volume Measuring - Weight Identifying - 1D code Identifying - 2D code
<b>Sensor resolution</b>	1 Mpixel
<b>Including image recording</b>	✓
<b>Object infeed and outfeed</b>	Manual
<b>Color image properties</b>	Standard resolution (1080p UWW)
<b>Legal-for-trade</b>	No

#### Mechanics/electronics

<b>Dimensions, system (L x W x H)</b>	1,210 mm x 900 mm x 900 mm
<b>Enclosure rating</b>	IP20
<b>Supply voltage</b>	24 V DC <sup>1)</sup>
<b>Panel PC</b>	7" touch display (800 x 600 RGB)
<b>Trigger</b>	Manual for code scanning
<b>Total weight</b>	90 kg
<b>External power supply</b>	AC 100 V ... 240 V, 50 Hz ... 60 Hz

<sup>1)</sup> SELV.

#### Performance

<b>Code types</b>	1D 2D Stacked code PDF417 Aztec 4-state Maxi-Code
<b>Minimum object size</b>	10 mm x 10 mm x 5 mm
<b>Maximum object size</b>	640 mm x 590 mm x 590 mm
<b>Throughput</b>	900 pph
<b>Accuracy of object coverage</b>	± 2.5 mm
<b>Accuracy of scale</b>	d = 5 g (40 g ... 15 kg), d = 10 g (15 kg ... 30 kg)

## Interfaces

<b>Ethernet</b>	✓ , TCP/IP, FTP
<b>Output data</b>	Maximum dimensions (length, width, height) of Minimum Bounding Box Volume (the minimum bounding box) Code data Weight Custom fields (up to 3) Status Image output in .jpg Data output in .txt, other formats like .csv, .xml etc. on request (customer-specific)

## Ambient data

<b>Permissible relative humidity</b>	≤ 90 %, Non-condensing
--------------------------------------	------------------------


## General notes

<b>Items supplied</b>	IP camera Power supply unit MDA-Basis inkl. MLG-2 Pro (2 x) Integrated weighing cells (4 x) Handheld scanner
-----------------------	--

## Classifications

<b>ECLASS 5.0</b>	27281001
<b>ECLASS 5.1.4</b>	27280190
<b>ECLASS 6.0</b>	27280190
<b>ECLASS 6.2</b>	27280190
<b>ECLASS 7.0</b>	27280190
<b>ECLASS 8.0</b>	27280190
<b>ECLASS 8.1</b>	27280190
<b>ECLASS 9.0</b>	27280190
<b>ECLASS 10.0</b>	27280190
<b>ECLASS 11.0</b>	27280190
<b>ECLASS 12.0</b>	27280190
<b>UNSPSC 16.0901</b>	43211701

Dimensional drawing



Dimensions in mm (inch)

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

**For us, that is “Sensor Intelligence.”**

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)