



FLX0-GCAN100

Flexi Compact

SAFETY CONTROLLERS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
FLX0-GCAN100	1085363

Other models and accessories → www.sick.com/Flexi_Compact



Detailed technical data

Features

Module	Gateway
Description	The gateway module enables a safety controller to send data to a network for control and diagnostic purposes, and to receive data from the network.
Security Level	SL-C 1 (IEC 62443-4-2)
Fieldbus	CANopen
Configuration method	Via software (Safety Designer)
Items supplied	Gateway Operating instructions for download

Interfaces

Configuration and diagnostics	
Configuration via TFT display	✓
Fieldbus	CANopen
Fieldbus interface	Male connector, D-Sub, 9-pin
Display elements	TFT display

Electronics

Protection class	III (EN 61140)
Interference resistance	EN 61000-6-2
Interference emission	EN 61000-6-4
Voltage supply	The voltage supply of the extension modules is maintained via the backplane bus
Power loss	≤ 2.1 W
Current consumption at nominal voltage	85 mA

Mechanics

Dimensions (W x H x D)	18 mm x 124.7 mm x 85.5 mm
Contamination rating	2 (IEC 61010-1)

Control device type	Open device (IEC 61010-2-201)
Weight	105 g (± 5 %)
Mounting	Mounting on a 35 mm × 7.5 mm mounting rail in accordance with IEC 60715

Ambient data

Enclosure rating	IP20 (EN 60529)
Ambient operating temperature	–25 °C ... +55 °C ¹⁾
Storage temperature	–25 °C ... +70 °C
Air humidity	≤ 95 %, Non-condensing
Vibration resistance	1 g, 5 Hz ... 200 Hz (EN 60068-2-6)
Shock resistance	15 g, 11 ms (EN 60068-2-27)

¹⁾ At altitudes up to 2,000 m above sea level For higher areas of application up to max. 4,000 m above sea level, see the operating instructions.


Certificates

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
China RoHS	✓
cULus certificate	✓
Information according to Art. 3 of Data Act (Regulation EU 2023/2854)	✓
Cybersecurity certificate	✓

Classifications

ECLASS 5.0	27243001
ECLASS 5.1.4	27243101
ECLASS 6.0	27243101
ECLASS 6.2	27243101
ECLASS 7.0	27243101
ECLASS 8.0	27243101
ECLASS 8.1	27243101
ECLASS 9.0	27243101
ECLASS 10.0	27243101
ECLASS 11.0	27243101
ECLASS 12.0	27243101
ETIM 5.0	EC001449
ETIM 6.0	EC001449
ETIM 7.0	EC001449
ETIM 8.0	EC001449
UNSPSC 16.0901	32151705



Dimensional drawing GCAN1 gateway



Dimensions in mm (inch)

Recommended accessories

Other models and accessories → www.sick.com/Flexi_Compact

	Brief description	Type	part no.
Safety relays			
	<ul style="list-style-type: none">• Applications: Output expansion module for OSSDs• Compatible sensor types: Safety sensors with OSSDs• Connection type: Front connector with spring terminals• Restart interlock: no• External device monitoring (EDM): Via path• Outputs: 4 enabling current paths (safe), 1 feedback current path (for use as external device monitoring, not safe), 1 signaling current path (not safe)• Housing width: 28 mm	RLY3-OSSD400	1099971
	<ul style="list-style-type: none">• Applications: Output expansion module for OSSDs• Compatible sensor types: Safety sensors with OSSDs• Connection type: Front connector with spring terminals• Restart interlock: no• External device monitoring (EDM): Via path• Outputs: 2 enabling current paths (safe), 1 feedback current path (for use as external device monitoring, not safe)• Housing width: 18 mm	RLY3-OSSD100	1085343

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com