

M2C-EA04300A10

deTem

SAFETY MULTIBEAM SENSORS



Ordering information

deTem2 Core

Number of beams	Beam separation	System part	Туре	Part no.
4	300 mm	Receiver	M2C-EA04300A10	1085570

Other models and accessories → www.sick.com/deTem





Detailed technical data

Features

Application	Normal industrial environment
Functional principle	Sender/receiver
System part	Receiver
Number of beams	4
Beam separation	300 mm
Response time	20 ms
Synchronization	Optical synchronisation
Items supplied	Receiver Safety instruction Mounting instructions Operating instructions for download

Safety-related parameters

Туре	Type 2 (IEC 61496-1)
Safety integrity level	SIL 1 (IEC 61508)
Category	Category 2 (ISO 13849-1)
Performance level	PL c (ISO 13849-1)
$\mbox{PFH}_{\mbox{\scriptsize D}}$ (mean probability of a dangerous failure per hour)	3 x 10 ⁻⁹
T _M (mission time)	20 years (ISO 13849-1)
Safe state in the event of a fault	At least one OSSD is in the OFF state.

Interfaces

System connection	Male connector M12, 5-pin
Flexi Loop compatible M12 male connector	√
Permitted cable length	50 m
Display elements	LEDs

Electrical data

Protection class	III (IEC 61140) ¹⁾
Supply voltage $V_{\rm S}$	24 V DC (19.2 V DC 28.8 V DC) ²⁾
Residual ripple	≤ 10 % ³⁾
Power consumption	≤ 150 mA
Power consumption	≤ 4.32 W (DC)
Output signal switching devices (OSSDs)	2 PNP semiconductors, short-circuit protected, cross-circuit monitored ⁴⁾
ON state, switching voltage HIGH	24 V DC (V _S - 2.25 V DC V _S)
OFF state, switching voltage LOW	≤ 2 V DC
Current-carrying capacity per OSSD	≤ 300 mA

 $^{^{1)}\,\}mbox{SELV/PELV}$ safety/protective extra-low voltage.

Mechanical data

Dimensions	See dimensional drawing
Housing cross-section	31 mm x 34 mm
Material	
Housing	Aluminum extruded profile
Front screen	Polycarbonate, scratch-resistant coating
Weight	880 g (± 50 g)
Cable bend radius	
Stationary position	> 12 x cable diameter
Flexible use	> 15 x cable diameter

Ambient data

Enclosure rating	IP65 (IEC 60529) IP67 (IEC 60529)
Ambient operating temperature	-30 °C +55 °C
Storage temperature	-30 °C +70 °C
Air humidity	15 % 95 %, Non-condensing
Vibration resistance	5 g, 10 Hz 55 Hz (IEC 60068-2-6)
Shock resistance	10 g, 16 ms (IEC 60068-2-27)

Classifications

eCl@ss 5.0	27272703
eCl@ss 5.1.4	27272703
eCl@ss 6.0	27272703
eCl@ss 6.2	27272703
eCl@ss 7.0	27272703
eCl@ss 8.0	27272703
eCl@ss 8.1	27272703
eCl@ss 9.0	27272703

²⁾ The external voltage supply must be capable of buffering brief mains voltage failures of 20 ms as specified in EN 60204-1. Suitable power supplies are available as accessories from SICK.


 $^{^{\}rm 3)}$ Within the limits of Vs.

 $^{^{\}rm 4)}$ Applies to the voltage range between –30 V and +30 V.

SAFETY MULTIBEAM SENSORS

eCl@ss 10.0	27272703
eCl@ss 11.0	27272703
eCl@ss 12.0	27272703
ETIM 5.0	EC001832
ETIM 6.0	EC001832
ETIM 7.0	EC001832
ETIM 8.0	EC001832
UNSPSC 16.0901	46171620

Dimensional drawing (Dimensions in mm (inch))



① Optical axis

Number of beams	Beam separation S	Length L
2	500 (19.69)	672 (26.46)
3	400 (15.75)	972 (38.27)
4	300 (11.81)	1,072 (42.2)

Recommended accessories

Other models and accessories → www.sick.com/deTem

	Brief description	Туре	Part no.		
Plug connecto	Plug connectors and cables				
No.	Head A: female connector, M12, 5-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 2 m	YF2A15-020UB5XLEAX	2095617		
	Head A: female connector, M12, 5-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 5 m	YF2A15-050UB5XLEAX	2095618		

	Brief description	Туре	Part no.
	•		
	Head A: female connector, M12, 5-pin, straight, A-coded Head B: Flying leads	YF2A15-100UB5XLEAX	2095619
	Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 10 m		
	Head A: female connector, M12, 5-pin, straight, A-coded	YF2A15-020UB5M2A15	2096009
100 NO	Head B: male connector, M12, 5-pin, straight, A-coded	2/12/ 02/02/01/12/12/	200000
•	Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 2 m		
	Head A: female connector, M12, 5-pin, straight, A-coded	YF2A15-050UB5M2A15	2096010
	Head B: male connector, M12, 5-pin, straight, A-coded Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 5 m		
	Head A: female connector, M12, 5-pin, straight, A-coded Head B: male connector, M12, 5-pin, straight, A-coded	YF2A15-100UB5M2A15	2096011
	Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 10 m		
Terminal and	alignment brackets		
	4 pieces, FlexFix bracket for 2 devices (e.g. sender and receiver), can be aligned	BEF-1SHABPKU4	2066614
(Carlo)	± 15°, including M5 screw, plastic	DEI 13HABER04	2000014
	4 pieces, QuickFix bracket for 2 devices (e.g. sender and receiver), plastic	BEF-3SHABPKU4	2098710
No.	· process, quient in analysis and a second in a recent strip, process	52. 55 5	2000.20
1			
Safety switch	ing amplifier		
<u> </u>	Applications: Evaluation unit	RLY3-OSSD200	1085344
	Compatible sensor types: Safety sensors with OSSDs		
	Connection type: Front connector with spring terminals Restart interlock: yes		
	External device monitoring (EDM): Integrated		
	Outputs: 2 enabling current paths (safe), 2 application diagnostic outputs (not		
	safe), 1 test pulse output (not safe) • Housing width: 18 mm		
		DIVO 000D000	1000000
	 Applications: Evaluation unit Compatible sensor types: Safety sensors with OSSDs 	RLY3-OSSD300	1099969
	Connection type: Front connector with spring terminals		
•	Restart interlock: yes		
	 External device monitoring (EDM): Integrated Outputs: 3 enabling current paths (safe), 2 application diagnostic outputs (not 		
	safe), 1 test pulse output (not safe)		
	Housing width: 18 mm		

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

