

MICS3-AAAZ90AZ1 microScan3

SAFETY LASER SCANNERS



MICS3-AAAZ90AZ1 | microScan3

SAFETY LASER SCANNERS



Ordering information

Integra- tion in the control system	Sub prod- uct family	Protective field range	Number of fields	Number of monitor- ing cases	Connec- tion type	Туре	Part no.
Local inputs and out- puts (I/O)	microS- can3 Core I/O	9 m	8	2	M12	MICS3- AAAZ90AZ1	1089325

Illustration may differ

Replacement sensor without system plug; only functional in combination with system plug;

Replacement sensor for 1089492

Other models and accessories → www.sick.com/microScan3



Detailed technical data

Features

Cub and duct family	
Sub product family	microScan3 Core I/O
Model	Sensor without system plug
Application	Indoor
Protective field range	9 m
Warning field range	64 m
Number of simultaneously monitored fields	< 4 ^{1) 2)}
Number of fields	8 ³⁾
Number of monitoring cases	2
Scanning angle	275°
Resolution (can be configured)	30 mm 40 mm 50 mm 60 mm 70 mm 150 mm 200 mm
Angular resolution	0.1°
Response time	≥ 90 ms
Protective field supplement	100 mm

 $^{1)}\ensuremath{\mathsf{Protection}}$, warning or contour detection fields.

 $^{\rm 2)}$ Please note the number of available OSSD pairs.

 $^{\rm 3)}$ Please note the number of available inputs and OSSD pairs.

MICS3-AAAZ90AZ1 | microScan3

SAFETY LASER SCANNERS

Safety-related parameters

Safety-related parameters			
Туре	Type 3 (IEC 61496)		
Safety integrity level	SIL 2 (IEC 61508)		
Category	Category 3 (EN ISO 13849)		
Performance level	PL d (EN ISO 13849)		
$\ensuremath{PFH}_{\ensuremath{D}}$ (mean probability of a dangerous failure per hour)	8.0 x 10 ⁻⁸		
T _M (mission time)	20 years (EN ISO 13849)		
Safe state in the event of a fault	At least one OSSD is in the OFF state.		
Functions			
Restart interlock	1		
External device monitoring (EDM)	1		
Multiple sampling	1		
Monitoring case switching	✓		
Simultaneous monitoring	✓		
Static protective field switching	✓		
Safe contour detection	✓		
Contour as a reference	✓		
Integrated configuration memory	\checkmark		
Measured data output	None		
Interfaces			
Connection type	Male connector, M12, 8 pin, A-coded (common male connector for power supply and inputs and outputs)		
Universal I/Os	3		
Outputs			
OSSD pairs	1		
Configuration method	PC with Safety Designer (Configuration and Diagnostic Software)		
Configuration and diagnostics interface	USB 2.0, Mini-USB		
Display elements	Graphic color display, LEDs		
Electrical data			
Protection class	III (EN 61140)		
Supply voltage V _s	24 V DC (16.8 V DC 30 V DC)		
Power consumption typical	7 W (without output load)		
Mechanical data			
Housing material	Aluminum		
Housing color	RAL 1021 (yellow), RAL 9005 (black)		
Optics cover material	Polycarbonate		
Optics cover surface finish	Outside with scratch-resistant coating		
Ambient data			
Enclosure rating	IP65 (IEC 60529)		

2024-04-25 15:42:24 | Product data sheet Subject to change without notice

MICS3-AAAZ90AZ1 | microScan3

SAFETY LASER SCANNERS

Ambient light immunity	≤ 3,000 lx (IEC 61496-3)		
Ambient operating temperature	-10 °C +50 °C		
Storage temperature	-25 °C +70 °C		
Vibration resistance	IEC 60068-2-6, IEC 60068-2-64, IEC 60721-3-5, IEC TR 60721-4-3, IEC 61496-1, IEC 61496-3		
Class	5M1 (IEC 60721-3-5) 3M4 (IEC TR 60721-4-3)		
Shock resistance	IEC 60068-2-27, IEC 60721-3-5, IEC TR 60721-4-3, IEC 61496-1, IEC 61496-3		
Class	5M1 (IEC 60721-3-5) 3M4 (IEC TR 60721-4-3)		
Continuous shock	100 m/s², 16 ms 150 m/s², 6 ms		
EMC	IEC 61496-1, IEC 61000-6-2, IEC 61000-6-4		
Other information			
Type of light	Pulsed laser diode		
Wave length	845 nm		
Detectable remission factor	1.8% to several 1000%		
Laser class	1M (21 CFR 1040.10 and 1040.11, IEC 60825-1)		
Classifications			
ECLASS 5.0	27272705		
ECLASS 5.1.4	27272705		
ECLASS 6.0	27272705		
ECLASS 6.2	27272705		
ECLASS 7.0	27272705		
ECLASS 8.0	27272705		
ECLASS 8.1	27272705		
ECLASS 9.0	27272705		
ECLASS 10.0	27272705		
ECLASS 11.0	27272705		
ECLASS 12.0	27272705		
ETIM 5.0	EC002550		
ETIM 6.0	EC002550		
ETIM 7.0	EC002550		
ETIM 8.0	EC002550		
UNSPSC 16.0901	39121528		

Pin assignment



Pin	Designation	Description	
1	+24 V DC	Supply voltage +24 V DC	
2	OSSD 1.A	OSSD pair 1, OSSD A	
3	0 V DC	Supply voltage 0 V DC	
4	OSSD 1.B	OSSD pair 1, OSSD B	
5	Uni-I/O 1	Universal I/O 1, configurable	
6	Uni-I/O 2	Universal I/O 2, configurable	
7	Uni-I/O 3	Universal I/O 3, configurable	
8	FE	Functional earth/shielding	
For dataile can operating instructions			

For details see operating instructions

Recommended accessories

Other models and accessories -> www.sick.com/microScan3

	Brief description	Туре	Part no.			
Mounting brackets and plates						
	1 piece, mounting bracket with protection of optics hood, Stainless steel V2A (1.4301), powder-coated IGP-DURA face 5803A	1b mounting kit	2074242			
-	1 piece, mounting bracket, heavy-duty version, with protection cover, for floor mounting, height adjustment possible from 90 310 mm, scanner tilt angle: \pm 5°. Additional mounting brackets are not required. \subseteq , steel, painted (RAL 1021)	Heavy-duty mounting kit for floor mounting	2102289			
	1 piece, mounting bracket 150 mm for floor mounting of microScan3, stainless steel, Bracket and 4 x M5 screws for attaching the microScan3	Mounting bracket 150 mm for floor mount- ing of microScan3	2112950			
R	1 piece, mounting bracket 300 mm for floor mounting of microScan3, stainless steel, Bracket and $4\ x\ M5$ screws for attaching the microScan3	Mounting bracket 300 mm for floor mount- ing of microScan3	2112951			
	1 piece, mounting bracket, Stainless steel V2A (1.4301), powder-coated IGP-DURA face 5803A	Mounting kit 1a	2073851			
	1 piece, alignment bracket, alignment with cross-wise axis and depth axis possible, distance between mounting surface and device: 22.3 mm, only in conjunction with mounting kit 1a (2073851) or 1b (2074242), Stainless steel V2A (1.4301), powder-coated IGP-DURA face 5803A	Mounting kit 2a	2073852			
Plug connectors and cables						
	 Connection type head A: Female connector, M12, 8-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 8-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Application: Zones with oils and lubricants, Drag chain operation 	DOL-1208G02MD25KM1	2079314			

MICS3-AAAZ90AZ1 | microScan3 SAFETY LASER SCANNERS

Brief description	Туре	Part no.
 Connection type head A: Female connector, M12, 8-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 8-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Application: Zones with oils and lubricants, Drag chain operation 	DOL-1208G05MD25KM1	2079315
 Connection type head A: Female connector, M12, 8-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 10 m, 8-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Application: Zones with oils and lubricants, Drag chain operation 	DOL-1208G10MD25KM1	2079316
 Connection type head A: Female connector, M12, 8-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 20 m, 8-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Application: Zones with oils and lubricants, Drag chain operation 	DOL-1208G20MD25KM1	2092105
 Connection type head A: Female connector, M12, 8-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 30 m, 8-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Application: Zones with oils and lubricants, Drag chain operation 	DOL-1208G30MD25KM1	2092106
 Connection type head A: Male connector, USB-A, straight Connection type head B: Male connector, Mini-USB, straight Signal type: USB Cable: 3 m, 4-wire Description: USB, shielded Note: For connecting the configuration connection to the USB interface on the PC 	Connection cable (male connector- male connector)	6042517
 Connection type head A: Male connector, USB-A, straight Connection type head B: Male connector, Mini-USB, straight Signal type: USB Cable: 5 m, 4-wire Description: USB, shielded Note: For connecting the configuration connection to the USB interface on the PC 		6053566
 Connection type head A: System plug Description: Integrated configuration memory, system connection; cable 250 mm with M12 male connector, 8-pin 	MICSX-ABIZZZZ1	2073156

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

