

# FC1A-DZ2A1A

FlexChain

**SWITCHING AUTOMATION LIGHT GRIDS** 





Illustration may differ

## Ordering information

Туре	Part no.
FC1A-DZ2A1A	1091611

Included in delivery: M8 4-PIN BUS CONNECTION MALE CONNECTOR (2)

Other models and accessories → www.sick.com/FlexChain



#### Detailed technical data

#### **Features**

Device version	FlexChain Host
Sensor principle	Sender/receiver Photoelectric retro-reflective sensor Photoelectric proximity sensor Light grid system
Configuration	${\tt USB\ connection\ for\ easy\ configuration\ of\ the\ FlexChain\ with\ SOPAS\ ET,\ the\ engineering\ tool\ from\ SICK}$
Parameterization	Sensor parameterization Zone definition Measurement functions Logic function Interface parameterization Diagnostics functions
Included with delivery	1 × FlexChain Host 1 × Quick Start Guide 2 x FlexChain terminators (2119481)

## Mechanics/electronics

Supply voltage $V_{\rm s}$	24 V <sup>1) 2)</sup>
Current consumption I <sub>max.</sub> (at maximum number of guests)	600 mA @ 24 V
Output current I <sub>max.</sub>	≤ 100 mA
Output load, capacitive	100 μF
Output load, Inductive	1 H
Initialization time	<1s
Dimensions (W x H x D)	109.4 mm x 25 mm x 35 mm
Connection type	Cable with plug M12, 5-pin <sup>3) 4)</sup>
Housing material	Plastic (ABS)

<sup>1) ± 20 %.</sup> 

 $<sup>^{2)}</sup>$  Reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

<sup>3)</sup> PLC communication control.

<sup>&</sup>lt;sup>4)</sup> 2x cables.

Synchronization	Cable
Enclosure rating	IP65, IP67
Circuit protection	U <sub>V</sub> connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression
Protection class	III
Weight	Approx. 170 g

<sup>1) ± 20 %.</sup> 

#### Performance

Response time ≤ 38	5 ms <sup>1)</sup>
--------------------	--------------------

<sup>1)</sup> Depending on system configuration.

## Communication interface

IO-Link	<b>√</b> , IO-Link V1.1
Data transmission rate	230,4 kbit/s (COM3)
Cycle time	≥ 2.3 ms
Process data length	32 Byte
CANopen	✓
Data transmission rate	50 kbit/s1 Mbit/s
Inputs/outputs	CANopen + 1 x I/O + 1 x Q (IO-Link)
Digital output	$Q_1, Q_2$
Number	2
Digital input	$ln_1$
Number	1

#### Ambient data

Shock resistance	Single shocks 30 g, 11 ms 6 per axle, continuous shocks 25 g, 6 ms, 1,000 per axis		
Vibration resistance	Sinusoidal oscillation 20-2,000 Hz 10 g, 3 h per axle		
EMC	EN 61000-6-2, EN 61000-6-3		
Ambient operating temperature	-25 °C +50 °C		
Ambient temperature, storage	-25 °C +70 °C		

## Smart Task

Smart Task name	Base logics

#### Classifications

ECLASS 5.0	27242608
ECLASS 5.1.4	27242608
ECLASS 6.0	27242608
ECLASS 6.2	27242608
ECLASS 7.0	27242608
ECLASS 8.0	27242608
ECLASS 8.1	27242608


 $<sup>^{2)}</sup>$  Reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

<sup>3)</sup> PLC communication control.

<sup>&</sup>lt;sup>4)</sup> 2x cables.


ECLASS 9.0	27242608
ECLASS 10.0	27242608
ECLASS 11.0	27242608
ECLASS 12.0	27242608
ETIM 5.0	EC001604
ETIM 6.0	EC001604
ETIM 7.0	EC001604
ETIM 8.0	EC001604
UNSPSC 16.0901	39121528

#### Dimensional drawing (Dimensions in mm (inch))



- ① Port A, cable with female connector, M8, 4-pin
- ② Port B, cable with female connector, M8, 4-pin
- ③ PLC, cable with male connector, M12, 5-pin
- 4 CANopen, cable with male connector, M12, 5-pin
- ⑤ USB Micro-B, cable with female connector, M16, 5-pin
- 6 Control panel

#### Connection type and diagram



#### Recommended accessories

Other models and accessories → www.sick.com/FlexChain

	Brief description	Туре	Part no.	
Connection m	Connection modules			
1118	FlexChain Adapter	FCA-A1Z2A1AZ	6073035	
1111	FlexChain Booster	FCA-BZZ2A1A1	6073036	
Plug connecto	ors and cables			
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 10 m, 5-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A15- 100VB5XLEAX	2096241	
100	<ul> <li>Connection type head A: Male connector, USB-A</li> <li>Connection type head B: Male connector, Micro-B</li> <li>Signal type: USB 2.0</li> <li>Cable: 2 m</li> <li>Description: USB 2.0, unshielded</li> </ul>	USB cable	6036106	
10 to	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Male connector, M12, 5-pin, straight, A-coded</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 10 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YF2A15- 100UB5M2A15	2096011	
	<ul> <li>Connection type head A: Male connector, M12, 5-pin, straight</li> <li>Signal type: CANopen</li> <li>Description: CANopen, unshielded, CAN male connector, with terminating resistor</li> </ul>	CAN male connector	6021167	
Sensor Integr	ration Gateway			
	<ul> <li>Further functions: Web server integrated, USB connection for easy configuration of the SIG200 Sensor Integration Gateway with SOPAS ET, the engineering tool from SICK, logic editor is available for easy configuration of logic functions</li> <li>Connection CONFIG: 1 x M8, 4-pin female connector, USB 2.0 (USB-A)</li> <li>Logic editor: yes</li> <li>Communication interface: IO-Link, USB, Ethernet, PROFINET, REST API</li> <li>Product category: IO-Link Master</li> </ul>	SIG200-0A0412200	1089794	
OS AND	<ul> <li>Further functions: Web server integrated, USB connection for easy configuration of the SIG200 Sensor Integration Gateway with SOPAS ET, the engineering tool from SICK, logic editor is available for easy configuration of logic functions</li> <li>Connection CONFIG: 1 x M8, 4-pin female connector, USB 2.0 (USB-A)</li> <li>Logic editor: yes</li> <li>Communication interface: IO-Link, USB, Ethernet, REST API</li> <li>Product category: IO-Link Master</li> </ul>	SIG200-0A0G12200	1102605	

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

