



V3S153-2AAAAAAP02

Visionary-B

3D MACHINE VISION

SICK
Sensor Intelligence.



Illustration may differ



Ordering information

Type	part no.
V3S153-2AAAAAAP02	1091808

Other models and accessories → www.sick.com/Visionary-B

Detailed technical data

Features

Task	Position determination Collision awareness
Technology	3D snapshot stereoscopy
Product category	Configurable, Streaming, pre-calibrated
Working distance	0.5 m ... 7 m
Detection angle	120° x 75°
Illumination	No internal illumination necessary, works only with ambient light
Factory calibrated	✓
Detection zone	6 m × 7 m for standard configuration
Further functions	2D camera integrated
Description	2 x sensor head, 1 x evaluation unit, 1 x 7" monitor, assembly accessories

Mechanics/electronics

Connection type	1 x USB (mouse and keyboard) 2 x sensor head Monitor (VGA/sound) Additional alarm output; two discrete outputs Machine-to-machine interface (reserved) Ethernet (reserved) Evaluation unit supply
Supply voltage	12 V DC, - 10 % 24 V DC, 40 % ¹⁾
Power consumption	≤ 35 W, Kit B
Output current	12 V (100 mA (max. overcurrent protection 430 mA))
Enclosure rating	IP69K IP67
Weight	1.3 kg, sensor head 3.8 kg, evaluation unit
Mounting	Height 1 m ... 2.4 m, angle according to the detection zone

¹⁾ Ensure harmonic-free supply voltage.

Performance

Detectable object shape	See HMI and operating instruction
--------------------------------	-----------------------------------

¹⁾ Typical.

On delay	< 50 s
Response time	< 200 ms ¹⁾
Integrated application	3D driver assistance system for collision warning outdoors, image capturing option integrated

¹⁾ Typical.

Interfaces

Configuration software	Via provided monitor
-------------------------------	----------------------

Ambient data

Electromagnetic compatibility (EMC)	EN 55016-2-3:2010 + A1:2011 + A2:2014 (interference immunity) / EN 55012:2008-06 + A1:2009 (radiated emission)
Fulfilled standards	ISO 13766:2006-05 (earth-moving machinery), EN 12895:2015-09 (industrial trucks), EN 13309:2010-09 (construction machinery), ISO 14982:2009-02 (agricultural and forestry machinery), ISO 7637-2:2011-03, ISO 16750-2:2012-11, ISO16001:2017, EN 62311:2008, FCC PART 15:2006-08
Shock load	EN 60068-2-29:1994-01 (50 g / 6 ms)
Vibration load	EN 60068-2-64:2008-11 (5,9 g / 10 Hz - 2 kHz)
Ambient operating temperature	-40 °C ... +75 °C, sensor head -40 °C ... +50 °C, evaluation unit
Ambient light immunity	200 lx ... 80,000 lx

Certificates

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
China RoHS	✓

Classifications

ECLASS 5.0	27310205
ECLASS 5.1.4	27310205
ECLASS 6.0	27310205
ECLASS 6.2	27310205
ECLASS 7.0	27310205
ECLASS 8.0	27310205
ECLASS 8.1	27310205
ECLASS 9.0	27310205
ECLASS 10.0	27310205
ECLASS 11.0	27310205
ECLASS 12.0	27310205
ETIM 5.0	EC001820
ETIM 6.0	EC001820
ETIM 7.0	EC001820
ETIM 8.0	EC001820
UNSPSC 16.0901	43211731

Dimensions in mm (inch)

The technical drawing includes three views of the power supply unit:


- Front View (Top Left):** Shows the main face of the unit with eight circular ports labeled 1 through 8. Dimensions include a width of 276,9 [10,9] mm and a height of 91,3 [3,59] mm.
- Side View (Bottom Left):** Shows the profile of the unit with mounting brackets. Dimensions include a total width of 258,9 [10,19] mm, a mounting bracket width of 30 [1,18] mm, a distance between brackets of 80 [3,15] mm, and a total height of 190 [7,48] mm.
- Top View (Right):** Shows the top surface of the unit with dimensions of 85 [3,35] mm in width and 221 [8,7] mm in depth.

Dimensions in mm (inch)

- 4 MACHINE VISION | SICK


- ③ M14, 9-pin machine interface (Kit C)
- ④ M14, 2-pin external power supply (reserved, not implemented)
- ⑤ M14, 4-pin, additional alarm output
- ⑥ Bayonet, 10-pin sensor head, female
- ⑦ Bayonet, 10-pin sensor head, male
- ⑧ M14, 9-pin VGA/sound

Dimensional drawing Monitor




Dimensions in mm (inch)

Field of view




Mounting height (m)	1.0	1.2	1.4	1.6	1.8	2.0	2.2	2.4
Mounting angle (°)	0	-6	-11	-17	-23	-29	-31	-33

Field of view




Connection diagram Visionary-B CV, kit B



two sensors operate by-turns. Keyboard and cable sets are not included in any kit.

Functional principle Detection volumes and 2D measuring ranges



Working distance absolute (z)	Measuring range (Δx)	Measuring range (Δy)	2D image pixel size (x × y)
0.5 m	1.73 m	0.77 m	2 mm × 1 mm
1.0 m	3.46 m	1.53 m	4 mm × 3 mm
1.5 m	5.20 m	2.30 m	6 mm × 4 mm
2.0 m	6.93 m	3.07 m	8 mm × 6 mm
3.0 m	10.39 m	4.60 m	13 mm × 8 mm
4.0 m	13.86 m	6.14 m	17 mm × 11 mm
5.0 m	17.32 m	7.67 m	21 mm × 14 mm
10.0 m	34.64 m	15.35 m	42 mm × 28 mm
15.0 m	51.96 m	23.02 m	63 mm × 42 mm
20.0 m	69.28 m	30.69 m	84 mm × 56 mm

Working distance absolute (z)	Measuring range (Δx)	Measuring range (Δy)	2D image pixel size (x × y)
40.0 m	138.56 m	61.39 m	167 mm × 113 mm

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com