



**SAFETY LASER SCANNERS** 



### MICS3-ACAZ90PZ1 | microScan3

SAFETY LASER SCANNERS



Illustration may differ

### Ordering information

Integra- tion in the control system	Sub prod- uct family	Protective field range	Number of fields	Number of monitor- ing cases	Connec- tion type	Туре	Part no.
PROFINET PROFIsafe	microS- can3 Core - PROFINET	9 m	8	8	RJ45 push- pull AIDA	MICS3- ACAZ90PZ1	1094458

Replacement sensor without system plug; only functional in combination with system plug;

Replacement sensor for 1094459

Other models and accessories → www.sick.com/microScan3



### Detailed technical data

#### Features

Sub product family	microScan3 Core - PROFINET
Model	Sensor without system plug
Application	Indoor
Protective field range	9 m
Warning field range	64 m
Number of simultaneously monitored fields	< 4 <sup>1)</sup>
Number of fields	8
Number of monitoring cases	8
Scanning angle	275°
Resolution (can be configured)	30 mm 40 mm 50 mm 60 mm 70 mm 150 mm 200 mm
Angular resolution	0.1°
Response time	≥ 115 ms
Protective field supplement	100 mm

<sup>1)</sup> Protection, warning or contour detection fields.

Safety-related parameters

Туре	Type 3 (IEC 61496)
Safety integrity level	SIL 2 (IEC 61508)

## MICS3-ACAZ90PZ1 | microScan3 SAFETY LASER SCANNERS

Category	Category 3 (EN ISO 13849)
Performance level	PL d (EN ISO 13849)
$\ensuremath{PFH}_{\ensuremath{D}}$ (mean probability of a dangerous failure per hour)	8.0 x 10 <sup>-8</sup>
T <sub>M</sub> (mission time)	20 years (EN ISO 13849)
Safe state in the event of a fault	The safety outputs via the network are logic 0.
Functions	
Restart interlock	✓
Multiple sampling	✓
Monitoring case switching	✓
Simultaneous monitoring	✓
Static protective field switching	✓
Safe contour detection	✓
Contour as a reference	✓
Integrated configuration memory	✓
Measured data output	Via Ethernet

#### Interfaces

Interfaces	
Connection type	
Voltage supply	1 x male connector, M12, 5-pin, L-coded
Fieldbus, industrial network	2 x female connector, RJ45 for push-pull male connector (copper)
Outputs	
OSSD pairs	0
Safety outputs via network	4
Configuration method	PC with Safety Designer (Configuration and Diagnostic Software)
Configuration and diagnostics interface	USB 2.0, Mini-USB, Ethernet
Fieldbus, industrial network	PROFINET
Protocol	PROFIsafe
Supported protocol versions	PROFINET specification V2.3 PROFIsafe profile in accordance with specification V2.6.1 PROFIsafe profile in accordance with specification V2.4
GSDML	According to GSDML specification V2.33
Cycle time	1 ms, 2 ms, 4 ms, 8 ms, 16 ms
Conformance	Conformance Class C
Network management	SNMP MIB-2 LLDP in accordance with IEEE 802.1AB MRP client support
Net load	Net load class III in accordance with security level 1 test
Switch properties	2 port real-time switch compliant with IEEE 802
Port properties	100Base-TX Auto-negotiation Auto-crossover (MDIX) Auto-polarity
Diagnostics	I&M data sets 0 5 PROFINET alarms
Additional services	PROFlenergy

# MICS3-ACAZ90PZ1 | microScan3 SAFETY LASER SCANNERS

	F_iPar_CRC Acyclic read-/write services for communication via TCI SNTP (client and server)	
Additional interfaces	TCP/IP communication via port 9000	
Display elements	Graphic color display, LEDs	
Electrical data		
Protection class	III (EN 61140)	
Supply voltage V <sub>s</sub>	24 V DC (16.8 V DC 30 V DC)	
Power consumption typical	7.2 W	
Mechanical data		
Dimensions (W x H x D)	112 mm x 163.1 mm x 111.1 mm	
Housing material	Aluminum	
Housing color	RAL 1021 (yellow), RAL 9005 (black)	
Optics cover material	Polycarbonate	
Optics cover surface finish	Outside with scratch-resistant coating	
Ambient data		
Enclosure rating	IP65 (IEC 60529)	
Ambient light immunity	≤ 3,000 lx (IEC 61496-3)	
Ambient operating temperature	-10 °C +50 °C	
Storage temperature	-25 °C +70 °C	
Vibration resistance	IEC 60068-2-6, IEC 60068-2-64, IEC 60721-3-5, IEC TR 60721-4-3, IEC 61496-1, IEC 61496-3	
Class	5M1 (IEC 60721-3-5) 3M4 (IEC TR 60721-4-3)	
Shock resistance	IEC 60068-2-27, IEC 60721-3-5, IEC TR 60721-4-3, IEC 61496-1, IEC 61496-3	
Class	5M1 (IEC 60721-3-5) 3M4 (IEC TR 60721-4-3)	
Continuous shock	100 m/s², 16 ms 150 m/s², 6 ms	
EMC	IEC 61496-1, IEC 61000-6-2, IEC 61000-6-4	
Other information		
Type of light	Pulsed laser diode	
Wave length	845 nm	
Detectable remission factor	1.8% to several 1000%	
Laser class	1M (21 CFR 1040.10 and 1040.11, IEC 60825-1)	
Classifications		
ECLASS 5.0	27272705	
ECLASS 5.1.4	27272705	
ECLASS 6.0	27272705	
ECLASS 6.2	27272705	
ECLASS 7.0	27272705	
ECLASS 8.0	27272705	
ECLASS 8.1	27272705	

## MICS3-ACAZ90PZ1 | microScan3

SAFETY LASER SCANNERS

ECLASS 9.0	27272705
ECLASS 10.0	27272705
ECLASS 11.0	27272705
ECLASS 12.0	27272705
ETIM 5.0	EC002550
ETIM 6.0	EC002550
ETIM 7.0	EC002550
ETIM 8.0	EC002550
UNSPSC 16.0901	39121528


### Pin assignment

Ethernet



Pin	Designation	Description	
1	TX+	Send data +	
2	TX-	Send data -	
3	RX+	Receive data +	
4	-	Reserved	
5	-	Reserved	
6	RX-	Receive data -	
7	-	Reserved	
8	-	Reserved	
Housing	SH	Shielding	
For details see operating instructions			

Voltage supply



$\underline{2}$ $\underbrace{3}$				
Pin	Designation	Description		
1	+24 V DC	Supply voltage +24 V DC		
2	n.c.	Not connected		
3	0 V DC	Supply voltage 0 V DC		
4	n.c.	Not connected		
5	FE	Functional earth/shielding		
For details see operating instructions				

## MICS3-ACAZ90PZ1 | microScan3

SAFETY LASER SCANNERS

#### **Recommended accessories**

Other models and accessories → www.sick.com/microScan3

	Brief description	Туре	Part no.
Mounting brac	skets and plates		_
	1 piece, mounting bracket with protection of optics hood, Stainless steel V2A (1.4301), powder-coated IGP-DURA face 5803A	1b mounting kit	2074242
-	1 piece, mounting bracket, heavy-duty version, with protection cover, for floor mounting, height adjustment possible from 90 310 mm, scanner tilt angle: $\pm$ 5°. Additional mounting brackets are not required. <sup>G</sup> , steel, painted (RAL 1021)	Heavy-duty mounting kit for floor mounting	2102289
	1 piece, mounting bracket 150 mm for floor mounting of microScan3, stainless steel, Bracket and 4 x M5 screws for attaching the microScan3	Mounting bracket 150 mm for floor mount- ing of microScan3	2112950
R	1 piece, mounting bracket 300 mm for floor mounting of microScan3, stainless steel, Bracket and 4 x M5 screws for attaching the microScan3	Mounting bracket 300 mm for floor mount- ing of microScan3	2112951
	1 piece, mounting bracket, Stainless steel V2A (1.4301), powder-coated IGP-DURA face 5803A	Mounting kit 1a	2073851
	1 piece, alignment bracket, alignment with cross-wise axis and depth axis possible, distance between mounting surface and device: 22.3 mm, only in conjunction with mounting kit 1a (2073851) or 1b (2074242), Stainless steel V2A (1.4301), powder-coated IGP-DURA face 5803A	Mounting kit 2a	2073852
	1 piece, Alignment bracket, alignment with cross-wise axis and depth axis possible, distance between mounting surface and device: 52.3 mm, only in conjunction with mounting kit 1a (2073851) or 1b (2074242), Stainless steel V2A (1.4301), powder-coated IGP-DURA face 5803A	Mounting kit 2b	2074184
Plug connecto	rs and cables		
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, L-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Drag chain operation</li> </ul>	YF2L15-020UH1XLEAX	2099599
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, L-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Drag chain operation</li> </ul>	YF2L15-050UH1XLEAX	2099626
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, L-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 10 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Drag chain operation</li> </ul>	YF2L15-100UH1XLEAX	2099627
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, L-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 20 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Drag chain operation</li> </ul>	YF2L15-200UH1XLEAX	2099628

# MICS3-ACAZ90PZ1 | microScan3 SAFETY LASER SCANNERS

	Brief description	Туре	Part no.
	<ul> <li>Connection type head A: System plug</li> <li>Description: Integrated configuration memory, System connection: voltage supply: 1 x M12 male connector, 5-pin, L-coded, EtherNet: 2 x RJ45 female connector for push-pull male connector (copper)</li> </ul>	MICSX-CPNNZZZZ1	2087905
Others			
	<ul> <li>Brief description: The software visualizes diagnostic and device information from safety laser scanners in real time, helping to identify error causes faster and reduce maintenance time.</li> <li>Supported products: All microScan3 variants (except for microScan3 Core I/O variants), outdoorScan3 Pro - EtherNet/IP</li> <li>Version: 1.0</li> <li>Note: With purchase, you accept the product description available under Downloads &gt; Documentation in connection with the <a href="https://www.sick.com/tools/tac/en/General-Terms-Conditions-Supply-Software-Products-AVB-Software-SICK.pdf" target="_blank">General Terms and Conditions for the Supply of Software Products (AVB Software SICK)</a>., With purchase, you accept the product description available under Downloads &gt; Documentation in connection with the <a href="https://www.sick.com/tools/tac/en/General-Terms-Conditions-Supply-Software-Products-AVB-Software-SICK.pdf" target="_blank">General Terms and Conditions for the Supply of Software Products (AVB Software SICK)</a>., With purchase, you accept the product description available under Downloads &gt; Documentation in connection with the <a href="https://www.sick.com/tools/tac/en/General-Terms-Conditions-Supply-Software-Products-AVB-Software-SICK.pdf" target="_blank">General-Terms-Conditions for the Supply of Software Products (AVB Software SICK)</a>.</li> </ul>	SOW/VTL-LI007PCWI0	1116788

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

## WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

