

M2C-EX04300A10

deTem

SAFETY MULTIBEAM SENSORS





Ordering information

deTem2 Core Ex II 3GD

| Number of beams | Beam separation | System part | Туре | Part no. |
|-----------------|-----------------|-------------|----------------|----------|
| 4 | 300 mm | Receiver | M2C-EX04300A10 | 1093909 |

Other models and accessories → www.sick.com/deTem

Illustration may differ



Detailed technical data

Features

| Application | Explosive areas |
|----------------------|---|
| Ex-approvals | ATEX for gas: II 3G Ex ec op is IIC T4 Gc ATEX for dust: II 3D Ex tc IIIC T135°C Dc |
| Functional principle | Sender/receiver |
| System part | Receiver |
| Number of beams | 4 |
| Beam separation | 300 mm |
| Response time | 20 ms |
| Synchronization | Optical synchronisation |
| Items supplied | Receiver "Notes for explosion protection" label(s) Safety instruction Mounting instructions Operating instructions for download |

Safety-related parameters

| Туре | Type 2 (IEC 61496-1) |
|---|--|
| Safety integrity level | SIL 1 (IEC 61508) |
| Category | Category 2 (ISO 13849-1) |
| Performance level | PL c (ISO 13849-1) |
| $\ensuremath{PFH_D}$ (mean probability of a dangerous failure per hour) | 3 x 10 ⁻⁹ |
| T _M (mission time) | 20 years (ISO 13849-1) |
| Safe state in the event of a fault | At least one OSSD is in the OFF state. |

Functions

Protective operation

| Interfaces | |
|-------------------|---------------------------|
| System connection | Male connector M12, 5-pin |
| Display elements | LEDs |

Electrical data

| Protection class | III (IEC 61140) |
|---|--|
| Supply voltage V _S | 24 V DC (19.2 V DC 28.8 V DC) ¹⁾ |
| Residual ripple | ≤ 10 % ²⁾ |
| Power consumption | ≤ 150 mA |
| Power consumption | ≤ 4.32 W (DC) |
| Output signal switching devices (OSSDs) | 2 PNP semiconductors, short-circuit protected, cross-circuit monitored ³⁾ |
| ON state, switching voltage HIGH | 24 V DC (V _S - 2.25 V DC V _S) |
| OFF state, switching voltage LOW | ≤ 2 V DC |
| Current-carrying capacity per OSSD | ≤ 300 mA |

¹⁾ The external voltage supply must be capable of buffering brief mains voltage failures of 20 ms as specified in EN 60204-1. Suitable power supplies are available as accessories from SICK.

Mechanical data

| Dimensions | See dimensional drawing |
|-----------------------|---------------------------|
| Housing cross-section | 38.7 mm x 45.6 mm |
| Material | |
| Housing | Aluminum extruded profile |
| Weight | 880 g (± 50 g) |
| Cable bend radius | |
| Stationary position | > 12 x cable diameter |
| Flexible use | > 15 x cable diameter |

Ambient data

| Enclosure rating | IP65 (IEC 60529) IP67 (IEC 60529) |
|-------------------------------|--------------------------------------|
| Ambient operating temperature | 0 °C +55 °C |
| Storage temperature | -30 °C +70 °C |
| Air humidity | 15 % 95 %, Non-condensing |
| Vibration resistance | 5 g, 10 Hz 55 Hz (IEC 60068-2-6) |
| Shock resistance | 10 g, 16 ms (IEC 60068-2-27) |

Other information

| Type of light | Near-infrared (NIR), invisible |
|---------------|--------------------------------|
| | |

Classifications

| eCl@ss 5.0 | 27272703 |
|--------------|----------|
| eCl@ss 5.1.4 | 27272703 |


 $^{^{2)}}$ Within the limits of $\mbox{\rm V}_{\mbox{\scriptsize S}}.$


 $^{^{3)}}$ Applies to the voltage range between $\mbox{-30 V}$ and $\mbox{+30 V}.$

SAFETY MULTIBEAM SENSORS

| eCl@ss 6.0 | 27272703 |
|----------------|----------|
| eCl@ss 6.2 | 27272703 |
| eCl@ss 7.0 | 27272703 |
| eCl@ss 8.0 | 27272703 |
| eCl@ss 8.1 | 27272703 |
| eCl@ss 9.0 | 27272703 |
| eCl@ss 10.0 | 27272703 |
| eCl@ss 11.0 | 27272703 |
| eCl@ss 12.0 | 27272703 |
| ETIM 5.0 | EC001832 |
| ETIM 6.0 | EC001832 |
| ETIM 7.0 | EC001832 |
| ETIM 8.0 | EC001832 |
| UNSPSC 16.0901 | 46171620 |

Dimensional drawing (Dimensions in mm (inch))





- ① Operating indicator
- ② Alignment indicator③ Optical axis

| Number of beams | Beam separation S | Length L |
|-----------------|-------------------|-------------|
| 2 | 500 (19.69) | 672 (26.46) |

| Number of beams | Beam separation S | Length L |
|-----------------|-------------------|--------------|
| 3 | 400 (15.75) | 972 (38.27) |
| 4 | 300 (11.81) | 1,072 (42.2) |

Recommended accessories

Other models and accessories → www.sick.com/deTem

| | Brief description | Туре | Part no. |
|--|--|--------------------|----------|
| Distributors | | | |
| | Head A: female connector, M12, 5-pin, A-coded Head B: male connector, M12, 5-pin, A-coded 5-pin | DSC-1205T000025KM0 | 6030664 |
| Plug connect | ors and cables | | |
| | Head A: female connector, M12, 5-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 2 m | YF2A15-020UB5XLEAX | 2095617 |
| | Head A: female connector, M12, 5-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 5 m | YF2A15-050UB5XLEAX | 2095618 |
| | Head A: female connector, M12, 5-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 10 m | YF2A15-100UB5XLEAX | 2095619 |
| No No | Head A: female connector, M12, 5-pin, straight, A-coded Head B: male connector, M12, 5-pin, straight, A-coded Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 2 m | YF2A15-020UB5M2A15 | 2096009 |
| | Head A: female connector, M12, 5-pin, straight, A-coded Head B: male connector, M12, 5-pin, straight, A-coded Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 5 m | YF2A15-050UB5M2A15 | 2096010 |
| | Head A: female connector, M12, 5-pin, straight, A-coded Head B: male connector, M12, 5-pin, straight, A-coded Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 10 m | YF2A15-100UB5M2A15 | 2096011 |
| Terminal and | alignment brackets | | |
| (Carlo) | 4 pieces, FlexFix bracket for 2 devices (e.g. sender and receiver), can be aligned \pm 15 $^{\circ}$, including M5 screw, plastic | BEF-1SHABPKU4 | 2066614 |
| NA STATE OF THE PARTY OF THE PA | 4 pieces, QuickFix bracket for 2 devices (e.g. sender and receiver), plastic | BEF-3SHABPKU4 | 2098710 |
| Safety switch | ing amplifier | | |
| | Applications: Evaluation unit Compatible sensor types: Safety sensors with OSSDs Connection type: Front connector with spring terminals Restart interlock: yes External device monitoring (EDM): Integrated Outputs: 2 enabling current paths (safe), 2 application diagnostic outputs (not safe), 1 test pulse output (not safe) Housing width: 18 mm | RLY3-OSSD200 | 1085344 |

M2C-EX04300A10 | deTem

SAFETY MULTIBEAM SENSORS

| Brief description | Туре | Part no. |
|--|--------------|----------|
| Applications: Evaluation unit Compatible sensor types: Safety sensors with OSSDs Connection type: Front connector with spring terminals Restart interlock: yes External device monitoring (EDM): Integrated Outputs: 3 enabling current paths (safe), 2 application diagnostic outputs (not safe), 1 test pulse output (not safe) Housing width: 18 mm | RLY3-OSSD300 | 1099969 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

