

GTB6-CC011K00 FlexChain

SWITCHING AUTOMATION LIGHT GRIDS



GTB6-CC011K00 | FlexChain

SWITCHING AUTOMATION LIGHT GRIDS



Ordering information

	Туре	Part no.	
	GTB6-CC011K00	1098784	
	Only in conjunction with FlexChain host		
	1091608 FC1A-AZ2A1A: Standard I/O		
	1091609 FC1A-BZ2A1A: Advanced I/O		
	1091610 FC1A-CZ2A1A: RS-485		
Illustration may differ	1091611 FC1A-DZ2A1A: CANopen		
	Other models and accessories www.sick.com/FlexChain		

Detailed technical data

Features

Device version	FlexChain Guest
Sensor principle	Photoelectric proximity sensor Light grid system
Mechanics/electronics	
Light source	PinPoint LED, visible red light
Light spot size (distance)	Ø 6 mm (100 mm)
Wave length	650 nm
Supply voltage V _s	12 V, via FlexChain (host)
Adjustment	Potentiometer (Sensitivity)
Dimensions (W x H x D)	12 mm x 31.5 mm x 21 mm
Connection type	Male connector M8, 4-pin, Cable with female connector, M8, 4-pin, 0.15 m
Housing material	Plastic (ABS)
Enclosure rating	IP65, IP67
Protection class	III
Weight	Approx. 23 g
Performance	
Operating range	0.25 m
Ambient data	
Shock resistance	Single shocks 30 g, 11 ms 6 per axle, continuous shocks 25 g, 6 ms, 1,000 per axis
Vibration resistance	Sinusoidal oscillation 20-2,000 Hz 10 g, 3 h per axle

EN 61000-6-2, EN 61000-6-3

¹⁾ Sunlight.

EMC

GTB6-CC011K00 | FlexChain SWITCHING AUTOMATION LIGHT GRIDS

Ambient light immunity	Direct: 9,000 lx ¹⁾
Ambient operating temperature	-25 °C +55 °C
Ambient temperature, storage	-25 °C +70 °C

¹⁾ Sunlight.


Classifications

ECLASS 5.0	27270903
ECLASS 5.1.4	27270903
ECLASS 6.0	27270903
ECLASS 6.2	27270903
ECLASS 7.0	27270903
ECLASS 8.0	27270903
ECLASS 8.1	27270903
ECLASS 9.0	27270903
ECLASS 10.0	27270903
ECLASS 11.0	27270903
ECLASS 12.0	27270903
ETIM 5.0	EC001821
ETIM 6.0	EC001821
ETIM 7.0	EC001821
ETIM 8.0	EC001821
UNSPSC 16.0901	39121528

GTB6-CC011K00 | FlexChain


SWITCHING AUTOMATION LIGHT GRIDS

Dimensional drawing (Dimensions in mm (inch))



- ① Center of optical axis, sender
- ② Center of optical axis, receiver
- ③ Threaded mounting hole M3
- ④ LED indicator green
- ⑤ LED indicator yellow

Connection type and diagram




- ② Cable with female connector, M8, 4-pin

Sensing distance

GTB6

% of sensing distance




① Object with 90% remission (based on standard white, DIN 5033)

② Sensing range on gray, 18% remission factor

③ Sensing range on black, 6% remission factor

Light spot size

GTB6




All dimensions in mm (inch)

GTB6-CC011K00 | FlexChain

SWITCHING AUTOMATION LIGHT GRIDS

Sensing range diagram

GTB6



Sensing range max. Sensing range

① Object with 90% remission (based on standard white, DIN 5033)

② Sensing range on gray, 18% remission factor

③ Sensing range on black, 6% remission factor

Recommended accessories

Other models and accessories -> www.sick.com/FlexChain

	Brief description	Туре	Part no.
Mounting brackets and plates			
	Stainless steel (1.4301)	BEF-WN-G6	2062909

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

