

RLY3-MULT100

ReLy

SAFETY RELAYS





Ordering information

Туре	Part no.
RLY3-MULT100	1100692

Other models and accessories → www.sick.com/ReLy

Illustration may differ





Detailed technical data

Features

Applications	Evaluation unit
Compatible sensor types	Safety sensors with OSSDs Safety sensors with test input Safety sensors with potential-free outputs Safety pressure mats

Safety-related parameters

Safety integrity level	SIL 3 (IEC 61508)
Category	Category 4 (ISO 13849-1)
Performance level	PL e (ISO 13849-1)
$\mbox{PFH}_{\mbox{\scriptsize D}}$ (mean probability of a dangerous failure per hour)	1.5 × 10 ⁻⁹
T _M (mission time)	20 years (ISO 13849-1)
Stop category	0 (IEC 60204-1)

Functions

Sensor monitoring	Discrepancy monitoring Sequence monitoring Cross-circuit detection
Restart interlock	√
Reset	Automatic Manual
External device monitoring (EDM)	✓

Interfaces

Connection type	Front connector with spring terminals
Inputs	2 safety inputs 1 input for reset pushbutton or external device monitoring (EDM)
Outputs	3 enabling current paths (safe) 2 application diagnostic outputs (not safe) 2 test pulse outputs (not safe)
Display elements	LEDs

Configuration method	Hard wired
	DIP switch

Electrical data

Operating data

Voltage supply	PELV or SELV
Supply voltage V_S	24 V DC (16.8 V 30 V)
Residual ripple	≤ 2.4 V
Power consumption	≤ 2.5 W (DC)

Safety inputs

Number	2
Input voltage	
HIGH	24 V DC (11 V 30 V)
LOW	0 V DC (-3 V 5 V)
Input current	4 mA 6 mA
Test pulse width	≤1 ms
Test pulse rate	≤ 10 Hz
Activation time tolerance between the two start buttons	≤3s

Reset pushbutton or external device monitoring (EDM) input

Number	1
Input voltage	
HIGH	24 V DC (11 V 30 V)
LOW	0 V DC (-3 V 5 V)
Input current	4 mA 6 mA

Enabling current paths

Response time	Depends on the configured sensor type, for details see operating instructions
Number	3
Type of output	N/O contacts, positively guided
Contact material	Silver alloy, gold flashed
Switching voltage	10 V AC 230 V AC 10 V DC 230 V DC
Switching current	10 mA 6 A
Total current	12 A
Mechanical life	1 x 10 ⁷ switching cycles
Overvoltage category	III (EN 60664-1)
Rated impulse withstand voltage U _{imp}	6 kV (EN 60664-1)

Application diagnostic outputs

Number	2
Type of output	Push-pull semiconductor output, short-circuit protected
Output voltage	
HIGH	≥ V _s - 3 V
LOW	≤ 3 V

Input current (NPN)	≤ 15 mA
Output current (PNP)	≤ 120 mA

Test pulse outputs

Number	2
Type of output	PNP semiconductors, short-circuit protected
Output voltage	≥ V _s - 3 V
Test pulse width	Depends on the configured sensor type ¹⁾
Test pulse interval	Depends on the configured sensor type, for details see operating instructions

 $^{^{1)}}$ For details see operating instructions.

Mechanical data

Dimensions (W x H x D)	18 mm x 124.6 mm x 85.5 mm
Weight	160 g

Ambient data


Enclosure rating	IP20 (IEC 60529)
Ambient operating temperature	-25 °C +55 °C
Storage temperature	-25 °C +70 °C
Air humidity	≤ 95 %, Non-condensing
Interference emission	According to IEC 61000-6-4
Interference resistance	According to IEC 61326-3-1 According to IEC 61000-6-2 According to IEC 60947-5-1

Classifications

eCl@ss 5.0	27371990
eCl@ss 5.1.4	27371990
eCl@ss 6.0	27371819
eCl@ss 6.2	27371819
eCl@ss 7.0	27371819
eCl@ss 8.0	27371819
eCl@ss 8.1	27371819
eCl@ss 9.0	27371819
eCl@ss 10.0	27371819
eCl@ss 11.0	27371819
eCl@ss 12.0	27371819
ETIM 5.0	EC001449
ETIM 6.0	EC001449
ETIM 7.0	EC001449
ETIM 8.0	EC001449
UNSPSC 16.0901	41113704

Dimensional drawing (Dimensions in mm (inch))

EMSS3, LOOP1, MULT1, OSSD3



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

