



**IME08-02BNSZWDSS59**

IME

INDUCTIVE PROXIMITY SENSORS

**SICK**  
Sensor Intelligence.



## Ordering information

| Type              | part no. |
|-------------------|----------|
| IME08-02BNSZWDS59 | 1115033  |

Other models and accessories → [www.sick.com/IME](http://www.sick.com/IME)

Illustration may differ



## Detailed technical data

## Features

|  |   |
|--|---|
| <b>Housing</b>                             | Metric                                      |
| <b>Housing</b>                             | Standard design                             |
| <b>Thread size</b>                         | M8 x 1                                      |
| <b>Diameter</b>                            | Ø 8 mm                                      |
| <b>Sensing range <math>S_n</math></b>      | 2 mm  |
| <b>Safe sensing range <math>S_a</math></b> | 1.62 mm                                     |
| <b>Installation type</b>                   | Flush                                       |
| <b>Switching frequency</b>                 | 4,000 Hz                                    |
| <b>Connection type</b>                     | Cable with AMP male connector, 3-pin, 0.2 m |
| <b>Switching output</b>                    | NPN   |
| <b>Switching output detail</b>             | NPN   |
| <b>Output function</b>                     | NO  |
| <b>Electrical wiring</b>                   | DC 3-wire                                   |
| <b>Enclosure rating</b>                    | IP67 <sup>1)</sup>                          |
| <b>Items supplied</b>                      | Mounting nut, steel, nickel-plated (2 x)    |

<sup>1)</sup> According to EN 60529.

## Mechanics/electronics

|                       |                     |
|-----------------------|---------------------|
| <b>Supply voltage</b> | 10 V DC ... 30 V DC |
| <b>Ripple</b>         | ≤ 10 %              |

<sup>1)</sup> At  $I_a$  max.

<sup>2)</sup> Supply voltage  $U_B$  and constant ambient temperature  $T_a$ .

<sup>3)</sup> Of  $S_r$ .

<sup>4)</sup> T drift +/-20% at -30 °C.

|  |  |
|--|--|
| <b>Voltage drop</b>                            | $\leq 2 \text{ V}$ <sup>1)</sup>           |
| <b>Time delay before availability</b>          | $\leq 100 \text{ ms}$                      |
| <b>Hysteresis</b>                              | 5 % ... 15 %                               |
| <b>Reproducibility</b>                         | $\leq 2 \%$ <sup>2)</sup><br><sup>3)</sup> |
| <b>Temperature drift (of <math>S_r</math>)</b> | $\pm 10 \%$                                |
| <b>EMC</b>                                     | According to EN 60947-5-2                  |
| <b>Continuous current <math>I_a</math></b>     | $\leq 200 \text{ mA}$                      |
| <b>No load current</b>                         | $\leq 10 \text{ mA}$                       |
| <b>Cable material</b>                          | PVC  |
| <b>Cable diameter</b>                          | $\varnothing 3.9 \text{ mm}$               |
| <b>Short-circuit protection</b>                | ✓  |
| <b>Power-up pulse protection</b>               | ✓  |
| <b>Shock and vibration resistance</b>          | 30 g, 11 ms/10 Hz ... 55 Hz, 1 mm          |
| <b>Ambient operating temperature</b>           | -30 °C ... +75 °C <sup>4)</sup>            |
| <b>Housing material</b>                        | Brass, nickel-plated                       |
| <b>Sensing face material</b>                   | Plastic, PA 66                             |
| <b>Housing length</b>                          | 71.5 mm                                    |
| <b>Thread length</b>                           | 52.5 mm                                    |
| <b>Tightening torque, max.</b>                 | $\leq 5 \text{ Nm}$                        |
| <b>UL File No.</b>                             | NRKH.E181493                               |

1) At  $I_a$  max.

2) Supply voltage  $U_B$  and constant ambient temperature  $T_a$ .

3) Of  $S_r$ .

4) T drift +/-20% at -30 °C.

#### Safety-related parameters

|                                     |             |
|-------------------------------------|-------------|
| <b>MTTF<sub>D</sub></b>             | 1,735 years |
| <b>DC<sub>avg</sub></b>             | 0 %         |
| <b>T<sub>M</sub> (mission time)</b> | 20 years    |

#### Reduction factors

|                                   |  |
|-----------------------------------|--|
| <b>Note</b>                       | The values are reference values which may vary |
| <b>St37 steel (Fe)</b>            | 1  |
| <b>Stainless steel (V2A, 304)</b> | Approx. 0.8                                    |
| <b>Aluminum (Al)</b>              | Approx. 0.45                                   |
| <b>Copper (Cu)</b>                | Approx. 0.4                                    |
| <b>Brass (Br)</b>                 | Approx. 0.4                                    |

#### Installation note

|               |                                       |
|---------------|---------------------------------------|
| <b>Remark</b> | Associated graphic see "Installation" |
| <b>B</b>      | 16 mm                                 |
| <b>C</b>      | 8 mm                                  |
| <b>D</b>      | 6 mm                                  |

|          |       |
|----------|-------|
| <b>F</b> | 16 mm |
|----------|-------|



## Classifications

|                       |          |
|-----------------------|----------|
| <b>ECLASS 5.0</b>     | 27270101 |
| <b>ECLASS 5.1.4</b>   | 27270101 |
| <b>ECLASS 6.0</b>     | 27270101 |
| <b>ECLASS 6.2</b>     | 27270101 |
| <b>ECLASS 7.0</b>     | 27270101 |
| <b>ECLASS 8.0</b>     | 27270101 |
| <b>ECLASS 8.1</b>     | 27270101 |
| <b>ECLASS 9.0</b>     | 27270101 |
| <b>ECLASS 10.0</b>    | 27270101 |
| <b>ECLASS 11.0</b>    | 27270101 |
| <b>ECLASS 12.0</b>    | 27274001 |
| <b>ETIM 5.0</b>       | EC002714 |
| <b>ETIM 6.0</b>       | EC002714 |
| <b>ETIM 7.0</b>       | EC002714 |
| <b>ETIM 8.0</b>       | EC002714 |
| <b>UNSPSC 16.0901</b> | 39122230 |


## Certificates

|   |   |
|---|---|
| <b>EU declaration of conformity</b>       | ✓ |
| <b>UK declaration of conformity</b>       | ✓ |
| <b>ACMA declaration of conformity</b>     | ✓ |
| <b>Moroccan declaration of conformity</b> | ✓ |
| <b>China RoHS</b>                         | ✓ |
| <b>cULus certificate</b>                  | ✓ |


## Installation note Flush installation



Connection diagram Cd-240



Dimensional drawing IME08, advanced, cable with male connector, flush



## Recommended accessories

Other models and accessories → [www.sick.com/IME](http://www.sick.com/IME)

|   | <b>Brief description</b>   | <b>Type</b> | <b>part no.</b> |
|---|--|-------------|-----------------|
| Mounting systems  |  |             |                 |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Clamping block for round sensors M8, with fixed stop</li> <li><b>Material:</b> Plastic</li> <li><b>Details:</b> Plastic (PA12), glass-fiber reinforced</li> <li><b>Items supplied:</b> Mounting hardware included</li> </ul>    | BEF-KHF-M08 | 2051478         |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Clamping block for round sensors M8, without fixed stop</li> <li><b>Material:</b> Plastic</li> <li><b>Details:</b> Plastic (PA12), glass-fiber reinforced</li> <li><b>Items supplied:</b> Mounting hardware included</li> </ul> | BEF-KH-M08  | 2051477         |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Mounting bracket for M8 sensors</li> <li><b>Material:</b> Steel</li> <li><b>Details:</b> Steel, zinc coated</li> <li><b>Items supplied:</b> Without mounting hardware</li> </ul>  | BEF-WN-M08  | 5321721         |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Mounting plate for M8 sensors</li> <li><b>Material:</b> Steel</li> <li><b>Details:</b> Steel, zinc coated</li> <li><b>Items supplied:</b> Without mounting hardware</li> </ul>  | BEF-WG-M08  | 5321722         |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

**For us, that is "Sensor Intelligence."**

## WORLDWIDE PRESENCE:

Contacts and other locations [www.sick.com](http://www.sick.com)