



DATA SHEET

SIG300-0A04AA100

SIG300
Network devices

SICK

Sensor Intelligence


NETWORK DEVICES

SIG300-OA04AA100

ORDERING INFORMATION

Type	part no.
SIG300-OA04AA100	1131011

Further device versions and accessories at www.sick.com/SIG300



DETAILED TECHNICAL DATA

FEATURES

Product category	IO-Link Master
Supported products	IO-Link Devices Binary switching sensors Binary actuators
Further functions	Web server integrated IIoT interface available
MTTF	29.4 years ¹⁾
MTTFd	58.8 years ¹⁾
Items supplied	SIG300, safety instruction, Blind plugs (9 x M12, 1 x USB-C)

¹⁾ The specified values are estimates. These are not exact calculations.

MECHANICS/ELECTRONICS

Connections	IO-Link	8 x M12, 5-pin female connector, A-coded
	Power	1 x M12, 5-pin male connector, L-coded

¹⁾ Each for U_N and U_A , typ. supply voltage 24 V DC.

²⁾ $\leq +40$ °C (see "Derating" information in operating instructions).

³⁾ Without load, sensors and outputs switched off.

⁴⁾ SF.

⁵⁾ BF.

⁶⁾ When using a SELV or PELV power supply unit.

	Ethernet	1 x M12, 5-pin female connector, L-coded
	USB-C	2 x M12, 4-pin female connector, D-coded 1 x USB-C
Power voltage supply	Supply voltage	20 V DC ... 30 V DC ¹⁾
	Current carrying capacity (PWR1, PWR2) max.	$\leq 16 \text{ A}, U_s$ ²⁾ $\leq 16 \text{ A}, U_A$ ²⁾
Current consumption		$\leq 200 \text{ mA}$ ³⁾
Total current (S1 ... S8)		$\leq 15.5 \text{ A}$ ²⁾
Pin assignment for class A port (S1-S6)	Pin 1 (L+) (Us)	2 A
	Pin 2 (DI/DO)	200 mA
	Pin 3 (M)	- 2.6 A
	Pin 4 (C/Q DI/DO)	200 mA
	Pin 5 (DI/DO) Port 5-6	200 mA
Pin assignment for class B port (S7-S8)	Pin 1 (L+) (Us)	2 A
	Pin 2 (L+) (UA)	2 A
	Pin 3 (M) (Us)	- 2 A
	Pin 4 (C/Q DI/DO)	200 mA
	Pin 5 (M) (UA)	- 2 A
Digital inputs	Number	16, configurable
	Input characteristics	EN 6131-2 type 1
	Circuit protection	Short-circuit protected
Digital outputs	Number	16, configurable
	Type	PNP NPN Push-Pull
	Switching frequency	$\leq 50 \text{ Hz}$
	Circuit protection	Short-circuit protected
Optical indicators		8 LED green (IO-Link activity pin 4) 6 LED yellow (DI/DO communication pin 2) 2 LED yellow (DI/DO communication pin 5) 2 LED yellow (Voltage supply U_A "On" pin 2, class B port) 2 LED green (Ethernet bus activity) 1 LED green (voltage supply U_s (sensors)) 1 LED green (voltage supply U_A (actuators)) 1 LED red/green ⁴⁾ 1 LED red/green ⁵⁾
Enclosure rating		IP67 (In fastened condition)
Protection class		III ⁶⁾
Contamination rating		2
Housing material		Polyamide + steel, galvanized
Housing color		Dark gray
Weight		460 g
Dimensions (L x W x H)		191.4 mm x 61.2 mm x 27.3 mm
UL File No.		E497722

¹⁾ Each for U_s and U_A , typ. supply voltage 24 V DC.

²⁾ $\leq +40 \text{ °C}$ (see "Derating" information in operating instructions).

³⁾ Without load, sensors and outputs switched off.

⁴⁾ SF.

⁵⁾ BF.

⁶⁾ When using a SELV or PELV power supply unit.

COMMUNICATION INTERFACE

IO-Link	✓, ✓
Remark	V1.1
Number of ports	8 pieces
Port Class	A/B
Data transmission rate	COM1, COM2, COM3
Additional features	Data Storage
Ethernet	✓
Fieldbus	✓
Industrial Ethernet	PROFINET
Number of ports	2 pieces
Data transmission rate	10/100 MBit/s
Conformity class	B
Specification	V2.45 (RT)
Network load class	III
Addressing	DCP, static IP address
Factory setting	DCP
REST API	✓
Specification	JSON integration for IO-Link version (V1.0.0)
Operator interfaces	Web server integrated

AMBIENT DATA


Ambient operating temperature	-40 °C ... +55 °C ¹⁾
Ambient temperature, storage	-40 °C ... +75 °C ¹⁾
Electromagnetic compatibility (EMC)	EN 61000-6-2:2016 EN 61000-6-4:2020
Shock load	EN 60068-2-27

¹⁾ Permissible relative humidity 0% ... 95% (non-condensing).

CERTIFICATES

EU declaration of conformity	✓
UK declaration of conformity	✓
China RoHS	✓
cULus certificate	✓
Profinet certificate	✓

DIMENSIONAL DRAWING



Dimensions in mm (inch)

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1131011



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence