



V3DU3-120RM25A

Ruler3000

3D MACHINE VISION

SICK
Sensor Intelligence.



Ordering information

| Type | part no. |
|----------------|----------|
| V3DU3-120RM25A | 1132220 |

Other models and accessories → www.sick.com/Ruler3000



Detailed technical data

Features

| | |
|--|---|
| Technology | 3D triangulation |
| Streaming | ✓ |
| Pre-calibrated | ✓ |
| Shutter technology | Global-Shutter |
| Working range | 430 mm ... 1,445 mm |
| Example field of view | 1,200 mm x 345 mm |
| Exposure mode | Linear HDR |
| Illumination | Integrated |
| Illumination color | Red, laser, Visible, 660 nm, ± 15 nm |
| Laser class | 2 (EN 60825-1:2014+A11:2021; IEC 60825-1:2014, Complies with the FDA performance requirements for laser products except for conformance with IEC 60825-1 Ed.3., as described in Laser Notice 56 dated May 8, 2019.) |
| Data synchronization | Free running, encoder triggered, external triggering |
| 3D measurement | ✓ |
| Scatter measurement | ✓ |
| Reflectance measurement | ✓ |
| Ambient light suppression | ✓ ¹⁾ |
| Scheimpflug adapter, integrated | ✓ |
| Width at minimum operating distance | 540 mm |
| Width at maximum operating distance | 1,680 mm |
| Maximum height range | 1,015 mm |

¹⁾ Red bandpass filter.

| | |
|-------------|--|
| Task | Detecting - Standard objects Detecting - Level Measuring - Dimension, contour and volume Monitoring and controlling - Quality Determining position - 3D position determination |
|-------------|--|

¹⁾ Red bandpass filter.

Mechanics/electronics

| | |
|-------------------------------|---|
| Connection type | Voltage – I/O: M12, 17-pin male connector Gigabit Ethernet: M12, 8-pin socket, X-coded |
| Connector material | M12: Nickel-coated brass |
| Supply voltage | 24 V DC, $\pm 10\%$ |
| Ripple | $< 5\text{ V}_{pp}$ |
| Power consumption | $\leq 12\text{ W}$ |
| Current consumption | $\leq 1.5\text{ A}$ |
| Enclosure rating | IP65 IP67 |
| Protection class | III |
| Housing material | Aluminum |
| Housing color | Blue |
| Window material | PMMA |
| Weight | 2.3 kg |
| Dimensions (L x W x H) | 336 mm x 77 mm x 138 mm |

Performance

| | |
|----------------------------|---|
| Image sensor | CMOS sensor from SICK with ROCC technology, M30 |
| Scan/frame rate | 46,000 3D profiles/s, In reduced ROI 7,000 3D profiles/s, full format |
| Data points/profile | 3,200 |
| Repeatability | 6.6 μm , for Z ¹⁾ |
| Typical resolution | Z resolution (height): 33 μm ... 265 μm , X resolution (width): 246 μm ... 710 μm |

¹⁾ Height values measured for different positions in the field of view. 20 measurements are performed at each position. The repeatability value is the 3-fold of the standard deviation (3σ) for all measurements at all positions.

Interfaces

| | |
|--|--|
| Ethernet | ✓, UDP/IP |
| Remark | GigE Vision Standard |
| Data transmission rate | $\leq 1\text{ Gbit/s}$ |
| Configuration software | Stream Setup |
| Operating system | Windows 10 |
| Application programming interface (API) | GenAPI, GenTL, Proprietary SICK GenIStream |
| Inputs/outputs | 4 x HIGH = 10 V ... 28.8 V, configurable |
| Encoder interface | RS-422 5 V, 2 x HTL single-ended |

Ambient data

| | |
|-------------------|-------------------------|
| Shock load | 15 g, 3 cycles per axis |
|-------------------|-------------------------|

¹⁾ Non-condensing.

| | |
|-------------------------------|--------------------------------------|
| Vibration load | 5 g, 10 Hz ... 150 Hz (EN 60068-2-6) |
| Ambient operating temperature | 0 °C ... +50 °C ¹⁾ |
| Storage temperature | -30 °C ... +70 °C ¹⁾ |

¹⁾ Non-condensing.


Classifications

| | |
|----------------|----------|
| ECLASS 5.0 | 27310205 |
| ECLASS 5.1.4 | 27310205 |
| ECLASS 6.0 | 27310205 |
| ECLASS 6.2 | 27310205 |
| ECLASS 7.0 | 27310205 |
| ECLASS 8.0 | 27310205 |
| ECLASS 8.1 | 27310205 |
| ECLASS 9.0 | 27310205 |
| ECLASS 10.0 | 27310205 |
| ECLASS 11.0 | 27310205 |
| ECLASS 12.0 | 27310205 |
| ETIM 5.0 | EC001820 |
| ETIM 6.0 | EC001820 |
| ETIM 7.0 | EC001820 |
| ETIM 8.0 | EC001820 |
| UNSPSC 16.0901 | 43211731 |

Certificates

| | |
|---|---|
| EU declaration of conformity | ✓ |
| UK declaration of conformity | ✓ |
| ACMA declaration of conformity | ✓ |
| China RoHS | ✓ |
| EAC certificate / DoC | ✓ |
| Information according to Art. 3 of Data Act (Regulation EU 2023/2854) | ✓ |
| GigE Vision | ✓ |
| GenICam | ✓ |

Dimensional drawing




Dimensions in mm (inch)

- ① Optical receiver (center)
- ② Optical sender (center)
- ③ Threaded mounting hole (M5, 12 mm deep) with through hole (Ø 4.2 mm)
- ④ Power I/O connection
- ⑤ Gigabit Ethernet connection (GbE)
- ⑥ Threaded mounting hole (M5, 9 mm deep)
- ⑦ Position and alignment hole for locating pins (Ø 5 mm)


Field of view

Ruler3120


Guaranteed field of view in mm




Characteristic curve Z resolution via Z position




Characteristic curve Width of the field of view via the Z position



Characteristic curve X resolution via Z position



Characteristic curve







The maximum line rate is based on the number of sensor lines used

- ① Line rate (kHz)
- ② Number of lines
- ③ Ruler3000 with activated HDR

- ④ Ruler3000 without activated HDR
- ⑤ Bandwidth limit for image width 2,560, height range only
- ⑥ Bandwidth limit for image width 3,072, height range only
- ⑦ Bandwidth limit for image width 2,560, height range and reflectance
- ⑧ Bandwidth limit for image width 3,072, height range and reflectance

Recommended accessories

Other models and accessories → www.sick.com/Ruler3000

| | Brief description | Type | part no. |
|---|--|--|----------|
| connectors and cables | | | |
|  | <ul style="list-style-type: none"> Connection type head A: Female connector, M12, 17-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 3 m, 17-wire, PUR Description: Sensor/actuator cable, twisted pair, shielded Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation | YF2A2D-030U-V1XLEAX | 6042772 |
|  | <ul style="list-style-type: none"> Connection type head A: Male connector, M12, 8-pin, straight, X-coded Connection type head B: Male connector, RJ45, 8-pin, straight Signal type: Ethernet, Gigabit Ethernet Cable: 2 m, 8-wire, PUR, halogen-free Description: Ethernet, shielded, Gigabit Ethernet Application: Zones with oils and lubricants | YM2X18-020EG1M-RJA8 | 2106258 |
|  | <ul style="list-style-type: none"> Connection type head A: Male connector, M12, 8-pin, straight, X-coded Connection type head B: Male connector, RJ45, 8-pin, straight Signal type: Ethernet, Gigabit Ethernet Cable: 3 m, 8-wire, PUR, halogen-free Description: Ethernet, shielded, Gigabit Ethernet Application: Zones with oils and lubricants | YM2X18-030EG1M-RJA8 | 2145693 |
| Mounting systems | | | |
|  | <ul style="list-style-type: none"> Description: Mounting bracket set consisting of mounting bracket, cooling plate, includes angle display for setting the tilt angle Suitable for: Lector63x, Inspector63x, Lector83x – up to 40 °C ambient operating temperature, Inspector83x – up to 40 °C ambient operating temperature, Lector83x – up to 40 °C ambient operating temperature, Inspector83x – up to 40 °C ambient operating temperature, Lector63x, Inspector63x | Mounting bracket set with inclination angle –40° - 40° | 2076735 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com