


SYS/BOT-ABIO4PCWI01MS3

Safe Robotics Area Protection

SAFETY SYSTEMS FOR ROBOTS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
SYS/BOT-ABIO4PCWI01MS3	1141111

Other models and accessories → www.sick.com/Safe_Robotics_Area_Protection

Detailed technical data

Features

Variant	sBot Speed I/O - ABB
Description	sBot Speed I/O – ABB is a safety system for ABB robots (GoFaTM and SWIFTITM) that makes it easy to protect your freely accessible robot application in an I/O infrastructure. The system ensures a safe stop with automatic restart of the robot. The microScan3 Pro I/O safety laser scanner is used to detect an approaching person. The microScan3 Configuration Tool (software) can be used to quickly and easily configure the safety laser scanner.
Product type	System (hardware and software)
Robot controller	ABB: SWIFTI CRB 1100, SWIFTI CRB 1300, GoFa CRB 15000
Compatible robot software	RobotWare (Omnicores) 7.10
Stopping process of the robot	With speed reduction
Robot restart	Automatic
Interfaces	
Communication interface	Discrete I/Os
Configuration interface	Ethernet
Safe state in the event of a fault	The safety-related semiconductor outputs are in the OFF state.
Safety laser scanners	microScan3 Pro I/O
Protective field range	4 m
Safety task	Hazardous area protection
Ambient operating temperature	-10 °C ... +50 °C
Storage temperature	-25 °C ... +70 °C
Air humidity	0% ... 95%, non-condensing
Voltage supply	
Supply voltage V_S	24 V DC (16.8 V DC ... 30 V DC)
Performance level	PL d (ISO 13849-1)
Items supplied	1 x microScan3 Pro I/O safety laser scanner (4 m) 1 x power cable, angled, 5 m 1 x signal cable with angled plug, 5 m 1 x mounting kit 1a 1 x RJ45 Ethernet cable, straight, 5 m microScan3 Configuration Tool (software) Operating instructions
Additional options required by ABB	
Collaborative Speed Control add-in	Option Collaborative speed control [3143-1]
Safety IO-Board	Safe base Dig. 6In/ 20Out [3037-2]

Classifications


ECLASS 5.0	27279090
-------------------	----------

ECLASS 5.1.4	27279090
ECLASS 6.0	27279090
ECLASS 6.2	27279090
ECLASS 7.0	27279090
ECLASS 8.0	27279090
ECLASS 8.1	27279090
ECLASS 9.0	27279090
ECLASS 10.0	27279090
ECLASS 11.0	27279090
ECLASS 12.0	27279090
ETIM 5.0	EC001449
ETIM 6.0	EC001449
ETIM 7.0	EC001449
ETIM 8.0	EC001449
UNSPSC 16.0901	32151705

Certificates

China RoHS	✓
Information according to Art. 3 of Data Act (Regulation EU 2023/2854)	✓


Dimensional drawing



Dimensions in mm (inch)

- ① mirror axis of rotation
- ② scan plane
- ③ countersink for M5 countersunk screw

Dimensional drawing



Dimensions in mm (inch)

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com