



DATA SHEET

# WLD4SP-221121A0ZZZ

W4  
Photoelectric sensors

# SICK

Sensor Intelligence

## PHOTOELECTRIC SENSORS

## WLD4SP-221121A0ZZZ



Illustration may differ

## ORDERING INFORMATION

Type	part no.
WLD4SP-221121A0ZZZ	1142556

Further device versions and accessories at [www.sick.com/W4](http://www.sick.com/W4)

## DETAILED TECHNICAL DATA

## FEATURES

Functional principle	Photoelectric retro-reflective sensor	
Functional principle detail	With minimum distance to reflector (dual lens system)	
Sensing range	Sensing range min.	0.035 m
	Sensing range max.	4.8 m
Maximum distance range from reflector to sensor (operating reserve 1)	0.035 m ... 4.8 m	
Recommended distance range from reflector to sensor (operating reserve 3,75)	0.1 m ... 3.4 m	
Reference reflector	Reflector PL80	
Recommended sensing range for the best performance	0.1 m ... 3.4 m	
Polarisation filter	Yes	
Emitted beam	Light source	PinPoint LED
	Type of light	Visible red light
	Shape of light spot	Point-shaped
	Light spot size (distance)	100 mm (2.5 m)
Maximum dispersion of the emitted beam around the standardized transmission axis (squint angle)	< +/- 1.5° (at T <sub>0</sub> = +23 °C)	
Key LED figures	Normative reference	EN 62471:2008-09   IEC 62471:2006, modified
	LED risk group marking	Free group
	Wave length	635 nm
	Average service life	100,000 h at T <sub>a</sub> = +25 °C
Adjustment		

	None	-
Display	LED green	Operating indicator Static on: power on
	LED yellow	Status of received light beam Static on: object not present Static off: object present Flashing: Below the 1.5 function reserve

## SAFETY-RELATED PARAMETERS

MTTF <sub>D</sub>	2,556 years
-------------------	-------------

## ELECTRONICS

Supply voltage U <sub>B</sub>	10 V DC ... 30 V DC <sup>1)</sup>																				
Ripple	≤ 5 V <sub>pp</sub>																				
Usage category	DC-12 (According to EN 60947-5-2) DC-13 (According to EN 60947-5-2)																				
Current consumption	≤ 20 mA, without load. At U <sub>B</sub> = 24 V																				
Protection class	III																				
Digital output	<table border="0"> <tr> <td>Number</td> <td>2</td> </tr> <tr> <td>Type</td> <td>Push-pull: PNP/NPN</td> </tr> <tr> <td>Switching mode</td> <td>Light/dark switching</td> </tr> <tr> <td>Signal voltage PNP HIGH/LOW</td> <td>Approx. U<sub>B</sub>-2.5 V / 0 V</td> </tr> <tr> <td>Signal voltage NPN HIGH/LOW</td> <td>Approx. U<sub>B</sub> / &lt; 2.5 V</td> </tr> <tr> <td>Output current I<sub>max</sub></td> <td>≤ 100 mA</td> </tr> <tr> <td>Circuit protection outputs</td> <td>Reverse polarity protected Overcurrent protected Short-circuit protected</td> </tr> <tr> <td>Response time</td> <td>≤ 500 μs</td> </tr> <tr> <td>Repeatability (response time)</td> <td>150 μs</td> </tr> <tr> <td>Switching frequency</td> <td>1,000 Hz</td> </tr> </table>	Number	2	Type	Push-pull: PNP/NPN	Switching mode	Light/dark switching	Signal voltage PNP HIGH/LOW	Approx. U <sub>B</sub> -2.5 V / 0 V	Signal voltage NPN HIGH/LOW	Approx. U <sub>B</sub> / < 2.5 V	Output current I <sub>max</sub>	≤ 100 mA	Circuit protection outputs	Reverse polarity protected Overcurrent protected Short-circuit protected	Response time	≤ 500 μs	Repeatability (response time)	150 μs	Switching frequency	1,000 Hz
Number	2																				
Type	Push-pull: PNP/NPN																				
Switching mode	Light/dark switching																				
Signal voltage PNP HIGH/LOW	Approx. U <sub>B</sub> -2.5 V / 0 V																				
Signal voltage NPN HIGH/LOW	Approx. U <sub>B</sub> / < 2.5 V																				
Output current I <sub>max</sub>	≤ 100 mA																				
Circuit protection outputs	Reverse polarity protected Overcurrent protected Short-circuit protected																				
Response time	≤ 500 μs																				
Repeatability (response time)	150 μs																				
Switching frequency	1,000 Hz																				
Pin/Wire assignment	<table border="0"> <tr> <td>Function of pin 4/black (BK)</td> <td>Digital output, light switching, object present → output Q LOW <sup>2)</sup></td> </tr> <tr> <td>Function of pin 2/white (WH)</td> <td>Digital output, dark switching, object present → output Q̄ HIGH <sup>2)</sup></td> </tr> </table>	Function of pin 4/black (BK)	Digital output, light switching, object present → output Q LOW <sup>2)</sup>	Function of pin 2/white (WH)	Digital output, dark switching, object present → output Q̄ HIGH <sup>2)</sup>																
Function of pin 4/black (BK)	Digital output, light switching, object present → output Q LOW <sup>2)</sup>																				
Function of pin 2/white (WH)	Digital output, dark switching, object present → output Q̄ HIGH <sup>2)</sup>																				

<sup>1)</sup> Limit values.

<sup>2)</sup> This switching output must not be connected to another output.

## MECHANICS

Housing	Rectangular						
Design detail	Slim						
Dimensions (W x H x D)	12.1 mm x 41.9 mm x 18.6 mm						
Connection	Male connector M8, 4-pin						
Material	<table border="0"> <tr> <td>Housing</td> <td>Plastic, VISTAL®</td> </tr> <tr> <td>Front screen</td> <td>Plastic, PMMA</td> </tr> <tr> <td>Male connector</td> <td>Plastic, VISTAL®</td> </tr> </table>	Housing	Plastic, VISTAL®	Front screen	Plastic, PMMA	Male connector	Plastic, VISTAL®
Housing	Plastic, VISTAL®						
Front screen	Plastic, PMMA						
Male connector	Plastic, VISTAL®						
Maximum tightening torque of the fixing screws	0.4 Nm						

## AMBIENT DATA

Enclosure rating	IP66 (EN 60529) IP67 (EN 60529)
------------------	------------------------------------

<sup>1)</sup> Supply voltage U<sub>B</sub>: 10 V DC ... 24 V DC, output current I<sub>max</sub>: ≤ 30 mA, enclosure rating: IP64 (EN 60529), UL file: no longer applicable.


Ambient operating temperature	-40 °C ... +60 °C +61 °C ... +70 °C <sup>1)</sup>
Ambient temperature, storage	-40 °C ... +75 °C
Typ. Ambient light immunity	Artificial light: ≤ 50,000 lx Sunlight: ≤ 50,000 lx
Shock resistance	30 g, 11 ms (3 positive and 3 negative shocks along X, Y, Z axes, 18 total shocks (EN60068-2-27))
Vibration resistance	10 Hz ... 1,000 Hz (Amplitude 1 mm, 3 x 30 min (EN60068-2-6))
Air humidity	35 % ... 95 %, relative humidity (no condensation)
Electromagnetic compatibility (EMC)	EN 60947-5-2
Resistance to cleaning agent	ECOLAB
UL File No.	NRKH.E181493 & NRKH7.E181493

<sup>1)</sup> Supply voltage  $U_s$ : 10 V DC ... 24 V DC, output current  $I_{max}$ : ≤ 30 mA, enclosure rating: IP64 (EN 60529), UL file: no longer applicable.

## CERTIFICATES


EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
cULus certificate	✓

## DISPLAY AND ADJUSTMENT ELEMENTS




- ① LED green
- ② LED yellow

## CONNECTION TYPE MALE CONNECTOR M8, 4-PIN



CONNECTION DIAGRAM CD-083



TRUTH TABLE PUSH-PULL: PNP/NPN - LIGHT SWITCHING Q


	Light switching Q (normally closed (upper switch), normally open (lower switch))	
	Object not present → Output HIGH	Object present → Output LOW
Light receive	✓	✗
Light receive indicator	☀	✗
Load resistance to L+	✗	⚡
Load resistance to M	⚡	✗

**TRUTH TABLE PUSH-PULL: PNP/NPN - DARK SWITCHING  $\bar{Q}$**

	Dark switching $\bar{Q}$ (normally open (upper switch), normally closed (lower switch))	
	Object not present → Output LOW	Object present → Output HIGH
Light receive	✓	✗
Light receive indicator	☀	✗
Load resistance to L+	⚡	✗
Load resistance to M	✗	⚡

**CHARACTERISTIC CURVE CHEMICAL-RESISTANT REFLECTORS**

Operating reserve




Recommended sensing range for the best performance

- ① Reflector PL20 CHEM
- ② Reflector P250 CHEM

**CHARACTERISTIC CURVE FINE TRIPLE REFLECTORS**

Operating reserve




Recommended sensing range for the best performance

- ① PL10F reflector
- ② Reflector PL20F
- ③ Reflector P250F

**CHARACTERISTIC CURVE REFLECTIVE TAPE**

Operating reserve




Recommended sensing range for the best performance

- ① Reflective tape REF-IRF-56
- ② Reflective tape REF-AC1000

**CHARACTERISTIC CURVE STANDARD REFLECTORS**

Operating reserve




Recommended sensing range for the best performance


- ① Reflector PL20A
- ② Reflector P250H
- ③ Reflector PL30A
- ④ Reflector PL40A Antifog
- ⑤ Reflector PL40A
- ⑥ Reflector PL250
- ⑦ Reflector PL80A

**LIGHT SPOT SIZE**

Dimensions in mm (inch)




**SENSING RANGE DIAGRAM CHEMICAL-RESISTANT REFLECTORS**



Recommended sensing range for the best performance

1	Reflector PL20 CHEM
2	Reflector P250 CHEM
A	Sensing range min. in m
B	Sensing range max. in m
C	Maximum distance range from reflector to sensor (operating reserve 1)
D	Recommended distance range from reflector to sensor (operating reserve 3,75)


**SENSING RANGE DIAGRAM FINE TRIPLE REFLECTORS**



Recommended sensing range for the best performance

1	PL10F reflector
2	Reflector PL20F
3	Reflector P250F
A	Sensing range min. in m
B	Sensing range max. in m
C	Maximum distance range from reflector to sensor (operating reserve 1)
D	Recommended distance range from reflector to sensor (operating reserve 3,75)


**SENSING RANGE DIAGRAM REFLECTIVE TAPE**



Recommended sensing range for the best performance

1	Reflective tape REF-IRF-56
2	Reflective tape REF-AC1000
A	Sensing range min. in m
B	Sensing range max. in m
C	Maximum distance range from reflector to sensor (operating reserve 1)
D	Recommended distance range from reflector to sensor (operating reserve 3,75)


**SENSING RANGE DIAGRAM STANDARD REFLECTORS**



Recommended sensing range for the best performance

1	Reflector PL20A
2	Reflector P250H
3	Reflector PL30A
4	Reflector PL40A Antifog
5	Reflector PL40A
6	Reflector P250
7	Reflector PL80A
A	Sensing range min. in m
B	Sensing range max. in m
C	Maximum distance range from reflector to sensor (operating reserve 1)
D	Recommended distance range from reflector to sensor (operating reserve 3,75)

**DIMENSIONAL DRAWING, SENSOR**



Dimensions in mm (inch)

- ① Center of optical axis, receiver
- ② Center of optical axis, sender
- ③ Connection
- ④ M3 mounting hole
- ⑤ display and adjustment elements

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at [www.sick.com/1142556](http://www.sick.com/1142556)



SICK AG  
WALDKIRCH  
GERMANY  
SICK.COM

# SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

**SICK**  
Sensor Intelligence