

SICK.COM



DATA SHEET

# CLV615-I3150

CLV61x  
Fixed mount barcode scanners

**SICK** Sensor Intelligence

## FIXED MOUNT BARCODE SCANNERS

## CLV615-I3150

## ORDERING INFORMATION

| Type         | part no. |
|--------------|----------|
| CLV615-I3150 | 1143676  |

Further device versions and accessories at [www.sick.com/CLV61x](http://www.sick.com/CLV61x)



## DETAILED TECHNICAL DATA

## FEATURES

|                    |   |
|--------------------|---|
| Version            | Long Range  |
| Connection type    | IO-Link   |
| Reading field      | Side (105°)   |
| Sensor type        | Raster scanner  |
| Optical focus      | Fixed focus   |
| Light source       | Light spot, laser, Visible, Red, 655 nm   |
| Laser class        | 2, complies with 21 CFR 1040.10 except for the conformance according to "Laser Notice No. 56" from May 8, 2019 (EN 60825-1:2014+A11:2021, IEC 60825-1:2014) |
| Aperture angle     | ≤ 50°   |
| Reading distance   | 25 mm ... 330 mm <sup>1)</sup>  |
| Scanning frequency | 400 Hz ... 1,000 Hz   |
| Code resolution    | 0.35 mm ... 0.5 mm  |

<sup>1)</sup> For details see reading field diagram.

## MECHANICS/ELECTRONICS

|                   |  |
|-------------------|--|
| Connection type   | 1 x IO-Link and POWER <sup>®</sup> connection, 5-pin M12 male connector, A-coded<br>1 x "Sensor 1" connection, 5-pin M12 female connector, A-coded<br>1 x Micro USB female connector, type B |
| Supply voltage    | 18 V DC ... 30 V DC  |
| Power consumption | 3.2 W  |
| Housing material  | Aluminum die cast  |

<sup>1)</sup> At 25 °C.

|                        |  |
|------------------------|--|
| Housing color          | Light blue (RAL 5012)                              |
| Window material        | Glass  |
| Enclosure rating       | IP65 (EN 60529:1991 + A1:2002 + A2:2013 + A3:2016) |
| Protection class       | III (EN 60950-1/EN 62368-1)                        |
| Weight                 | 260 g  |
| Dimensions (L x W x H) | 80 mm x 96 mm x 38 mm                              |
| MTBF                   | 100,000 h  |
| MTTF                   | 40,000 h (Laser diode) <sup>1)</sup>               |

<sup>1)</sup> At 25 °C.

## PERFORMANCE

|  |   |
|--|---|
| Readable code structures               | 1D codes  |
| Bar code types                         | All current code types, Code 39, Code 128, Code 93, Codabar, UPC / GTIN / EAN, Interleaved 2 of 5 |
| Code printing process                  | Label (printed codes)   |
| Print ratio                            | 2:1 ... 3:1   |
| No. of codes per scan                  | 1   |
| No. of codes per reading interval      | 1   |
| No. of characters per reading interval | 31  |
| No. of multiple readings               | 1 ... 99  |

## INTERFACES

|                        |                        |   |
|------------------------|------------------------|---|
| IO-Link                | Function               | ✓, V1.1<br>IO-Link V1.1 as per the IEC 61131-9 standard, Host: Process data, service data (parameterization, diagnostics), data storage |
|                        | Data transmission rate | COM3 (230,4 kBaud)  |
| USB                    | Function               | ✓<br>Service interface  |
|                        | Digital inputs         | 2 (1 x "Sensor 1", 1 x via IO-Link Ctrl bits)   |
| Digital outputs        |                        | 1 (Via IO-Link process data output (ctrl. bits))  |
| Reading pulse          |                        | IO-Link (default), Free (auto cycle), Digital input for local read cycle sensor   |
| Optical indicators     |                        | 2 LEDs  |
| Configuration software |                        | SOPAS ET  |

## AMBIENT DATA

|                                     |   |
|-------------------------------------|---|
| Electromagnetic compatibility (EMC) | EN 61000-6-4: 2019 / EN 61000-6-2: 2019 |
| Vibration resistance                | EN 60068-2-6:2008-02                    |
| Shock resistance                    | EN 60068-2-27:2009-05                   |
| Ambient operating temperature       | 0 °C ... +40 °C                         |
| Storage temperature                 | -20 °C ... +70 °C                       |
| Relative humidity                   | 90 %, Non-condensing                    |
| Ambient light immunity              | 2,000 lx, on barcode                    |
| Bar code print contrast (PCS)       | ≥ 60 %                                  |

## GENERAL NOTES

|                |                |
|----------------|----------------|
| Items supplied | Single scanner |
|----------------|----------------|


## CERTIFICATES

|                              |   |
|------------------------------|---|
| EU declaration of conformity | ✓ |
|------------------------------|---|

# FIXED MOUNT BARCODE SCANNERS - CLV615-I3150

|   |   |
|---|---|
| UK declaration of conformity  | ✓ |
| ACMA declaration of conformity  | ✓ |
| China RoHS  | ✓ |
| cULus certificate   | ✓ |
| IO-Link certificate   | ✓ |
| Laser safety (IEC 60825-1) declaration of manufacturer                | ✓ |
| Information according to Art. 3 of Data Act (Regulation EU 2023/2854) | ✓ |


## DIMENSIONAL DRAWING



Dimensions in mm (inch)

- ① blind hole thread M5, 5 mm deep (2 x), for mounting
- ② “Sensor 1” connection, female connector, M12, 5-pin, A-coded
- ③ “IO-Link” connection, male connector, M12, 5-pin, A-coded
- ④ internal impact point: rotation point of the variable direction laser beam
- ⑤ Additional plate for type label
- ⑥ Viewing window, side orientation
- ⑦ central position of the deflected laser beam in the V-shaped aperture angle
- ⑧ swivel connector unit (max 180° rotation angle from end position to end position)
- ⑨ reference point for reading distance (from housing edge to object)
- ⑩ “IO-Link” status display (RGB LED)
- ⑪ “Sensor” status display (RGB LED), with signal color assignment for events
- ⑫ type label
- ⑬ laser warning label
- ⑭ Cover for “USB” port (female connector, 5-pin, Micro-B type). The interface can only be used by SICK Service.

**READING FIELD DIAGRAM**



Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at [www.sick.com/1143676](http://www.sick.com/1143676)



SICK AG  
WALDKIRCH  
GERMANY  
SICK.COM

# SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

**SICK**  
Sensor Intelligence