



V3S146-1ABBBCA

Visionary AI-Assist

3D MACHINE VISION

SICK
Sensor Intelligence.



Ordering information

| Type | part no. |
|----------------|----------|
| V3S146-1ABBBCA | 1144257 |

Included in delivery: V3S146-1ABBAAA (1), AI-Assist (1)

Other models and accessories → www.sick.com/Visionary_AI-Assist



Detailed technical data

Features

| | |
|-----------------------------|--|
| Technology | 3D snapshot stereoscopy |
| Configurable | ✓ |
| Pre-calibrated | ✓ |
| Application software | AI-Assist, for detecting people and objects ¹⁾ |
| Working range | 0.28 m ... 16 m ²⁾ 0.65 m ... 37 m ³⁾ |
| Field of view | wide 130° x 105° (configurable) ⁴⁾ |
| | narrow 90° x 60° (configurable) ⁴⁾ |
| Exposure mode | Automatic Single or multiple (HDR) |
| Detectable objects | All objects (incl. people) ⁵⁾ |
| Classified objects | Persons ⁶⁾ |
| Neural network | Customized network |
| Task | Detecting - Standard objects Protecting objects - Vehicles Protecting people - Warning in outdoor areas Processing data - Visualizing Determining position - 3D position determination |

¹⁾ The SICK SensorApp can, if necessary, be deinstalled again.

²⁾ Valid for the 130° x 105° field of view.

³⁾ Valid for the 90° x 60° field of view.

⁴⁾ 2D and 3D data is available over the entire field of view.

⁵⁾ Detection based on 3D data. The performance depends on the scene and the ambient conditions.

⁶⁾ Based on AI classification.

Mechanics/electronics

| | |
|------------------------|---|
| Connection type | Power/I/O: M12 17-pin, A-coded Gigabit Ethernet: M12, 8-pin, X-coded |
| Supply voltage | 10 V DC ... 57 V DC ¹⁾ |

¹⁾ These values apply to the voltage applied to the device. When selecting the voltage source, please consider the voltage drop across the cable.

²⁾ Applies to operation with 24 V supply voltage.

³⁾ At 12 V, 5 m cable.

| | |
|-------------------------------|----------------------------|
| Power consumption | Typ. 19.5 W ²⁾ |
| Peak current | 2 A ³⁾ |
| Input voltage | 5 V ... 60 V |
| Output voltage | 9 V ... 57 V |
| Output current | ≤ 100 mA |
| Enclosure rating | IP67, IP69, IPX9K |
| Protection class | III |
| Housing color | Anthracite |
| Weight | 1.5 kg |
| Base distance | 112 mm |
| Dimensions (L x W x H) | 162 mm x 96.6 mm x 79.3 mm |

¹⁾ These values apply to the voltage applied to the device. When selecting the voltage source, please consider the voltage drop across the cable.

²⁾ Applies to operation with 24 V supply voltage.

³⁾ At 12 V, 5 m cable.

Safety-related parameters

| | | |
|-------------------------|----------------------|-------------------------|
| MTTF_D | | |
| | GB, 50% stress 25 °C | 84 years ¹⁾ |
| | GB, 50% stress 40 °C | 38 years ¹⁾ |
| | GB, 50% stress 55 °C | 17 years ¹⁾ |
| | GM, 50% stress 25 °C | 21 years ²⁾ |
| | GM, 50% stress 40 °C | 9.5 years ²⁾ |
| | GM, 50% stress 55 °C | 4.2 years ²⁾ |

¹⁾ GB: Controlled, fixed environment with low operational stress according to the T332.2 standard.

²⁾ GM: Mobile, highly fluctuating environment with high loads according to the T332.2 standard.

Functions

| | |
|-------------------------------|---|
| Integrated application | The installed "AI-Assist" software enables the detection of people and/or objects in flexibly adaptable 3D fields. The data is processed within the device. |
| Filter | Ground filter Sensitivity of people detection Minimum object size |
| Language | English, German |

Performance

| | |
|--------------------------|---------------------------------|
| Sensor properties | |
| Sensor resolution | 1,024 px x 576 px ¹⁾ |

¹⁾ The specified sensor resolution corresponds to the usable resolution. Due to the stereo technology, the physical resolution of the individual camera sensors cannot be fully utilized.

²⁾ Up to 26 Tera Operations Per Second (TOPS).

³⁾ The performance depends on the scene and the ambient conditions.

⁴⁾ Valid for the 90° x 60° field of view. Individual values can be found in the graphs "Field of view "narrow" (90° x 60°) absolute measurement accuracy and repeatability" and "Field of view "wide" (130° x 105°) absolute measurement accuracy and repeatability". The tables can be found under "Technical drawings".

⁵⁾ The response time is affected by the exposure time.

⁶⁾ With a default setting of one 3D field.

| | |
|--|--|
| AI accelerator | Hailo-8 ²⁾ |
| Number of fields | ≤ 16 |
| Number of simultaneously monitored fields | ≤ 16 |
| Object resolution | The minimum object size is individually configurable for each field. |
| Person recognition | |
| In various poses such as: | Standing, sitting, squatting, partially concealed, lying down ³⁾ |
| Scan/frame rate | ≤ 18 fps |
| Measurement accuracy (typical) | ± 2 mm, up to 5 m ⁴⁾ ± 35 mm, up to 4 m ⁴⁾ ± 850 mm, up to 20 m ⁴⁾ |
| Repeatability | ± 0.6 mm, up to 5 m ⁴⁾ ± 6 mm, up to 4 m ⁴⁾ ± 260 mm, up to 20 m ⁴⁾ |
| Switch-on delay | Approx. 20 s |
| Response time | Typ. 200 ms ^{5) 6)} |

¹⁾ The specified sensor resolution corresponds to the usable resolution. Due to the stereo technology, the physical resolution of the individual camera sensors cannot be fully utilized.

²⁾ Up to 26 Tera Operations Per Second (TOPS).

³⁾ The performance depends on the scene and the ambient conditions.

⁴⁾ Valid for the 90° x 60° field of view. Individual values can be found in the graphs "Field of view "narrow" (90° x 60°) absolute measurement accuracy and repeatability" and "Field of view "wide" (130° x 105°) absolute measurement accuracy and repeatability". The tables can be found under "Technical drawings".

⁵⁾ The response time is affected by the exposure time.

⁶⁾ With a default setting of one 3D field.

Interfaces

| | |
|-------------------------------|--|
| Ethernet | ✓ , TCP/IP, UDP/IP |
| Remark | Gigabit-Ethernet (100/1000 Mbit/s) |
| Function | Data interface, Communication interface, Configuration interface |
| Data transmission rate | ≤ 1,000 Mbit/s |
| REST API | ✓ |
| Function | Communication interface, Configuration interface |
| CAN | ✓ |
| Remark | J1939 |
| Function | Data interface, Communication interface |
| Data transmission rate | 250 kBaud |
| Digital inputs/outputs | |
| Number | 4 |
| Remark | Configurable |
| Function | Data interface, Communication interface, Configuration interface |
| Logic | HIGH active, LOW active |
| Detail | Invert, debouncing (0 ms ... 1,000 ms) |
| Operator | AND, OR, XOR |
| Output mode | PNP, NPN, Push-pull |
| Restart | Immediate, Time, Input |
| Digital inputs | |

| | | |
|-------------------------------|-------------|---|
| | Number | 2 |
| | Remark | Are available in addition to the 4 digital inputs/outputs |
| | Function | Configuration interface |
| | Logic | HIGH active, LOW active |
| | Detail | Debouncing (0 ms ... 1,000 ms) |
| Configuration software | | SOPASair browser-based user interface, SICK AppManager |
| Operating system | | Windows, Linux |
| Optical indicators | | 2 status LEDs |
| Data output | | 2D video stream (RGB) Field evaluation System diagnostics |
| Video live stream | | |
| | Frame rate | ≤ 30 fps |
| | Resolution | 1,024 px x 576 px |
| | Protocol | RTSP |
| | Compression | MJPEG |
| Ignition plus | | ✓ |

Ambient data

| | |
|--|--|
| Electromagnetic compatibility (EMC) | Agricultural and forestry machinery / EN ISO 14982 Earth-moving and building construction machinery / EN ISO 13766-1 Industrial trucks / EN 12895+A1 |
| Vibration resistance | 5 g, 10 Hz ... 500 Hz (IEC 60068-2-6) 4.24 g RMS, 10 Hz ... 250 Hz (IEC 60068-2-64) |
| Shock resistance | 100 g, 6 ms (IEC 60068-2-27) |
| Ambient operating temperature | -40 °C ... +55 °C |
| Storage temperature | -40 °C ... +85 °C |
| Ambient light immunity | 5 lx ... 300 klx ¹⁾ |

¹⁾ Detection of a person (standing front on) at a distance of 5 meters for the "wide" field of view (130° x 105°).

Licenses

| | |
|----------------------------|--|
| Description | The installed "AI-Assist" software enables the detection of people and/or objects in flexibly adaptable 3D fields. The data is processed within the device. |
| Product type | Software |
| License type | Device license |
| License description | The software is provided as a device license. A license is bound to a specific hardware ID. It is possible to move the license to another device, if necessary, if it has been properly removed from the original device. The license costs are included in the price. |
| Scope of use | Full version |
| License period | The license is issued without a time limit. |
| No. of licenses | 1 |

Certificates

| | |
|---------------------------------------|---|
| EU declaration of conformity | ✓ |
| UK declaration of conformity | ✓ |
| ACMA declaration of conformity | ✓ |
| China RoHS | ✓ |


Information according to Art. 3 of Data Act (Regulation EU 2023/2854)

✓

Classifications

| | |
|-----------------------|----------|
| ECLASS 5.0 | 27310205 |
| ECLASS 5.1.4 | 27310205 |
| ECLASS 6.0 | 27310205 |
| ECLASS 6.2 | 27310205 |
| ECLASS 7.0 | 27310205 |
| ECLASS 8.0 | 27310205 |
| ECLASS 8.1 | 27310205 |
| ECLASS 9.0 | 27310205 |
| ECLASS 10.0 | 27310205 |
| ECLASS 11.0 | 27310205 |
| ECLASS 12.0 | 27310205 |
| ETIM 5.0 | EC001820 |
| ETIM 6.0 | EC001820 |
| ETIM 7.0 | EC001820 |
| ETIM 8.0 | EC001820 |
| UNSPSC 16.0901 | 43211731 |

Dimensional drawing




Dimensions in mm (inch)

- ① Connection: Power/I/O
- ② "Device" status LED
- ③ "Application" status LED

- ④ Pressure compensation element
- ⑤ Ethernet status LED
- ⑥ Ethernet connection
- ⑦ M6 threaded hole, 7 mm deep (2x), for mounting
- ⑧ service interface
- ⑨ Sensor coordinate origin
- ⑩ Interface bracket
- ⑪ Mounting bracket (accessories)
- ⑫ M6 threaded hole, 10 mm deep (3x), for mounting


Field of view 130° x 105° (wide) absolute measurement accuracy and repeatability



The values are typical values and apply in the central image area for a well-lit scene and high-contrast objects.

| Absolute working distance (z) | Measuring range ($\Delta x \times \Delta y$) | Area per pixel | Measurement accuracy Δz (average value) | Repeatability σz (average value) |
|-------------------------------|--|-----------------|---|--|
| 1.0 m | ~ 4.3 m x 2.6 m | ~ 4 mm x 4 mm | ± 5 mm | ± 0.5 mm |
| 4.0 m | ~ 17.2 m x 10.4 m | ~ 17 mm x 17 mm | ± 80 mm | ± 12 mm |
| 8.0 m | ~ 34.3 m x 20.8 m | ~ 35 mm x 35 mm | ± 300 mm | ± 50 mm |
| 12.0 m | ~ 51.5 m x 31.3 m | ~ 52 mm x 52 mm | ± 700 mm | ± 100 mm |
| 16.0 m | ~ 68.6 m x 41.7 m | ~ 70 mm x 70 mm | ± 1,200 mm | - |


Field of view 90° x 60° (narrow) absolute measurement accuracy and repeatability



The values are typical values and apply in the central image area for a well-lit scene and high-contrast objects.

| Absolute working distance (z) | Measuring range (Δx x Δy) | Area per pixel | Measurement accuracy Δz (average value) | Repeatability σz (average value) |
|-------------------------------|---------------------------|-----------------|---|----------------------------------|
| 1.0 m | ~ 2.0 m x 1.2 m | ~ 2 mm x 2 mm | ± 2 mm | ± 0.6 mm |
| 4.0 m | ~ 8.0 m x 4.6 m | ~ 8 mm x 8 mm | ± 35 mm | ± 6 mm |
| 8.0 m | ~ 16.0 m x 9.2 m | ~ 16 mm x 16 mm | ± 140 mm | ± 30 mm |
| 12.0 m | ~ 24.0 m x 13.9 m | ~ 24 mm x 24 mm | ± 300 mm | ± 60 mm |
| 20.0 m | ~ 40.0 m x 23.1 m | ~ 40 mm x 40 mm | ± 850 mm | ± 260 mm |
| 25.0 m | ~ 50.0 m x 28.9 m | ~ 50 mm x 50 mm | ± 1,300 mm | - |


Connection type Gigabit Ethernet



socket: M12, 8-pin, X-coded

- ① DA+ (data A+)
- ② DA- (data A-)
- ③ DB+ (data B+)
- ④ DB- (data B-)
- ⑤ DD+ (data D+)
- ⑥ DD- (data D-)
- ⑦ DC- (data C-)
- ⑧ DC+ (data C+)

Connection type



- ① GND
- ② UV
- ③ CAN L
- ④ CAN H
- ⑤ IGN_EN
- ⑥ IGN_PLUS

- ⑦ TxD
- ⑧ RxD
- ⑨ SensGND
- ⑩ SENS in 1
- ⑪ GND
- ⑫ UV
- ⑬ DIO 1
- ⑭ DIO 2
- ⑮ SENS in 2
- ⑯ DIO 3
- ⑰ DIO 4

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com