



# STL-2312-GM35AA3

Other connectors and cables

CONNECTORS AND CABLES

**SICK**  
Sensor Intelligence.



### Ordering information

Type	part no.
STL-2312-GM35AA3	2061621

Other models and accessories → [www.sick.com/Other\\_connectors\\_and\\_cables](http://www.sick.com/Other_connectors_and_cables)



### Detailed technical data

#### Technical specifications

<b>Connection type head A</b>	Female connector, JST, 8-pin, straight
<b>Connection type head B</b>	Male connector, M23, 12-pin, straight
<b>Locking nut material</b>	Zinc die-cast, nickel-plated
<b>Cable</b>	0.35 m, 8-wire, PUR, halogen-free
<b>Jacket material</b>	PUR, halogen-free
<b>Cable diameter</b>	5.6 mm
<b>Conductor cross section</b>	4 x 2 x 0.15 mm <sup>2</sup>
<b>Shielding</b>	Shielded
<b>Signal type</b>	Incremental
<b>Enclosure rating</b>	IP66/ IP67
<b>Operating temperature</b>	
Stationary position	-20 °C ... +130 °C

#### Certificates


<b>EU declaration of conformity</b>	✓
<b>China RoHS</b>	✓

#### Classifications

<b>ECLASS 5.0</b>	19030312
<b>ECLASS 5.1.4</b>	19030312
<b>ECLASS 6.0</b>	27060304
<b>ECLASS 6.2</b>	27060304
<b>ECLASS 7.0</b>	27060304
<b>ECLASS 8.0</b>	27060304
<b>ECLASS 8.1</b>	27060304
<b>ECLASS 9.0</b>	27060304
<b>ECLASS 10.0</b>	27060304
<b>ECLASS 11.0</b>	27060304
<b>ECLASS 12.0</b>	27060304
<b>ETIM 5.0</b>	EC000830
<b>ETIM 6.0</b>	EC000830

<b>ETIM 7.0</b>	EC003249
<b>ETIM 8.0</b>	EC003249
<b>UNSPSC 16.0901</b>	26121604

### Dimensional drawing



Dimensions in mm (inch)

### PIN assignment

PIN	Signal TTL, HTL	Signal Sinus 1,0 V <sub>SS</sub>	Farbe der Adern
1	$\bar{B}$	SIN-	Schwarz
2	Nicht belegt	Nicht belegt	
3	Z	Z	Lila
4	$\bar{Z}$	$\bar{Z}$	Gelb
5	A	COS+	Weiß
6	$\bar{A}$	COS-	Braun
7	Nicht belegt	Nicht belegt	
8	B	SIN+	Rosa
9	Nicht belegt	Nicht belegt	
10	GND	GND	Blau
11	Nicht belegt	Nicht belegt	
12	U <sub>s</sub>	U <sub>s</sub>	Rot
Schirm	Schirm <sup>1)</sup>	Schirm <sup>1)</sup>	

#### Achtung!

Die paarig verdrehten Litzen müssen entsprechend den Signalen zugeordnet werden.

Weiß/Braun = A/ $\bar{A}$  oder COS+/COS-

Lila/Gelb = Z/ $\bar{Z}$

Rosa/Schwarz = B/ $\bar{B}$  oder SIN+/SIN-

Rot/Blau = vorzugsweise U<sub>s</sub> und GND

<sup>1)</sup> Schirm encoderseitig mit Gehäuse verbunden. Steuerungsseitig mit Erde verbunden.

**Achtung!** Nur in Kombination mit den elektrischen Schnittstellen A, C, E und P.

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)