

BEF-EOAS-A

Flanges and nozzles

MOUNTING SYSTEMS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
BEF-EOAS-A	2130480

Other models and accessories → www.sick.com/Flanges_and_nozzles


Detailed technical data

Features

Accessory group	Mounting systems
Accessory family	Flanges and nozzles
Suitable for	UR3e, UR5e, UR7e, UR10e, UR12e, UR16e, UR8L, UR15, UR18
Material	Aluminum (anodised)
Dimensions (W x H x L)	69 mm x 34.5 mm x 69 mm
Weight	185 g
Payload	Distance 0 mm: 16 kg ¹⁾ Distance 150 mm: 3.5 kg ¹⁾ Distance 250 mm: 2.0 kg ¹⁾ Distance 350 mm: 1.3 kg ¹⁾

¹⁾ Maximum payload as a function of the distance between the center of gravity and the EOAS flange. The payload refers to the end effector and the payload. The weight of the EOAS sensor and the EOAS flange is already taken into account in this value. Applies to robot speeds up to 1,500 mm/s.

Dimensional drawing



Dimensions in mm (inch)

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com