



# FBM-N11

Fieldbus modules

INTEGRATION MODULES AND ADAPTERS

**SICK**  
Sensor Intelligence.



## Ordering information

Type	part no.
FBM-N11	2081101

Other models and accessories → [www.sick.com/Fieldbus\\_modules](http://www.sick.com/Fieldbus_modules)



## Detailed technical data

### Features

<b>Product segment</b>	Integration modules and adapters
<b>Product</b>	Fieldbus modules
<b>Description</b>	MLG-2 ProNet, fieldbus module: PROFINET
<b>Dimensions (W x H x L)</b>	34 mm x 133 mm x 40.6 mm


### Classifications

<b>ECLASS 5.0</b>	27242202
<b>ECLASS 5.1.4</b>	27242602
<b>ECLASS 6.0</b>	27242602
<b>ECLASS 6.2</b>	27242602
<b>ECLASS 7.0</b>	27242602
<b>ECLASS 8.0</b>	27242602
<b>ECLASS 8.1</b>	27242602
<b>ECLASS 9.0</b>	27242602
<b>ECLASS 10.0</b>	27242602
<b>ECLASS 11.0</b>	27242602
<b>ECLASS 12.0</b>	27242602
<b>ETIM 5.0</b>	EC001597
<b>ETIM 6.0</b>	EC001597
<b>ETIM 7.0</b>	EC001597
<b>ETIM 8.0</b>	EC001597
<b>UNSPSC 16.0901</b>	32151705

### Certificates

<b>cULus certificate</b>	✓
--------------------------	---

Dimensional drawing PROFINET, EtherCAT®, EtherNet/IP



Dimensions in mm (inch)

- ① safty screw M4; turning moment 0,5 Nm
- ② for thread bold M4; turning moment 0,5 Nm

Recommended accessories

Other models and accessories → [www.sick.com/Fieldbus\\_modules](http://www.sick.com/Fieldbus_modules)

	Brief description	Type	part no.
connectors and cables			
	<ul style="list-style-type: none"> <li><b>Description:</b> Sensor/actuator cable, shielded</li> <li><b>Connection type head A:</b> Female connector, M12, 12-pin, straight</li> <li><b>Connection type head B:</b> Male connector, M12, 12-pin, straight</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 2 m, 12-wire, shielded, PVC</li> <li><b>Note:</b> Connection cable, extension cable 1:1, shielded, for TTK70 inspector</li> </ul>	DSL-1212-G02MAC	6041763

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)