


# LL3-DM02

Fiber-optic cables

FIBER-OPTIC SENSORS

**SICK**  
Sensor Intelligence.



### Ordering information

Type	part no.
LL3-DM02	5308077

Other models and accessories → [www.sick.com/Fiber-optic\\_cables](http://www.sick.com/Fiber-optic_cables)

### Detailed technical data

#### Features

<b>Device type</b>	Fiber-optic cables
<b>Functional principle</b>	Proximity system
<b>Fiber-optic head design</b>	Threaded sleeve
<b>Application</b>	Standard
<b>Compatible fiber-optic amplifiers</b>	GLL70, WLL80, WLL180, GLL170(T), WLL24 Ex, KTL180
<b>Sensing range max.</b>	710 mm (Sensing range of WLL80 at 8 ms)
<b>Minimal object diameter</b>	0.015 mm <sup>1)</sup>
<b>Optical fiber head</b>	
Angle of dispersion	60°
Integrated lens	No
Compatibility tip adapters	Yes
<b>Optical fiber</b>	
Compatibility with infrared light	No
Optical fiber cable can be shortened	✓
Adapter end sleeves required	Yes
<b>Included with delivery</b>	Mounting, 2 x M4 hexagon nut, 2 x washer, adapter sleeves, BF-WLL160-13 (1.3 mm) adapter sleeves, FC fiber cutter (5304141)
<b>For fiber-optic</b>	LL3-DA06, LL3-DA09

<sup>1)</sup> Minimum detectable object was determined at optimum measuring distance and optimum setting.

#### Mechanics

<b>Optical fiber head</b>	
Light emission	Axial
Thread diameter (housing)	M4
<b>Optical fiber</b>	
Fiber length	2,000 mm
Bending radius	15 mm
Dynamic flexibility (robotics)	No
Outside diameter, optical fiber cable connection	1.3 mm
Fiber arrangement	Coaxial
Core structure	S: Ø 0,5 mm, R: 9 x Ø 0,25 mm <sup>1)</sup> Coaxial

<sup>1)</sup> C = Coaxial, S = Sender, E = Receiver.

<b>Material</b>	Optical fiber head	Stainless steel
	Sheath	Polyethylen (PE)
	Fibers	Polymethylmethacrylat (PMMA)
<b>Weight</b>		21 g

<sup>1)</sup> C = Coaxial, S = Sender, E = Receiver.

#### Ambient data

<b>Ambient operating temperature</b>	-40 °C ... +70 °C
--------------------------------------	-------------------

#### Sensing ranges with GLL70

<b>Operating mode 50 µs</b>	70 mm
<b>Operating mode 250 µs</b>	245 mm
<b>Operating mode 1 ms</b>	365 mm
<b>Operating mode 4 ms</b>	600 mm

#### Sensing ranges with WLL80

<b>Operating mode 16 µs</b>	45 mm
<b>Operating mode 70 µs</b>	170 mm
<b>Operating mode 250 µs</b>	265 mm
<b>Operating mode 500 µs</b>	320 mm
<b>Operating mode 1 ms</b>	380 mm
<b>Operating mode 2 ms</b>	505 mm
<b>Operating mode 8 ms</b>	710 mm
<b>Note</b>	Sensing ranges related to fiber-optic sensors with type of light: visible red light

#### Sensing ranges with WLL180T

<b>Operating mode 16 µs</b>	40 mm
<b>Operating mode 70 µs</b>	130 mm
<b>Operating mode 250 µs</b>	200 mm
<b>Operating mode 2 ms</b>	350 mm
<b>Operating mode 8 ms</b>	600 mm
<b>Note</b>	Sensing ranges related to fiber-optic sensors with type of light: visible red light

#### Sensing ranges with GLL170

<b>Operating mode 250 µs</b>	70 mm
------------------------------	-------

#### Sensing ranges with GLL170T

<b>Operating mode 50 µs</b>	60 mm
<b>Operating mode 250 µs</b>	110 mm

#### Sensing ranges with KTL180


<b>Operating mode 16 µs</b>	2 mm
<b>Operating mode 200 µs</b>	2 mm
<b>When using LL3-DA06</b>	16 mm

<b>When using LL3-DA09</b>	6 mm
----------------------------	------

### Classifications

<b>ECLASS 5.0</b>	27270905
<b>ECLASS 5.1.4</b>	27270905
<b>ECLASS 6.0</b>	27270905
<b>ECLASS 6.2</b>	27270905
<b>ECLASS 7.0</b>	27270905
<b>ECLASS 8.0</b>	27270905
<b>ECLASS 8.1</b>	27270905
<b>ECLASS 9.0</b>	27270905
<b>ECLASS 10.0</b>	27270905
<b>ECLASS 11.0</b>	27270905
<b>ECLASS 12.0</b>	27270905
<b>ETIM 5.0</b>	EC002651
<b>ETIM 6.0</b>	EC002651
<b>ETIM 7.0</b>	EC002651
<b>ETIM 8.0</b>	EC002651
<b>UNSPSC 16.0901</b>	39121528

### Dimensional drawing LL3-DM02



Dimensions in mm (inch)

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)