




LL3-DY01

Fiber-optic cables

FIBER-OPTIC SENSORS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
LL3-DY01	5308093

Included in delivery: FC (1)

Other models and accessories → www.sick.com/Fiber-optic_cables

Detailed technical data

Features

Device type	Fiber-optic cables
Functional principle	Proximity system
Fiber-optic head design	Smooth sleeve
Application	Resistant to oil/chemicals
Special features	Special application: Teflon-coating, chemically resistant
Compatible fiber-optic amplifiers	GLL70, WLL80, WLL180, GLL170(T), WLL24 Ex, KTL180
Sensing range max.	450 mm (Sensing range of WLL80 at 8 ms)
Minimal object diameter	0.02 mm ¹⁾
Optical fiber head	
Angle of dispersion	60°
Integrated lens	No
Compatibility tip adapters	No
Optical fiber	
Compatibility with infrared light	No
Optical fiber cable can be shortened	✓
Adapter end sleeves required	No
Included with delivery	FC fiber cutter (5304141)

¹⁾ Minimum detectable object was determined at optimum measuring distance and optimum setting.

Mechanics

Optical fiber head	
Light emission	Axial
Smooth sleeve diameter	6 mm
Optical fiber	
Fiber length	2,000 mm
Bending radius	60 mm
Dynamic flexibility (robotics)	No
Outside diameter, optical fiber cable connection	2.2 mm
Fiber arrangement	Singlefiber
Core structure	2 x Ø 1,0 mm ¹⁾ Singlefiber

¹⁾ C = Coaxial, S = Sender, E = Receiver.

Material		
	Optical fiber head	Polytetrafluorethylen (PTFE)
	Sheath	Polytetrafluorethylen (PTFE)
	Fibers	Polymethylmethacrylat (PMMA)
Weight		72 g

¹⁾ C = Coaxial, S = Sender, E = Receiver.

Ambient data

Ambient operating temperature	-40 °C ... +100 °C
--------------------------------------	--------------------

Sensing ranges with GLL70

Operating mode 50 µs	120 mm
Operating mode 250 µs	320 mm
Operating mode 1 ms	430 mm
Operating mode 4 ms	450 mm

Sensing ranges with WLL80

Operating mode 16 µs	100 mm
Operating mode 70 µs	250 mm
Operating mode 250 µs	355 mm
Operating mode 500 µs	390 mm
Operating mode 1 ms	435 mm
Operating mode 2 ms	450 mm
Operating mode 8 ms	450 mm
Note	Sensing ranges related to fiber-optic sensors with type of light: visible red light

Sensing ranges with WLL180T

Operating mode 16 µs	100 mm
Operating mode 70 µs	180 mm
Operating mode 250 µs	200 mm
Operating mode 2 ms	150 mm
Operating mode 8 ms	280 mm
Note	Sensing ranges related to fiber-optic sensors with type of light: visible red light

Sensing ranges with GLL170

Operating mode 250 µs	110 mm
------------------------------	--------

Sensing ranges with GLL170T

Operating mode 50 µs	160 mm
Operating mode 250 µs	150 mm

Sensing ranges with KTL180


Operating mode 16 µs	2 mm
Operating mode 200 µs	2 mm

Classifications

ECLASS 5.0	27270905
-------------------	----------

ECLASS 5.1.4	27270905
ECLASS 6.0	27270905
ECLASS 6.2	27270905
ECLASS 7.0	27270905
ECLASS 8.0	27270905
ECLASS 8.1	27270905
ECLASS 9.0	27270905
ECLASS 10.0	27270905
ECLASS 11.0	27270905
ECLASS 12.0	27270905
ETIM 5.0	EC002651
ETIM 6.0	EC002651
ETIM 7.0	EC002651
ETIM 8.0	EC002651
UNSPSC 16.0901	39121528

Dimensional drawing LL3-DY01



Dimensions in mm (inch)

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com