



LL3-DC04

Fiber-optic cables

FIBER-OPTIC SENSORS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
LL3-DC04	5326018

Included in delivery: BF-WLL160-13 (1), FC (1)

Other models and accessories → www.sick.com/Fiber-optic_cables

Detailed technical data

Features

Device type	Fiber-optic cables
Functional principle	Proximity system
Fiber-optic head design	Flat type, 90° deflection
Application	High flexible (static), Robotics (dynamic flexible), Icd / clear material / semiconductor, Limited sensing range
Compatible fiber-optic amplifiers	GLL70, WLL80, WLL180, GLL170(T)
Sensing range max.	40 mm (Sensing range of WLL80 at 8 ms)
Minimal object diameter	0.4 mm ¹⁾
Optical fiber head	
Angle of dispersion	27°
Integrated lens	Yes
Compatibility tip adapters	No
Optical fiber	
Compatibility with infrared light	No
Optical fiber cable can be shortened	✓
Adapter end sleeves required	Yes
Included with delivery	Adapter sleeves, BF-WLL160-13 (1.3 mm) adapter sleeves, FC fiber cutter (5304141)

¹⁾ Minimum detectable object was determined at optimum measuring distance and optimum setting.

Mechanics

Optical fiber head		
	Light emission	Radial
Optical fiber		
	Fiber length	3,000 mm
	Bending radius	4 mm
	Dynamic flexibility (robotics)	Yes
	Outside diameter, optical fiber cable connection	1.3 mm
	Fiber arrangement	Multi-fiber
	Core structure	S: 9 x Ø 0,25 mm, R: 9 x Ø 0,25 mm Multi-fiber
Material		
	Optical fiber head	Acrylnitril-Butadien-Styrol (ABS)
	Sheath	Polyethylen (PE)

	Fibers	Polymethylmethacrylat (PMMA)
Weight		43 g

Ambient data

Ambient operating temperature	0 °C ... +70 °C
--------------------------------------	-----------------

Sensing ranges with WLL80

Operating mode 16 µs	0 mm ... 32 mm
Operating mode 70 µs	0 mm ... 39 mm
Operating mode 250 µs	0 mm ... 40 mm
Operating mode 500 µs	0 mm ... 40 mm
Operating mode 1 ms	0 mm ... 40 mm
Operating mode 2 ms	0 mm ... 40 mm
Operating mode 8 ms	0 mm ... 40 mm
Note	Sensing ranges related to fiber-optic sensors with type of light: visible red light

Sensing ranges with WLL180T

Operating mode 16 µs	4 mm ... 18 mm
Operating mode 70 µs	0 mm ... 31 mm
Operating mode 250 µs	0 mm ... 34 mm
Operating mode 2 ms	0 mm ... 38 mm
Operating mode 8 ms	0 mm ... 38 mm
Note	Sensing ranges related to fiber-optic sensors with type of light: visible red light

Sensing ranges with GLL170

Operating mode 250 µs	0 mm ... 14 mm
------------------------------	----------------

Sensing ranges with GLL170T


Operating mode 50 µs	0 mm ... 16 mm
Operating mode 250 µs	0 mm ... 19 mm

Classifications

ECLASS 5.0	27270905
ECLASS 5.1.4	27270905
ECLASS 6.0	27270905
ECLASS 6.2	27270905
ECLASS 7.0	27270905
ECLASS 8.0	27270905
ECLASS 8.1	27270905
ECLASS 9.0	27270905
ECLASS 10.0	27270905
ECLASS 11.0	27270905
ECLASS 12.0	27270905
ETIM 5.0	EC002651
ETIM 6.0	EC002651

ETIM 7.0	EC002651
ETIM 8.0	EC002651
UNSPSC 16.0901	39121528

Dimensional drawing LL3-DC04



Dimensions in mm (inch)

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com