



YF2A2B-050UD2XLEAX

Sensor-actuator cables

CONNECTORS AND CABLES

SICK
Sensor Intelligence.



Ordering information

| Type | part no. |
|--------------------|----------|
| YF2A2B-050UD2XLEAX | 2130999 |

Other models and accessories → www.sick.com/Sensor-actuator_cables



Detailed technical data

Technical specifications

| | | |
|--------------------------------|--|-----------------------|
| Connection type head A | Female connector, M12, 12-pin, straight, A-coded | |
| Connection type head B | Flying leads | |
| Locking plug connector | Screw connection | |
| Connector material | TPU | |
| Connector color | Black | |
| Locking nut material | Zinc die-cast, nickel-plated | |
| Seal material | FKM | |
| Tightening torque | 0.6 Nm | |
| Width across flats | 13 | |
| Cable | 5 m, 12-wire, PUR, halogen-free | |
| Jacket material | PUR, halogen-free | |
| Jacket color | Black | |
| Cable diameter | 6.5 mm | |
| Conductor cross section | 0.14 mm ² | |
| Shielding | Shielded | |
| Bending radius | Flexible use | > 10 x cable diameter |
| | | > 5 x cable diameter |
| | | > 10 x cable diameter |
| Bending cycles | ≤ 5,000,000 | |
| Nominal voltage, cable | 300 V AC | |
| Test voltage, cable | 2,000 V AC | |
| Reference voltage | 30 V AC 30 V DC | 30 V AC |
| | | 30 V DC |
| Rated impulse voltage | 0.8 kV | |
| Current loading | 1.5 A | |
| Traversing speed | 3.3 m/s | |

| | |
|---------------------------------------|--|
| Travelling distance | 5 m |
| Acceleration | $\leq 5 \text{ m/s}^2$ |
| Signal type | Sensor/actuator cable |
| Torsion force | 30° / 1 m |
| Torsion cycles | 2,000,000 |
| Cycles per minutes | 35 |
| Application | Drag chain operation Zones with oils and lubricants Robot |
| Enclosure rating | IP67 |
| Operating temperature | |
| Flexible use | -25 °C ... +80 °C |
| Stationary position | -40 °C ... +80 °C |
| Drag chain operation | -25 °C ... +80 °C |
| Head | -25 °C ... +85 °C |
| Contamination rating | 3 |
| Insulation resistance | 100 MΩ |
| Overshoot category | III |
| Specific insulation resistance | 30 mΩ |
| Thermal resistance, piping | Flame retardant according to UL 1581 Section 1090 (H), CSA FT2 / IEC 60332-2-2 |


Certificates

| | |
|-------------------------------------|---|
| EU declaration of conformity | ✓ |
| China RoHS | ✓ |
| cULus certificate | ✓ |

Classifications

| | |
|-----------------------|----------|
| ECLASS 5.0 | 19030312 |
| ECLASS 5.1.4 | 19030312 |
| ECLASS 6.0 | 27060304 |
| ECLASS 6.2 | 27060304 |
| ECLASS 7.0 | 27060304 |
| ECLASS 8.0 | 27060304 |
| ECLASS 8.1 | 27060304 |
| ECLASS 9.0 | 27060304 |
| ECLASS 10.0 | 27060304 |
| ECLASS 11.0 | 27060304 |
| ECLASS 12.0 | 27060304 |
| ETIM 5.0 | EC000830 |
| ETIM 6.0 | EC000830 |
| ETIM 7.0 | EC003249 |
| ETIM 8.0 | EC003249 |
| UNSPSC 16.0901 | 26121604 |

Dimensional drawing



Dimensions in mm (inch)

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations www.sick.com