



# Bar code tape

Positioning codes

**CODES**

**SICK**  
Sensor Intelligence.



### Ordering information

| Type          | part no. |
|---------------|----------|
| Bar code tape | 5324106  |

Other models and accessories → [www.sick.com/Positioning\\_codes](http://www.sick.com/Positioning_codes)

### Detailed technical data

#### Features

|                        |                                                        |
|------------------------|--------------------------------------------------------|
| <b>Product segment</b> | Codes                                                  |
| <b>Product</b>         | Positioning codes                                      |
| <b>Description</b>     | 30 mm, height: 40 mm, measuring range: 320 m ... 340 m |
| <b>Suitable for</b>    | OLM100/OLM200-1x0x                                     |
| <b>Type</b>            | Standard barcode tape                                  |

#### Mechanics

|                              |                                                                                                                                                                                                                                                   |
|------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Height</b>                | 40 mm                                                                                                                                                                                                                                             |
| <b>Measuring range</b>       | 320 m ... 340 m                                                                                                                                                                                                                                   |
| <b>Raster spacing</b>        | 30 mm                                                                                                                                                                                                                                             |
| <b>Mechanical properties</b> | Moisture resistant<br>Limited chemical resistance<br>Scratch resistant<br>UV-resistant<br>Smudge-proof                                                                                                                                            |
| <b>Adhesive</b>              | Modified acrylates                                                                                                                                                                                                                                |
| <b>Adhesive strength</b>     | Aluminum: > 18 N / 25 mm<br>Steel: > 21 N / 25 mm<br>Polypropylene: > 14 N / 25 mm<br>Polyethylene: > 10 N / 25 mm                                                                                                                                |
| <b>Chemical resistance</b>   | 5% sodium hydroxide (2 h / 60 °C)<br>3% nitric acid (24 h / 21 °C)<br>Water (10 d / 21 °C)<br>Heptane (24 h / 21 °C)<br>Brake fluid (24 h / 21 °C)<br>Ethanol (2 min / wipe)<br>3% acetic acid (72 h / 21 °C)<br>3% sodium nitrate (24 h / 21 °C) |

#### Ambient data

|                                      |                                                |
|--------------------------------------|------------------------------------------------|
| <b>Ambient operating temperature</b> | -40 °C ... +150 °C                             |
| <b>Processing temperature</b>        | ≥ 4 °C                                         |
| <b>Resistance</b>                    | Dry<br>Salzsprühnebel (150 h / 5%)<br>UV light |

|                      |                                    |
|----------------------|------------------------------------|
| Substrate properties | Clean<br>Dry<br>Fat-free<br>Smooth |
|----------------------|------------------------------------|

Classifications

|                |          |
|----------------|----------|
| ECLASS 5.0     | 24280801 |
| ECLASS 5.1.4   | 24280801 |
| ECLASS 6.0     | 24280801 |
| ECLASS 6.2     | 24280801 |
| ECLASS 7.0     | 24280801 |
| ECLASS 8.0     | 24280801 |
| ECLASS 8.1     | 24280801 |
| ECLASS 9.0     | 24280801 |
| ECLASS 10.0    | 24281501 |
| ECLASS 11.0    | 24281501 |
| ECLASS 12.0    | 24281501 |
| ETIM 5.0       | EC000608 |
| ETIM 6.0       | EC000608 |
| ETIM 7.0       | EC000608 |
| ETIM 8.0       | EC000608 |
| UNSPSC 16.0901 | 41122702 |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

**For us, that is “Sensor Intelligence.”**

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)