

LL3-TH12

Fiber-optic cables

FIBER-OPTIC SENSORS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
LL3-TH12	5325972

Other models and accessories → www.sick.com/Fiber-optic_cables

Detailed technical data

Features

Device type	Fiber-optic cables
Functional principle	Through-beam system, consisting of a sender and a receiver
Fiber-optic head design	Threaded sleeve
Application	Heat-resistant ($\geq 100^{\circ}\text{C}$)
Special features	Combination of 2000 mm cost-effective low-temperature cable and 200 mm high-temperature cable (200°C)
Compatible fiber-optic amplifiers	GLL70, WLL80, WLL180, GLL170(T)
Sensing range max.	2,990 mm (Sensing range of WLL80 at 8 ms)
Minimal object diameter	0.12 mm ¹⁾
Optical fiber head	
Angle of dispersion	60°
Integrated lens	No
Compatibility tip adapters	Yes
Optical fiber	
Compatibility with infrared light	No ²⁾
Adapter end sleeves required	No
Included with delivery	Mounting, 6 x M4 hexagon nut, 2 x M4 hexagon nut (plastic), 4 x washer, FC fiber cutter (5304141), LL3-TB09

¹⁾ Minimum detectable object was determined at optimum measuring distance and optimum setting.

²⁾ Reduced sensing ranges possible when using a fiber-optic amplifier with infrared light.

Mechanics

Optical fiber head	
Light emission	Axial
Thread diameter (housing)	M4
Optical fiber taper diameter	≥ 2.6 mm
Optical fiber taper length after 2 mm	≥ 3 mm
Optical fiber	
Fiber length	2,000 mm
Bending radius	25 mm
Dynamic flexibility (robotics)	No
Outside diameter, optical fiber cable connection	2.2 mm
Fiber arrangement	Singlefiber

Material	Core structure	Ø 0,8 mm Singlefiber
	Optical fiber head	Copper-zinc alloy (CuZn)
	Sheath	Stainless steel
	Fibers	Glass
Weight		68 g

Ambient data

Ambient operating temperature	-60 °C ... +200 °C
--------------------------------------	--------------------

Sensing ranges with WLL80

Operating mode 16 µs	230 mm
Operating mode 70 µs	680 mm
Operating mode 250 µs	1,080 mm
Operating mode 500 µs	1,330 mm
Operating mode 1 ms	1,570 mm
Operating mode 2 ms	2,065 mm
Operating mode 8 ms	2,990 mm
Note	Sensing ranges related to fiber-optic sensors with type of light: visible red light

Sensing ranges with WLL180T

Operating mode 16 µs	100 mm
Operating mode 70 µs	330 mm
Operating mode 250 µs	570 mm
Operating mode 2 ms	1,100 mm
Operating mode 8 ms	1,200 mm
Note	Sensing ranges related to fiber-optic sensors with type of light: visible red light

Sensing ranges with GLL170

Operating mode 250 µs	410 mm
------------------------------	--------

Sensing ranges with GLL170T


Operating mode 50 µs	330 mm
Operating mode 250 µs	490 mm

Classifications

ECLASS 5.0	27270905
ECLASS 5.1.4	27270905
ECLASS 6.0	27270905
ECLASS 6.2	27270905
ECLASS 7.0	27270905
ECLASS 8.0	27270905
ECLASS 8.1	27270905
ECLASS 9.0	27270905
ECLASS 10.0	27270905

ECLASS 11.0	27270905
ECLASS 12.0	27270905
ETIM 5.0	EC002651
ETIM 6.0	EC002651
ETIM 7.0	EC002651
ETIM 8.0	EC002651
UNSPSC 16.0901	39121528

Dimensional drawing LL3-TH12



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com