



CQ35-25NPP-KC1

CAPACITIVE PROXIMITY SENSORS

SICKSensor Intelligence.




Ordering information

Туре	Part no.
CQ35-25NPP-KC1	6020479

Other models and accessories → www.sick.com/CQ

Illustration may differ



Detailed technical data

Features

Housing	Rectangular
Dimensions (W x H x D)	35 mm x 69.5 mm x 15 mm
Sensing range S _n	4 mm 25 mm
Safe sensing range S _a	18 mm
Installation type	Non-flush
Switching frequency	50 Hz
Connection type	Male connector M12, 4-pin
Switching output	PNP
Output function	Complementary
Electrical wiring	DC 4-wire
Adjustment	Potentiometer, 270° (Sensitivity)
Enclosure rating	IP67 ¹⁾
Items supplied	Screwdriver for potentiometer adjustment (1 x)

¹⁾ According to EN 60529.

Mechanics/electronics

Supply voltage	10 V DC 36 V DC
Ripple	≤ 10 % ¹⁾

 $^{^{1)}}$ Of Ub.

 $^{^{2)}}$ At I $_{\rm a}$ max.

³⁾ Without load.

 $^{^{4)}}$ Of Sr.

 $^{^{5)}\,\}mathrm{Supply}$ voltage Ub and constant ambient temperature Ta.

⁶⁾ In EMC critical applications, conducted interference levels may lie within the frequency range of the oscillator. This can cause changes to the output signal. (See operating instructions.).

Voltage drop	\leq 2.5 V DC $^{2)}$
Current consumption	10 mA ³⁾
Time delay before availability	≤ 100 ms
Hysteresis	4 % 20 %
Reproducibility	≤ 5 % ^{4) 5)}
Temperature drift (of S _r)	± 10 %
EMC	According to EN 60947-5-2 ⁶⁾
Continuous current I _a	≤ 200 mA
Short-circuit protection	√
Reverse polarity protection	✓
Power-up pulse protection	√
Shock and vibration resistance	30 g, 11 ms / 10 55 Hz, 1 mm
Ambient operating temperature	-25 °C +75 °C
Housing material	Plastic, PC
Sensing face material	Plastic
UL File No.	NRKH.E191603

¹⁾ Of Ub.

Safety-related parameters

MTTF _D	897 years
DC _{avg}	0 %
T _M (mission time)	20 years

Reduction factors

Note	The values are reference values which may vary
Metal	1
Water	1
PVC	Approx. 0.4
Oil	Approx. 0.25
Glass	0.6
Ceramics	0.5
Alcohol	0.7
Wood	0.2 0.7

Installation note

Remark	Associated graphic see "Installation"
Α	35 mm
В	35 mm
F	6 x S _n (max. 150 mm)

²⁾ At I_a max.

³⁾ Without load.

⁴⁾ Of Sr.


⁵⁾ Supply voltage Ub and constant ambient temperature Ta.

⁶⁾ In EMC critical applications, conducted interference levels may lie within the frequency range of the oscillator. This can cause changes to the output signal. (See operating instructions.).


Classifications

. Ale F A	07070400
eCl@ss 5.0	27270102
eCl@ss 5.1.4	27270102
eCl@ss 6.0	27270102
eCl@ss 6.2	27270102
eCl@ss 7.0	27270102
eCl@ss 8.0	27270102
eCl@ss 8.1	27270102
eCl@ss 9.0	27270102
eCl@ss 10.0	27270102
eCl@ss 11.0	27270102
eCl@ss 12.0	27274201
ETIM 5.0	EC002715
ETIM 6.0	EC002715
ETIM 7.0	EC002715
ETIM 8.0	EC002715
UNSPSC 16.0901	39122230


Installation note



Connection type



Connection diagram




Cd-006

Dimensional drawing (Dimensions in mm (inch))

CQ35, connector





- ① Display LED② Potentiometer
- ③ Connection

Recommended accessories

Other models and accessories → www.sick.com/CQ

	Brief description	Туре	Part no.
Plug connec	tors and cables		
	Head A: female connector, M12, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 2 m	YF2A14- 020UB3XLEAX	2095607
	Head A: female connector, M12, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 2 m	YF2A14- 020VB3XLEAX	2096234
	Head A: female connector, M12, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 5 m	YF2A14- 050UB3XLEAX	2095608
	Head A: female connector, M12, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m	YF2A14- 050VB3XLEAX	2096235
	Head A: female connector, M12, 4-pin, angled, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 2 m	YG2A14- 020UB3XLEAX	2095766
1	Head A: female connector, M12, 4-pin, angled, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 2 m	YG2A14- 020VB3XLEAX	2095895
3	Head A: female connector, M12, 4-pin, angled, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 5 m	YG2A14- 050UB3XLEAX	2095767
	Head A: female connector, M12, 4-pin, angled, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m	YG2A14- 050VB3XLEAX	2095897

CQ35-25NPP-KC1 | CQ CAPACITIVE PROXIMITY SENSORS

Brief description	Туре	Part no.
Head A: female connector, M12, 4-pin, straight Cable: unshielded	DOS-1204-G	6007302
Head A: female connector, M12, 4-pin, angled Cable: unshielded	DOS-1204-W	6007303

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

