



WTB190L-P132

W190 Laser Standard

PHOTOELECTRIC SENSORS

SICK
Sensor Intelligence.



Illustration may differ

Ordering information

Type	part no.
WTB190L-P132	6026549

Other models and accessories → www.sick.com/W190_Laser_Standard

Detailed technical data

Features

Functional principle	Photoelectric proximity sensor
Functional principle detail	Background suppression
Dimensions (W x H x D)	15 mm x 44.4 mm x 30 mm
Housing design (light emission)	Rectangular
Sensing range max.	40 mm ... 100 mm ¹⁾
Type of light	Visible red light
Light source	Laser
Light spot size (distance)	Ø 2 mm (80 mm)
Laser class	2
Adjustment	None

¹⁾ Object with 90% remission (based on standard white, DIN 5033).

Mechanics/electronics

Supply voltage U_B	10 V DC ... 30 V DC ¹⁾
Ripple	± 10 % ²⁾
Current consumption	40 mA ³⁾
Switching output	PNP
Switching mode	Light/dark switching
Switching mode selector	Selectable via light/dark rotary switch
Output current I_{max.}	≤ 100 mA

¹⁾ Limit values.

²⁾ May not fall below or exceed U_V tolerances.

³⁾ Without load.

⁴⁾ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

⁶⁾ Do not bend below 0 °C.

⁷⁾ A = V_S connections reverse-polarity protected.

⁸⁾ D = outputs overcurrent and short-circuit protected.

⁹⁾ Reference voltage: 50 V DC.

Response time	0.7 ms ⁴⁾
Switching frequency	700 Hz ⁵⁾
Connection type	Cable, 3-wire, 2 m ⁶⁾
Conductor cross section	0.18 mm ²
Circuit protection	A ⁷⁾ D ⁸⁾
Protection class	III ⁹⁾
Weight	200 g
Housing material	Plastic, ABS
Optics material	Plastic, PMMA
Tightening torque, max.	0.5 Nm
Enclosure rating	IP67
Ambient operating temperature	-10 °C ... +40 °C
Ambient temperature, storage	-20 °C ... +60 °C

1) Limit values.

2) May not fall below or exceed U_y tolerances.

3) Without load.

4) Signal transit time with resistive load.

5) With light/dark ratio 1:1.

6) Do not bend below 0 °C.

7) A = V_S connections reverse-polarity protected.


8) D = outputs overcurrent and short-circuit protected.

9) Reference voltage: 50 V DC.

Classifications


ECLASS 5.0	27270904
ECLASS 5.1.4	27270904
ECLASS 6.0	27270904
ECLASS 6.2	27270904
ECLASS 7.0	27270904
ECLASS 8.0	27270904
ECLASS 8.1	27270904
ECLASS 9.0	27270904
ECLASS 10.0	27270904
ECLASS 11.0	27270904
ECLASS 12.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528

Adjustments




- ⑥ Status indicator LED, yellow: Output active
- ⑦ Status indicator LED, green: Laser on
- ⑧ Adjustment of sensing range
- ⑨ selector switch light/dark switching


Connection type




Connection diagram Cd-043




Characteristic curve



Light spot size




Sensing range diagram



1	Scanning range on white, 90 % remission
2	Scanning range on grey, 18 % remission
3	Scanning range on black, 6 % remission

Dimensional drawing



Dimensions in mm (inch)

- ① Center of optical axis
- ② Mounting hole, $\varnothing$ approx. 3.1 mm
- ③ Connector 4-pin, M8, 90° rotatable or cable 2 m, 3-wire
- ④ Status indicator LED, yellow: Output active
- ⑤ Status indicator LED, green: Laser on
- ⑥ sensitivity control
- ⑦ selector switch light/dark switching

Recommended accessories

Other models and accessories → www.sick.com/W190_Laser_Standard

	Brief description	Type	part no.
Mounting systems			
	Description: Mounting bracket Material: Steel Details: Steel, zinc coated Items supplied: Mounting hardware included	BEF-W190	5311362
	Description: Plate N11N for universal clamp bracket Material: Stainless steel Details: Stainless steel 1.4571 (sheet), Stainless steel 1.4408 (clamp) Items supplied: Universal clamp (5322627), mounting hardware Usable for: DeltaPac, Glare, WTD20E	BEF-KHS-N11N	2071081
connectors and cables			
	Connection type head A: Male connector, M8, 3-pin, straight, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: 0.14 mm² ... 0.5 mm²	STE-0803-G	6037322

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com