

**SAFETY SINGLE-BEAM SENSORS** 



### L40S-33MA2A | L4000 Systems

SAFETY SINGLE-BEAM SENSORS



#### Ordering information

Scanning range	Model	Housing material	System part	Туре	Part no.
84 m	M30 axial	Nickel-plat- ed brass	Sender	L40S-33MA2A	6027335

Other models and accessories -> www.sick.com/L4000\_Systems

## 

#### Detailed technical data

Features	
Light source	LED
Type of light	Visible red light
Scanning range	84 m
Number of beams	1
Detection capability	30 mm
Optical axis	Axial
Response time	0.4 ms
Response time	0.4 ms + Test device response time (UE401)
Safety-related parameters	
Туре	Type 4 (IEC 61496-1) <sup>1)</sup>
Safety integrity level	SIL 3 (IEC 61508) <sup>1)</sup>
Category	Category 4 (EN ISO 13849) <sup>1)</sup>
Performance level	PL e (EN ISO 13849) <sup>1)</sup>
$\ensuremath{PFH}\xspace_D$ (mean probability of a dangerous failure per hour)	$2.9 \times 10^{-10} (EN ISO 13849)^{1)}$
T <sub>M</sub> (mission time)	20 years (EN ISO 13849) <sup>1)</sup>
<sup>1)</sup> Only in conjunction with UE401.	
Interfaces	
Connection type	Male connector M12, 4-pin, angled
Display elements	LED
Electrical data	
Protection class	III (IEC 61140)
Supply voltage V <sub>S</sub>	24 V DC (19.2 V DC 28.8 V DC)
Power consumption	≤ 60 mA
Mechanical data	
Design	Cylindrical

# L40S-33MA2A | L4000 Systems SAFETY SINGLE-BEAM SENSORS

Dimensions (diameter x length)	M30 x 100 mm
Housing material	Nickel-plated brass
Lens material	Glass
Weight	212 g

#### Ambient data

Enclosure rating	IP67 (EN 60529)
Ambient operating temperature	-20 °C +55 °C
Storage temperature	-25 °C +75 °C
Air humidity	15 % 95 %, Non-condensing
Vibration resistance	5 g, 10 Hz 55 Hz (IEC 60068-2-6)
Shock resistance	10 g, 16 ms (IEC 60068-2-29)

#### Other information

Light source	LED
Type of light	Visible red light
Wave length	660 nm
Aperture angle/receiving angle	± 2.5° / ± 2.5°

#### Classifications


ECLASS 5.0	27272701
ECLASS 5.1.4	27272701
ECLASS 6.0	27272701
ECLASS 6.2	27272701
ECLASS 7.0	27272701
ECLASS 8.0	27272701
ECLASS 8.1	27272701
ECLASS 9.0	27272701
ECLASS 10.0	27272701
ECLASS 11.0	27272701
ECLASS 12.0	27272701
ETIM 5.0	EC001831
ETIM 6.0	EC001831
ETIM 7.0	EC001831
ETIM 8.0	EC001831
UNSPSC 16.0901	46171620

### L40S-33MA2A | L4000 Systems

SAFETY SINGLE-BEAM SENSORS

#### Dimensional drawing (Dimensions in mm (inch))

M30, axial, angled



#### **Recommended accessories**

Other models and accessories → www.sick.com/L4000\_Systems

	Brief description	Туре	Part no.	
Alignment aids				
<b>N</b>	Adapter AR60 for M30 sensors (L4000 Systems, L41 and L21)	AR60 adapter, M30 sensors	5311529	
Deflector mirr	rors			
Þ	Horizontal deflection, 75 mm x 80 mm reflector surface, Glass, Incl. mounting kit (2 x swivel mount)	PNS75-008	1026647	
estar T	Horizontal deflection, 96 mm x 124 mm reflector surface, Glass	PSK1	1005229	
	Deflector mirror for 90 $^\circ$ deflection, mirror surface 97 mm x 80 mm, not suitable for column mounting, Glass, mounting hardware included	PSK45	5306053	
Mounting bra	ckets and plates			
40	Mounting bracket for M30 sensors, steel, zinc coated, without mounting hardware	BEF-WN-M30	5308445	
Plug connecto	ors and cables			
•	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A14-050VB3XLEAX	2096235	
*	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YG2A14-050VB3XLEAX	2095897	

# L40S-33MA2A | L4000 Systems SAFETY SINGLE-BEAM SENSORS

	Brief description	Туре	Part no.	
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight</li> <li>Description: Unshielded, Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: -</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm<sup>2</sup></li> </ul>	DOS-1204-G	6007302	
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled</li> <li>Description: Unshielded, Head A: female connector, M12, 4-pin, angled, unshielded, for power supply, for cable diameter 3 mm 6.5 mm Head B: -</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm<sup>2</sup></li> </ul>	DOS-1204-W	6007303	
Switching amplifiers				
	<ul> <li>Applications: Evaluation unit</li> <li>Compatible sensor types: L4000 Systems single-beam photoelectric safety switches</li> </ul>	UE401-A0010	6027343	

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

### WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

