





FORK SENSORS



Ordering information

Туре	Part no.
WF2-40B410	6028428

Other models and accessories -> www.sick.com/WF

Illustration may differ



Detailed technical data

Features

Functional principle	Fork sensor
Functional principle detail	Optical detection principle
Dimensions (W x H x D)	10 mm x 32 mm x 57 mm
Fork width	2 mm
Fork depth	42 mm
Minimum detectable object (MDO)	0.2 mm
Label detection	✓
Light source	LED, infrared
Wave length	850 nm
Adjustment	Plus/minus button (Sensitivity, light/dark switching, key lock)
Teach-in mode	-
Output function	Light/darkswitching, selectable via button

Mechanics/electronics

Current consumption	40 mA
Switching frequency	10 kHz ¹⁾
Response time	100 µs
Stability of response time	± 20 µs
Jitter	40 µs
Switching output	PNP/NPN
Switching output (voltage)	PNP: HIGH = $U_V \le 2 V / LOW$ approx. 0 V NPN: HIGH = approx. $U_V / LOW \le 2 V$
Switching mode	Light/dark switching
Output current I _{max.}	100 mA

 $^{1)}$ With light/dark ratio 1:1.

²⁾ Reference voltage DC 50 V.

³⁾ Depending on fork width.

WF2-40B410 | WF

FORK SENSORS

Initialization time	100 ms
Connection type	Male connector M8, 4-pin
Protection class	III ²)
Circuit protection	U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression
Enclosure rating	IP65
Weight	Approx. 36 g 160 g ³⁾
Housing material	Metal, Aluminum

¹⁾ With light/dark ratio 1:1.

²⁾ Reference voltage DC 50 V.


³⁾ Depending on fork width.

Safety-related parameters

MTTF _D	97 years
DC _{avg}	0 %
Ambient data	
Ambient light immunity	≤ 10,000 lx
Shock load	According to EN 60068-2-27
UL File No.	NRKH.E191603
Classifications	
ECLASS 5.0	27270909
ECLASS 5.1.4	27270909
ECLASS 6.0	27270909
ECLASS 6.2	27270909
ECLASS 7.0	27270909
ECLASS 8.0	27270909
ECLASS 8.1	27270909
ECLASS 9.0	27270909
ECLASS 10.0	27270909
ECLASS 11.0	27270909
ECLASS 12.0	27270909
ETIM 5.0	EC002720
ETIM 6.0	EC002720
ETIM 7.0	EC002720
ETIM 8.0	EC002720
UNSPSC 16.0901	39121528

FORK SENSORS

Dimensional drawing (Dimensions in mm (inch))



Dimensions	in	mm	(inch)
------------	----	----	--------

	A Fork width	B Fork depth	С	C1
WF2	2	42/59/95	14	5
	(0.08)	(1.65/2.32/3.74)	(0.55)	(0.20)
WF5	5	42/59/95	14	6.5
	(0.20)	(1.65/2.32/3.74)	(0.55)	(0.20)
WF15	15	42/59/95	27	5
	(0.59)	(1.65/2.32/3.74)	(1.06)	(0.20)
WF30	30	42/59/95	42	5
	(1.18)	(1.65/2.32/3.74)	(1.65)	(0.20)
WF50	50	42/59/95	51	16
	(1.97)	(1.65/2.32/3.74)	(2.01)	(0.63)
WF80	80	42/59/95	81	16
	(3.15)	(1.65/2.32/3.74)	(3.19)	(0.63)
WF120	120	42/59/95	121	16
	(4.72)	(1.65/2.32/3.74)	(4.76)	(0.63)


① Optical axis

② Mounting hole, Ø 4.2 mm

③ WF50/80/120 only

Adjustments

Adjustment: plus/minus buttons (WFxx-B410)




Function signal indicator (yellow), switching output
 Function indicator (red)

③ "+"/"-" buttons and function button

Connection diagram

Cd-086



Concept of operation


Setting the switching threshold via plus/minus buttons (WFxx-B410)

1. No object in the beam path

0

The yellow function indicator illuminates when the light received is at its optimum level. If necessary, increase sensitivity using the "+" button.

2. Object in the beam path



Yellow function indicator goes out. If necessary, reduce sensitivity using the "-" button.

Recommended accessories

Other models and accessories -> www.sick.com/WF

	Brief description	Туре	Part no.		
Plug connecto	Plug connectors and cables				
	 Connection type head A: Female connector, M8, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF8U14- 050VA3XLEAX	2095889		
	 Connection type head A: Male connector, M8, 4-pin, straight Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: 0.14 mm² 0.5 mm² 	STE-0804-G	6037323		

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

