

WL100L-E2231

W100 Laser

MINIATURE PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
WL100L-E2231	6030713

Included in delivery: BEF-W100-A (1), P250F (1)

Other models and accessories → www.sick.com/W100_Laser

Illustration may differ



Detailed technical data

Features

Functional principle	Photoelectric retro-reflective sensor
Functional principle detail	Dual lens
Dimensions (W x H x D)	11 mm x 31 mm x 20 mm
Housing design (light emission)	Rectangular
Sensing range max.	0.08 m 12 m ¹⁾
Sensing range	0.08 m 10 m ¹⁾
Type of light	Visible red light
Light source	Laser ²⁾
Light spot size (distance)	Ø 12 mm (10 m)
Wave length	650 nm
Laser class	1
Adjustment	Potentiometer, 270°
Special applications	Detecting small objects

¹⁾ Reflector P250F.

Mechanics/electronics

Supply voltage U _B	10 V DC 30 V DC ¹⁾
Ripple	± 10 % ²⁾

 $^{^{1)}}$ Limit values when operated in short-circuit protected network: max. 8 A.

 $^{^{2)}}$ Average service life: 50,000 h at T_U = +25 °C.

 $^{^{\}rm 2)}$ May not exceed or fall below ${\rm U_{V}}$ tolerances.

³⁾ Without load.

 $^{^{4)}}$ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

 $^{^{6)}}$ A = $\rm V_{S}$ connections reverse-polarity protected.

⁷⁾ B = inputs and output reverse-polarity protected.

 $^{^{8)}}$ D = outputs overcurrent and short-circuit protected.

Current consumption	30 mA ³⁾
Switching output	NPN
Switching mode	Light/dark switching
Switching mode selector	Selectable via light/dark rotary switch
Signal voltage NPN HIGH/LOW	Approx. V_S / < 1.8 V
Output current I _{max.}	≤ 100 mA
Response time	< 0.25 ms ⁴⁾
Switching frequency	2,000 Hz ⁵⁾
Connection type	Male connector M8, 4-pin
Circuit protection	A ⁶⁾ B ⁷⁾ D ⁸⁾
Weight	10 g
Polarisation filter	✓
Housing material	Plastic, ABS/PC
Optics material	Plastic, PMMA
Enclosure rating	IP65
Items supplied	Stainless steel mounting bracket (1.4301/304) BEF-W100-A
Ambient operating temperature	-10 °C +50 °C
Ambient temperature, storage	-40 °C +70 °C

¹⁾ Limit values when operated in short-circuit protected network: max. 8 A.

Safety-related parameters

MTTF _D	453 years
DC _{avg}	0 %

Classifications

ECLASS 5.0	27270902
ECLASS 5.1.4	27270902
ECLASS 6.0	27270902
ECLASS 6.2	27270902
ECLASS 7.0	27270902
ECLASS 8.0	27270902
ECLASS 8.1	27270902
ECLASS 9.0	27270902
ECLASS 10.0	27270902
ECLASS 11.0	27270902

 $^{^{2)}\,\}text{May}$ not exceed or fall below U_{V} tolerances.

³⁾ Without load.

 $^{^{4)}}$ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

⁶⁾ A = V_S connections reverse-polarity protected.

 $^{^{7)}}$ B = inputs and output reverse-polarity protected.

 $^{^{8)}}$ D = outputs overcurrent and short-circuit protected.


WL100L-E2231 | W100 Laser


MINIATURE PHOTOELECTRIC SENSORS

ECLASS 12.0	27270901
ETIM 5.0	EC002717
ETIM 6.0	EC002717
ETIM 7.0	EC002717
ETIM 8.0	EC002717
UNSPSC 16.0901	39121528

Dimensional drawing (Dimensions in mm (inch))

WT100L, WL100L






- ① Threaded mounting hole M3
- ② Center of optical axis, receiver
- 3 Center of optical axis, sender
- 4 Connection

Adjustments

WT100L, WL100L




- ⑤ Orange LED indicator: switching output active
- ® LED indicator green: power on
- ① Sensing range (WT) / sensitivity (WL) adjustment: potentiometer, 270°
- 8 Light/ dark rotary switch: L = light switching, D = dark switching

Connection type




Connection diagram

Cd-066



Characteristic curve

WL100L




- ① Reflector P250F
- ② Reflector PL20F
- ③ PL10F reflector

MINIATURE PHOTOELECTRIC SENSORS

Light spot size

WL100L




All dimensions in mm (feet)

Sensing range diagram

WL100L

3 PL10F reflector



Recommended accessories

Other models and accessories → www.sick.com/W100_Laser

	Brief description	Туре	Part no.
Mounting brackets and plates			
	Universal mounting bracket for reflectors, steel, zinc coated	BEF-WN-REFX	2064574
Plug connectors and cables			
	 Connection type head A: Male connector, M8, 4-pin, straight Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: 0.14 mm² 0.5 mm² 	STE-0804-G	6037323
Reflectors			
	Fine triple reflector, screw connection, suitable for laser sensors, $52 \text{ mm} \times 62 \text{ mm}$, PM-MA/ABS, Screw-on, 2 hole mounting	P250F	5308843

	Brief description	Туре	Part no.
Others			
	 Connection type head A: Female connector, M8, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF8U14- 050VA3XLEAX	2095889

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

